

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- RH

BASE

Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, matte finish.

ARTICULATED STEM

Threaded AISI 304 stainless steel with adjusting square.

STANDARD EXECUTIONS

- **LVQ.A-SST:** without no-slip disk.
- **LVQ.A-AS-SST:** with NBR rubber no-slip disk, hardness 70 Shore A, supplied assembled to the base.

FEATURES

The special knurling under the lower lip of the base provides excellent stability and grip when using the levelling element without no-slip disk even on surfaces that are not perfectly flat.

The particular assembling system of the no-slip disk to the base assures a perfect anchoring, preventing separation even in case of impact during transport or of adhesion (sticking) to the floor (see No-slip disks on page 979).

ORDER INFORMATION


The levelling elements are supplied unassembled to make carriage and storage easier. The components (base and stem) are supplied in separate packing: less volume taken and better protection from scratches and dirt.

To order bases and stems separately, see:

- table of possible combinations Bases/Stems (see page 983)
- the codes of the Bases (see page 980)
- the codes of the Stems (see page 985).

ACCESSORIES ON REQUEST

AISI 304 stainless steel nut (see Nuts NT. on page 979).




Levelling elements and supports

LVQ.A-SST

LVQ.A-AS-SST

Code	Description	Code	Description	D	d2A	L	l	l1	l2	h	s	Articulation ∅	Max. limit static load* [lbf]	⚖	⚖ #
90323903	LVQ.A-60-14-SST-5/8-11x4	90327903	LVQ.A-60-14-AS-SST-5/8-11x4	2.36	5/8-11	5.35	4.000	1.34	1.28	0.94	1/2	0.55	4032	0.42	0.46
90323905	LVQ.A-60-14-SST-5/8-11x6	90327905	LVQ.A-60-14-AS-SST-5/8-11x6	2.36	5/8-11	7.32	6.000	1.34	1.28	0.94	1/2	0.55	4032	0.59	0.63
90323907	LVQ.A-60-14-SST-5/8-11x8	90327907	LVQ.A-60-14-AS-SST-5/8-11x8	2.36	5/8-11	9.33	8.000	1.34	1.28	0.94	1/2	0.55	4032	0.77	0.81
90323911	LVQ.A-60-14-SST-3/4-10x4	90327911	LVQ.A-60-14-AS-SST-3/4-10x4	2.36	3/4-10	5.55	4.000	1.54	1.44	0.94	9/16	0.55	4032	0.56	0.6
90323913	LVQ.A-60-14-SST-3/4-10x6	90327913	LVQ.A-60-14-AS-SST-3/4-10x6	2.36	3/4-10	7.52	6.000	1.54	1.44	0.94	9/16	0.55	4032	0.81	0.85
90323915	LVQ.A-60-14-SST-3/4-10x8	90327915	LVQ.A-60-14-AS-SST-3/4-10x8	2.36	3/4-10	9.53	8.000	1.54	1.44	0.94	9/16	0.55	4032	1.06	1.1

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.



LVQ.A-SST

LVQ.A-AS-SST

INOX STAINLESS STEEL INCH

Code	Description	Code	Description	D	d2A	L	l	l1	l2	h	s	Articulation ∅	Max. limit static load* [lbf]	⚖	⚖ #
90324183	LVQ.A-70-14-SST-5/8-11x4	90328183	LVQ.A-70-14-AS-SST-5/8-11x4	2.76	5/8-11	5.16	4.000	1.14	1.08	0.75	1/2	0.55	4032	0.41	0.46
90324186	LVQ.A-70-14-SST-5/8-11x6	90328185	LVQ.A-70-14-AS-SST-5/8-11x6	2.76	5/8-11	7.13	6.000	1.14	1.08	0.75	1/2	0.55	4032	0.59	0.63
90324187	LVQ.A-70-14-SST-5/8-11x8	90328187	LVQ.A-70-14-AS-SST-5/8-11x8	2.76	5/8-11	9.13	8.000	1.14	1.08	0.75	1/2	0.55	4032	0.76	0.81
90324192	LVQ.A-70-14-SST-3/4-10x4	90328195	LVQ.A-70-14-AS-SST-3/4-10x4	2.76	3/4-10	5.35	4.000	1.34	1.24	0.75	9/16	0.55	4032	0.55	0.6
90324193	LVQ.A-70-14-SST-3/4-10x6	90328191	LVQ.A-70-14-AS-SST-3/4-10x6	2.76	3/4-10	7.32	6.000	1.34	1.24	0.75	9/16	0.55	4032	0.81	0.85
90324195	LVQ.A-70-14-SST-3/4-10x8	90328195	LVQ.A-70-14-AS-SST-3/4-10x8	2.76	3/4-10	9.33	8.000	1.34	1.24	0.75	9/16	0.55	4032	1.06	1.1
90325003	LVQ.A-80-14-SST-5/8-11x4	90329003	LVQ.A-80-14-AS-SST-5/8-11x4	3.15	5/8-11	5.35	4.000	1.34	1.28	0.94	1/2	0.55	4032	0.46	0.52
90325005	LVQ.A-80-14-SST-5/8-11x6	90329005	LVQ.A-80-14-AS-SST-5/8-11x6	3.15	5/8-11	7.32	6.000	1.34	1.28	0.94	1/2	0.55	4032	0.64	0.7
90325007	LVQ.A-80-14-SST-5/8-11x8	90329007	LVQ.A-80-14-AS-SST-5/8-11x8	3.15	5/8-11	9.33	8.000	1.34	1.28	0.94	1/2	0.55	4032	0.81	0.87
90325011	LVQ.A-80-14-SST-3/4-10x4	90329011	LVQ.A-80-14-AS-SST-3/4-10x4	3.15	3/4-10	5.55	4.000	1.54	1.44	0.94	9/16	0.55	4032	0.6	0.66
90325013	LVQ.A-80-14-SST-3/4-10x6	90329013	LVQ.A-80-14-AS-SST-3/4-10x6	3.15	3/4-10	7.52	6.000	1.54	1.44	0.94	9/16	0.55	4032	0.64	0.91
90325015	LVQ.A-80-14-SST-3/4-10x8	90329015	LVQ.A-80-14-AS-SST-3/4-10x8	3.15	3/4-10	9.53	8.000	1.54	1.44	0.94	9/16	0.55	4032	1.11	1.17
90325853	LVQ.A-100-14-SST-5/8-11x4	90329853	LVQ.A-100-14-AS-SST-5/8-11x4	3.94	5/8-11	5.31	4.000	1.34	1.28	0.94	1/2	0.55	4032	0.53	0.65
90325855	LVQ.A-100-14-SST-5/8-11x6	90329855	LVQ.A-100-14-AS-SST-5/8-11x6	3.94	5/8-11	7.32	6.000	1.34	1.28	0.94	1/2	0.55	4032	0.7	0.82
90325857	LVQ.A-100-14-SST-5/8-11x8	90329857	LVQ.A-100-14-AS-SST-5/8-11x8	3.94	5/8-11	9.33	8.000	1.34	1.28	0.94	1/2	0.55	4032	0.88	1
90325861	LVQ.A-100-14-SST-3/4-10x4	90329861	LVQ.A-100-14-AS-SST-3/4-10x4	3.94	3/4-10	5.51	4.000	1.54	1.44	0.94	9/16	0.55	4032	0.67	0.79
90325863	LVQ.A-100-14-SST-3/4-10x6	90329863	LVQ.A-100-14-AS-SST-3/4-10x6	3.94	3/4-10	7.52	6.000	1.54	1.44	0.94	9/16	0.55	4032	0.92	1.04
90325865	LVQ.A-100-14-SST-3/4-10x8	90329865	LVQ.A-100-14-AS-SST-3/4-10x8	3.94	3/4-10	9.53	8.000	1.54	1.44	0.94	9/16	0.55	4032	1.17	1.29

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.

