

INSLX[®]

SAFETY DATA SHEET

Revision Date: 26-Mar-2020

Revision Number: 2

1. PRODUCT AND COMPANY IDENTIFICATION

Product Name	TOUGH SHIELD FLOOR AND PATIO - LOW VOC, GRAY PEARL
Product Code	CTS-3308
Alternate Product Code	UG0508
Product Class	Water thinned paint
Color	Gray
Recommended use	Paint
Restrictions on use	No information available

Manufacturer
Benjamin Moore & Co.
101 Paragon Drive
Montvale, NJ 07645
Phone: 1-866-708-9180
insl-x.com

Emergency Telephone
CHEMTREC (US): 800-424-9300
CHEMTREC (outside US): (703)-527-3887

2. HAZARDS IDENTIFICATION

Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Carcinogenicity	Category 2
-----------------	------------

Label elements

Warning

Hazard statements

Suspected of causing cancer



Appearance liquid

Odor little or no odor

Precautionary Statements - Prevention

Obtain special instructions before use

Do not handle until all safety precautions have been read and understood

Use personal protective equipment as required

Precautionary Statements - Response

IF exposed or concerned: Get medical advice/attention

Precautionary Statements - Storage

Store locked up

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not applicable

Other information

No information available

Other hazards

CAUTION: All floor coatings may become slippery when wet. Where non-skid characteristics are desired, use an appropriate anti-slip aggregate.

3. COMPOSITION INFORMATION ON COMPONENTS

Chemical name	CAS No.	Weight-%
Kaolin	1332-58-7	5 - 10
Titanium dioxide	13463-67-7	5 - 10
Nepheline syenite	37244-96-5	5 - 10
Ethanol, 2-(2-butoxyethoxy)-	112-34-5	1 - 5
2-Propanol-1-butoxy	5131-66-8	1 - 5
Carbon black	1333-86-4	0.1 - 0.5
Sodium C14-C16 olefin sulfonate	68439-57-6	0.1 - 0.5

4. FIRST AID MEASURES

General Advice	No hazards which require special first aid measures.
Eye Contact	Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.
Skin Contact	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes.
Inhalation	Move to fresh air. If symptoms persist, call a physician.
Ingestion	Clean mouth with water and afterwards drink plenty of water. Consult a physician if necessary.
Most Important Symptoms/Effects	None known.
Notes To Physician	Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Protective equipment and precautions for firefighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.
Specific Hazards Arising From The Chemical	Closed containers may rupture if exposed to fire or extreme heat.
Sensitivity to mechanical impact	No
Sensitivity to static discharge	No
Flash Point Data	
Flash point (°F)	Not applicable
Flash Point (°C)	Not applicable
Method	Not applicable
Flammability Limits In Air	
Lower flammability limit:	Not applicable
Upper flammability limit:	Not applicable

NFPA **Health:** 1 **Flammability:** 0 **Instability:** 0 **Special:** Not Applicable

NFPA Legend

0 - Not Hazardous
1 - Slightly
2 - Moderate
3 - High
4 - Severe

The ratings assigned are only suggested ratings, the contractor/employer has ultimate responsibilities for NFPA ratings where this system is used.

Additional information regarding the NFPA rating system is available from the National Fire Protection Agency (NFPA) at www.nfpa.org.

6. ACCIDENTAL RELEASE MEASURES

Personal Precautions	Avoid contact with skin, eyes and clothing. Ensure adequate ventilation.
Other Information	Prevent further leakage or spillage if safe to do so.
Environmental precautions	See Section 12 for additional Ecological Information.
Methods for Cleaning Up	Soak up with inert absorbent material. Sweep up and shovel into suitable containers for disposal.

7. HANDLING AND STORAGE

Handling	Avoid contact with skin, eyes and clothing. Avoid breathing vapors, spray mists or
-----------------	--

sanding dust. In case of insufficient ventilation, wear suitable respiratory equipment.

Storage Keep container tightly closed. Keep out of the reach of children.

Incompatible Materials No information available

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Limits

Chemical name	ACGIH TLV	OSHA PEL
Kaolin	TWA: 2 mg/m ³ particulate matter containing no asbestos and <1% crystalline silica, respirable particulate matter	15 mg/m ³ - TWA 5 mg/m ³ - TWA
Titanium dioxide	TWA: 10 mg/m ³	15 mg/m ³ - TWA
Ethanol, 2-(2-butoxyethoxy)-	TWA: 10 ppm inhalable fraction and vapor	N/E
Carbon black	TWA: 3 mg/m ³ inhalable particulate matter	3.5 mg/m ³ - TWA

Legend

ACGIH - American Conference of Governmental Industrial Hygienists Exposure Limits

OSHA - Occupational Safety & Health Administration Exposure Limits

N/E - Not Established

Engineering Measures Ensure adequate ventilation, especially in confined areas.

Personal Protective Equipment

Eye/Face Protection Safety glasses with side-shields.

Skin Protection Protective gloves and impervious clothing.

Respiratory Protection In case of insufficient ventilation wear suitable respiratory equipment.

Hygiene Measures Avoid contact with skin, eyes and clothing. Remove and wash contaminated clothing before re-use. Wash thoroughly after handling.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	liquid
Odor	little or no odor
Odor Threshold	No information available
Density (lbs/gal)	10.0 - 10.4
Specific Gravity	1.21 - 1.25
pH	No information available
Viscosity (cps)	No information available
Solubility(ies)	No information available
Water solubility	No information available
Evaporation Rate	No information available
Vapor pressure	No information available
Vapor density	No information available
Wt. % Solids	45 - 55
Vol. % Solids	35 - 45

Wt. % Volatiles	45 - 55
Vol. % Volatiles	55 - 65
VOC Regulatory Limit (g/L)	< 100
Boiling Point (°F)	212
Boiling Point (°C)	100
Freezing point (°F)	32
Freezing Point (°C)	0
Flash point (°F)	Not applicable
Flash Point (°C)	Not applicable
Method	Not applicable
Flammability (solid, gas)	Not applicable
Upper flammability limit:	Not applicable
Lower flammability limit:	Not applicable
Autoignition Temperature (°F)	No information available
Autoignition Temperature (°C)	No information available
Decomposition Temperature (°F)	No information available
Decomposition Temperature (°C)	No information available
Partition coefficient	No information available

10. STABILITY AND REACTIVITY

Reactivity	Not Applicable
Chemical Stability	Stable under normal conditions.
Conditions to avoid	Prevent from freezing.
Incompatible Materials	No materials to be especially mentioned.
Hazardous Decomposition Products	None under normal use.
Possibility of hazardous reactions	None under normal conditions of use.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Principal Routes of Exposure Eye contact, skin contact and inhalation.

Acute Toxicity

Product Information No information available

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Eye contact May cause slight irritation.
Skin contact Substance may cause slight skin irritation. Prolonged or repeated contact may dry

Inhalation	skin and cause irritation.
Ingestion	May cause irritation of respiratory tract.
Sensitization	Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.
Neurological Effects	No information available
Mutagenic Effects	No information available.
Reproductive Effects	No information available.
Developmental Effects	No information available.
Target organ effects	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Other adverse effects	No information available.
Aspiration Hazard	No information available

Numerical measures of toxicity

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral) 93828 mg/kg

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Kaolin 1332-58-7	> 5000 mg/kg (Rat)	> 5000 mg/kg (Rat)	-
Titanium dioxide 13463-67-7	> 10000 mg/kg (Rat)	-	-
Ethanol, 2-(2-butoxyethoxy)- 112-34-5	= 5660 mg/kg (Rat)	= 2700 mg/kg (Rabbit)	-
2-Propanol-1-butoxy 5131-66-8	= 1900 mg/kg (Rat) = 5660 µL/kg (Rat)	= 3100 mg/kg (Rabbit)	-
Carbon black 1333-86-4	> 15400 mg/kg (Rat)	> 3 g/kg (Rabbit)	-
Sodium C14-C16 olefin sulfonate 68439-57-6	= 2220 mg/kg (Rat)	> 740 mg/kg (Rabbit)	-

Chronic Toxicity

Carcinogenicity

The information below indicates whether each agency has listed any ingredient as a carcinogen:.

Chemical name	IARC	NTP	OSHA
Titanium dioxide	2B - Possible Human Carcinogen		Listed
Carbon black	2B - Possible Human Carcinogen		Listed

• Although IARC has classified titanium dioxide as possibly carcinogenic to humans (2B), their summary concludes: "No significant exposure to titanium dioxide is thought to occur during the use of products in which titanium dioxide is bound to other materials, such as paint."

Legend

IARC - International Agency for Research on Cancer
NTP - National Toxicity Program
OSHA - Occupational Safety & Health Administration

12. ECOLOGICAL INFORMATION

Ecotoxicity Effects

The environmental impact of this product has not been fully investigated.

Product Information

Acute Toxicity to Fish

No information available

Acute Toxicity to Aquatic Invertebrates

No information available

Acute Toxicity to Aquatic Plants

No information available

Persistence / Degradability

No information available.

Bioaccumulation

No information available.

Mobility in Environmental Media

No information available.

Ozone

No information available

Component Information

Acute Toxicity to Fish

Titanium dioxide

LC50: > 1000 mg/L (Fathead Minnow - 96 hr.)

Acute Toxicity to Aquatic Invertebrates

Ethanol, 2-(2-butoxyethoxy)-

EC50: 100 mg/L (Daphnia - 48 hr.)

Acute Toxicity to Aquatic Plants

No information available

13. DISPOSAL CONSIDERATIONS

Waste Disposal Method

Dispose of in accordance with federal, state, and local regulations. Local requirements may vary, consult your sanitation department or state-designated environmental protection agency for more disposal options.

14. TRANSPORT INFORMATION

DOT Not regulated

ICAO / IATA Not regulated

IMDG / IMO Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA: United States Yes - All components are listed or exempt.

DSL: Canada Yes - All components are listed or exempt.

Federal Regulations

SARA 311/312 hazardous categorization

Acute health hazard	No
Chronic Health Hazard	Yes
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372:

<u>Chemical name</u>	<u>CAS No.</u>	<u>Weight-%</u>	<u>CERCLA/SARA 313</u> <u>(de minimis concentration)</u>
Ethanol, 2-(2-butoxyethoxy)-	112-34-5	1 - 5	1.0

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product contains the following HAPs:

<u>Chemical name</u>	<u>CAS No.</u>	<u>Weight-%</u>	<u>Hazardous Air Pollutant</u> <u>(HAP)</u>
Ethanol, 2-(2-butoxyethoxy)-	112-34-5	1 - 5	Listed

US State Regulations

California Proposition 65



WARNING: Cancer and Reproductive Harm— www.P65warnings.ca.gov

State Right-to-Know

Chemical name	Massachusetts	New Jersey	Pennsylvania
Kaolin	X	X	X
Titanium dioxide	X	X	X
Ethanol, 2-(2-butoxyethoxy)-		X	X
Carbon black	X	X	X

Legend

X - Listed

16. OTHER INFORMATION

HMIS - **Health:** 1* **Flammability:** 0 **Reactivity:** 0 **PPE:** -

HMIS Legend

0 - Minimal Hazard

1 - Slight Hazard

2 - Moderate Hazard

3 - Serious Hazard

4 - Severe Hazard

* - Chronic Hazard

X - Consult your supervisor or S.O.P. for "Special" handling instructions.

Note: The PPE rating has intentionally been left blank. Choose appropriate PPE that will protect employees from the hazards the material will present under the actual normal conditions of use.

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings are not required on MSDSs under 29 CFR 1910.1200, the preparer, has chosen to provide them. HMIS® ratings are to be used only in conjunction with a fully implemented HMIS® program by workers who have received appropriate HMIS® training. HMIS® is a registered trade and service mark of the NPCA. HMIS® materials may be purchased exclusively from J. J. Keller (800) 327-6868.

WARNING! If you scrape, sand, or remove old paint, you may release lead dust. LEAD IS TOXIC. EXPOSURE TO LEAD DUST CAN CAUSE SERIOUS ILLNESS, SUCH AS BRAIN DAMAGE, ESPECIALLY IN CHILDREN. PREGNANT WOMEN SHOULD ALSO AVOID EXPOSURE. Wear a NIOSH approved respirator to control lead exposure. Clean up carefully with a HEPA vacuum and a wet mop. Before you start, find out how to protect yourself and your family by contacting the National Lead Information Hotline at 1-800-424-LEAD or log on to www.epa.gov/lead.

Prepared By Product Stewardship Department
Benjamin Moore & Co.
101 Paragon Drive
Montvale, NJ 07645
800-225-5554

Revision Date: 26-Mar-2020
Revision Summary Not available

Disclaimer

The information contained herein is presented in good faith and believed to be accurate as of the effective date shown above. This information is furnished without warranty of any kind. Employers should use this information only as a supplement to other information gathered by them and must make independent determination of suitability and completeness of information from all sources to assure proper use of these materials and the safety and health of employees. Any use of this data and information must be determined by the user to be in accordance with applicable federal, provincial, and local laws and regulations.

End of Safety Data Sheet