

INSL-X

SAFETY DATA SHEET

Revision Date: 24-Mar-2020

Revision Number: 1

1. PRODUCT AND COMPANY IDENTIFICATION

Product Name INSL-X HEAVY DUTY DEGREASER
Product Code CL01-00
Alternate Product Code UA3200
Product Class SURFACE PREPARATION PRODUCT
Color Clear
Recommended use Degreaser
Restrictions on use No information available

Manufacturer
Benjamin Moore & Co.
101 Paragon Drive
Montvale, NJ 07645
Phone: 1-866-708-9180
insl-x.com

Emergency Telephone
CHEMTREC (US): 800-424-9300
CHEMTREC (outside US): (703)-527-3887

2. HAZARDS IDENTIFICATION

Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin corrosion/irritation	Category 2
Serious eye damage/eye irritation	Category 1
Skin sensitization	Category 1

Label elements

Danger

Hazard statements

Causes skin irritation
Causes serious eye damage
May cause an allergic skin reaction



Appearance liquid

Odor mild

Precautionary Statements - Prevention

Wash face, hands and any exposed skin thoroughly after handling
 Wear protective gloves/protective clothing/eye protection/face protection
 Avoid breathing dust/fume/gas/mist/vapors/spray
 Contaminated work clothing should not be allowed out of the workplace

Eyes

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.
 Continue rinsing
 Immediately call a POISON CENTER or doctor/physician

Skin

IF ON SKIN: Wash with plenty of soap and water
 Take off contaminated clothing and wash before reuse
 If skin irritation or rash occurs: Get medical advice/attention

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not applicable

Other information

No information available

3. COMPOSITION INFORMATION ON COMPONENTS

Chemical name	CAS No.	Weight-%
Ethanol, 2-(2-butoxyethoxy)-	112-34-5	5 - 10
Sodium tripolyphosphate	7758-29-4	1 - 5
Monoethanolamine phosphate	29868-05-1	0.5 - 1
Ethanol, 2-amino-	141-43-5	0.5 - 1
3,5,7-Triaza-1-azoniatricyclo[3.3.1.1 ^{3,7}]decane, 1-(3-chloro-2-propen-1-yl)-, chloride	4080-31-3	0.5 - 1

4. FIRST AID MEASURES

General Advice

No hazards which require special first aid measures.

Eye Contact

Immediate medical attention is required. Immediately flush with plenty of water.
 After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes.

Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. If skin irritation persists, call a physician. Wash clothing before reuse. Destroy contaminated articles such as shoes.

Inhalation

Move to fresh air. If symptoms persist, call a physician.

Ingestion

Clean mouth with water and afterwards drink plenty of water. Consult a physician if necessary.

Most Important Symptoms/Effects May cause allergic skin reaction.

Notes To Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Protective equipment and precautions for firefighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.
Specific Hazards Arising From The Chemical	Closed containers may rupture if exposed to fire or extreme heat.
Sensitivity to mechanical impact	No
Sensitivity to static discharge	No
Flash Point Data	
Flash point (°F)	375
Flash Point (°C)	191
Method	PMCC
Flammability Limits In Air	
Lower flammability limit:	Not applicable
Upper flammability limit:	Not applicable

NFPA **Health:** 2 **Flammability:** 1 **Instability:** 0 **Special:** Not Applicable

NFPA Legend

0 - Not Hazardous
 1 - Slightly
 2 - Moderate
 3 - High
 4 - Severe

The ratings assigned are only suggested ratings, the contractor/employer has ultimate responsibilities for NFPA ratings where this system is used.

Additional information regarding the NFPA rating system is available from the National Fire Protection Agency (NFPA) at www.nfpa.org.

6. ACCIDENTAL RELEASE MEASURES

Personal Precautions	Avoid contact with skin, eyes and clothing. Ensure adequate ventilation.
Other Information	Prevent further leakage or spillage if safe to do so.
Environmental precautions	See Section 12 for additional Ecological Information.
Methods for Cleaning Up	Soak up with inert absorbent material. Sweep up and shovel into suitable

containers for disposal.

7. HANDLING AND STORAGE

Handling	Avoid contact with skin, eyes and clothing. Avoid breathing vapors, spray mists or sanding dust. In case of insufficient ventilation, wear suitable respiratory equipment.
Storage	Keep container tightly closed. Keep out of the reach of children.
Incompatible Materials	No information available

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Limits

Chemical name	ACGIH TLV	OSHA PEL
Ethanol, 2-(2-butoxyethoxy)-	TWA: 10 ppm inhalable fraction and vapor	N/E
Ethanol, 2-amino-	STEL: 6 ppm TWA: 3 ppm	3 ppm - TWA 6 mg/m ³ - TWA

Legend

ACGIH - American Conference of Governmental Industrial Hygienists Exposure Limits

OSHA - Occupational Safety & Health Administration Exposure Limits

N/E - Not Established

Engineering Measures Ensure adequate ventilation, especially in confined areas.

Personal Protective Equipment

Eye/Face Protection

Safety glasses with side-shields. If splashes are likely to occur, wear:. Tightly fitting safety goggles.

Skin Protection

Protective gloves and impervious clothing.

Respiratory Protection

In case of insufficient ventilation wear suitable respiratory equipment.

Hygiene Measures Avoid contact with skin, eyes and clothing. Remove and wash contaminated clothing before re-use. Wash thoroughly after handling.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	liquid
Odor	mild
Odor Threshold	No information available
Density (lbs/gal)	8.85 - 8.95
Specific Gravity	1.06 - 1.08
pH	No information available
Viscosity (cps)	No information available
Solubility(ies)	No information available
Water solubility	No information available
Evaporation Rate	No information available
Vapor pressure	No information available
Vapor density	No information available

Wt. % Solids	55 - 65
Vol. % Solids	50 - 60
Wt. % Volatiles	35 - 45
Vol. % Volatiles	40 - 50
VOC Regulatory Limit (g/L)	< 225
VOC Content (% by weight)	< 0.5
Boiling Point (°F)	200
Boiling Point (°C)	93
Freezing point (°F)	No information available
Freezing Point (°C)	No information available
Flash point (°F)	375
Flash Point (°C)	191
Method	PMCC
Flammability (solid, gas)	Not applicable
Upper flammability limit:	Not applicable
Lower flammability limit:	Not applicable
Autoignition Temperature (°F)	No information available
Autoignition Temperature (°C)	No information available
Decomposition Temperature (°F)	No information available
Decomposition Temperature (°C)	No information available
Partition coefficient	No information available

10. STABILITY AND REACTIVITY

Reactivity	Not Applicable
Chemical Stability	Stable under normal conditions.
Conditions to avoid	Prevent from freezing.
Incompatible Materials	No materials to be especially mentioned.
Hazardous Decomposition Products	None under normal use.
Possibility of hazardous reactions	None under normal conditions of use.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Principal Routes of Exposure Eye contact, skin contact and inhalation.

Acute Toxicity

Product Information No information available

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Eye contact	Severely irritating to eyes. May cause burns. Risk of serious damage to eyes.
Skin contact	Substance may cause slight skin irritation. Prolonged or repeated contact may dry skin and cause irritation.
Inhalation	May cause irritation of respiratory tract.
Ingestion	Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.
Sensitization	May cause an allergic skin reaction
Neurological Effects	No information available.
Mutagenic Effects	No information available.
Reproductive Effects	No information available.
Developmental Effects	No information available.
Target organ effects	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Other adverse effects	No information available.
Aspiration Hazard	No information available

Numerical measures of toxicity

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral)	14010 mg/kg
ATEmix (inhalation-dust/mist)	150 mg/L
ATEmix (inhalation-vapor)	1100 mg/L

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Ethanol, 2-(2-butoxyethoxy)- 112-34-5	= 5660 mg/kg (Rat)	= 2700 mg/kg (Rabbit)	-
Sodium tripolyphosphate 7758-29-4	= 3120 mg/kg (Rat)	> 7940 mg/kg (Rabbit)	-
Ethanol, 2-amino- 141-43-5	= 1720 mg/kg (Rat)	= 1000 mg/kg (Rabbit) = 1 mL/kg (Rabbit)	-
3,5,7-Triaza-1-azoniatricyclo[3.3.1.1 3,7]decane, 1-(3-chloro-2-propen-1-yl)-, chloride 4080-31-3	= 500 mg/kg (Rat)	= 565 mg/kg (Rabbit)	-

Chronic Toxicity**Carcinogenicity**

There are no known carcinogenic chemicals in this product above reportable levels.

12. ECOLOGICAL INFORMATION

Ecotoxicity Effects

The environmental impact of this product has not been fully investigated.

Product Information**Acute Toxicity to Fish**

No information available

Acute Toxicity to Aquatic Invertebrates

No information available

Acute Toxicity to Aquatic Plants

No information available

Persistence / Degradability

No information available.

Bioaccumulation

No information available.

Mobility in Environmental Media

No information available.

Ozone

No information available

Component Information**Acute Toxicity to Fish**Ethanol, 2-amino-

LC50: 3684 mg/L (Zebra Fish - 96 hr.)

Acute Toxicity to Aquatic InvertebratesEthanol, 2-(2-butoxyethoxy)-

EC50: 100 mg/L (Daphnia - 48 hr.)

Ethanol, 2-amino-

EC50: 65 mg/L (Daphnia - 48 hr.)

Acute Toxicity to Aquatic PlantsEthanol, 2-amino-

EC50: 15 mg/L (Green algae (Scenedesmus subspicatus), 72 hrs.)

13. DISPOSAL CONSIDERATIONS**Waste Disposal Method**

Dispose of in accordance with federal, state, and local regulations. Local requirements may vary, consult your sanitation department or state-designated environmental protection agency for more disposal options.

14. TRANSPORT INFORMATION**DOT** Not regulated**ICAO / IATA** Not regulated**IMDG / IMO** Not regulated**15. REGULATORY INFORMATION**

International Inventories**TSCA: United States**

Yes - All components are listed or exempt.

DSL: Canada

No - Not all of the components are listed.

One or more component is listed on NDSL.

Federal Regulations**SARA 311/312 hazardous categorization**

Acute health hazard	Yes
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372:

<u>Chemical name</u>	<u>CAS No.</u>	<u>Weight-%</u>	<u>CERCLA/SARA 313 (de minimis concentration)</u>
Ethanol, 2-(2-butoxyethoxy)-	112-34-5	5 - 10	1.0
3,5,7-Triaza-1-azoniatricyclo[3.3.1.1 ^{3,7}]]decane, 1-(3-chloro-2-propen-1-yl)-, chloride	4080-31-3	0.5 - 1	1.0

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product contains the following HAPs:

<u>Chemical name</u>	<u>CAS No.</u>	<u>Weight-%</u>	<u>Hazardous Air Pollutant (HAP)</u>
Ethanol, 2-(2-butoxyethoxy)-	112-34-5	5 - 10	Listed

US State Regulations**California Proposition 65**

WARNING: Cancer and Reproductive Harm– www.P65warnings.ca.gov

State Right-to-Know

<u>Chemical name</u>	<u>Massachusetts</u>	<u>New Jersey</u>	<u>Pennsylvania</u>
Ethanol, 2-(2-butoxyethoxy)-		X	X
Sodium tripolyphosphate	X		X
3,5,7-Triaza-1-azoniatricyclo[3.3.1.1 ^{3,7}]]decane, 1-(3-chloro-2-propen-1-yl)-, chloride		X	

Legend

X - Listed

16. OTHER INFORMATION**HMIS - Health: 2 Flammability: 1 Reactivity: 0 PPE: -****HMIS Legend**

- 0 - Minimal Hazard
- 1 - Slight Hazard
- 2 - Moderate Hazard
- 3 - Serious Hazard
- 4 - Severe Hazard
- * - Chronic Hazard

X - Consult your supervisor or S.O.P. for "Special" handling instructions.

Note: The PPE rating has intentionally been left blank. Choose appropriate PPE that will protect employees from the hazards the material will present under the actual normal conditions of use.

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings are not required on MSDSs under 29 CFR 1910.1200, the preparer, has chosen to provide them. HMIS® ratings are to be used only in conjunction with a fully implemented HMIS® program by workers who have received appropriate HMIS® training. HMIS® is a registered trade and service mark of the NPCA. HMIS® materials may be purchased exclusively from J. J. Keller (800) 327-6868.

WARNING! If you scrape, sand, or remove old paint, you may release lead dust. LEAD IS TOXIC. EXPOSURE TO LEAD DUST CAN CAUSE SERIOUS ILLNESS, SUCH AS BRAIN DAMAGE, ESPECIALLY IN CHILDREN. PREGNANT WOMEN SHOULD ALSO AVOID EXPOSURE. Wear a NIOSH approved respirator to control lead exposure. Clean up carefully with a HEPA vacuum and a wet mop. Before you start, find out how to protect yourself and your family by contacting the National Lead Information Hotline at 1-800-424-LEAD or log on to www.epa.gov/lead.

Prepared By Product Stewardship Department
Benjamin Moore & Co.
101 Paragon Drive
Montvale, NJ 07645
800-225-5554

Revision Date: 24-Mar-2020
Revision Summary Not available

Disclaimer

The information contained herein is presented in good faith and believed to be accurate as of the effective date shown above. This information is furnished without warranty of any kind. Employers should use this information only as a supplement to other information gathered by them and must make independent determination of suitability and completeness of information from all sources to assure proper use of these materials and the safety and health of employees. Any use of this data and information must be determined by the user to be in accordance with applicable federal, provincial, and local laws and regulations.

End of Safety Data Sheet