


**STANDARD EXECUTIONS**

Butt-welded hub.

- **VCM-SST**: threaded blind hole, AISI 304 stainless steel, sandblasted matte finish.
- **VCM-SST-p**: threaded stud, AISI 304 stainless steel, sandblasted matte finish.



ELESA Original design



**VCM-SST**

Code	Description	D	d	L	d1	l2	hmin.	⚖
9169542	VCM-SST-40-5/16-18	1.57	5/16-18	0.94	0.55	0.47	0.59	0.08
9169547	VCM-SST-50-3/8-16	1.97	3/8-16	1.18	0.71	0.65	0.71	0.14
9169552	VCM-SST-60-1/2-13	2.36	1/2-13	1.48	0.79	0.79	0.87	0.24

**VCM-SST-p**

Code	Description	D	d	L	d1	l	l2	⚖
9169561	VCM-SST-40-p-5/16-18-079	1.57	5/16-18	0.94	0.55	0.79	0.47	0.11
9169562	VCM-SST-40-p-5/16-18-098	1.57	5/16-18	0.94	0.55	0.98	0.47	0.12
9169563	VCM-SST-40-p-5/16-18-157	1.57	5/16-18	0.94	0.55	1.57	0.47	0.12
9169571	VCM-SST-50-p-3/8-16-079	1.97	3/8-16	1.18	0.71	0.79	0.65	0.21
9169572	VCM-SST-50-p-3/8-16-098	1.97	3/8-16	1.18	0.71	0.98	0.65	0.21
9169573	VCM-SST-50-p-3/8-16-157	1.97	3/8-16	1.18	0.71	1.57	0.65	0.22
9169580	VCM-SST-60-p-1/2-13-079	2.36	1/2-13	1.48	0.79	0.79	0.79	0.33
9169581	VCM-SST-60-p-1/2-13-098	2.36	1/2-13	1.48	0.79	0.98	0.79	0.34
9169582	VCM-SST-60-p-1/2-13-157	2.36	1/2-13	1.48	0.79	1.57	0.79	0.36