

Lobe knobs



• **Material**

High resilience polypropylene based (PP) technopolymer. Resistant to solvents, oils, greases and other chemical agents.

• **Colour**

Black, matte finish.

• **Standard execution**

Brass boss, threaded pass-through hole.

Accessories on request

Coloured centre caps (see table).




Cap for	C9	C2	C3	C4	C5	C6	Description
VCT.32	6900	6903	6904	6905	6906	6901	CA.VCT.32-*
VCT.40	6910	6913	6914	6915	6916	6911	CA.VCT.40-*
VCT.50	6920	6923	6924	6925	6926	6921	CA.VCT.50-*
VCT.63-74-95	6930	6933	6934	6935	6936	6931	CA.VCT.63-74-95-*



* Complete with colour index, example: CA.VCT.40-C2

C9 RAL9005	C2 RAL2004	C3 RAL7035	C4 RAL1021	C5 RAL5024	C6 RAL3000
---------------	---------------	---------------	---------------	---------------	---------------



american unit
metric unit

Code	Description	D	d26	L	d1	d3	l2	h	
969848	VCT.32 FP-1/4-20	1.26 32	1/4-20	0.91 23	0.59 15	0.39 10	0.39 10	0.47 12	0.02 10
969897	VCT.40 FP-1/4-20	1.57 40	1/4-20	1.06 27	0.67 17	0.47 12	0.47 12	0.71 18	0.06 26
969898	VCT.40 FP-5/16-18	1.57 40	5/16-18	1.06 27	0.67 17	0.47 12	0.47 12	0.71 18	0.05 24
969956	VCT.50 FP-5/16-18	1.97 50	5/16-18	1.26 32	0.75 19	0.59 15	0.55 14	0.79 20	0.08 38
969957	VCT.50 FP-3/8-16	1.97 50	3/8-16	1.26 32	0.75 19	0.59 15	0.55 14	0.79 20	0.07 34
970016	VCT.63 FP-5/16-18	2.48 63	5/16-18	1.46 37	0.87 22	0.75 19	0.63 16	1.02 26	0.1 44
970017	VCT.63 FP-3/8-16	2.48 63	3/8-16	1.46 37	0.87 22	0.75 19	0.63 16	1.02 26	0.09 42
970018	VCT.63 FP-1/2-13	2.48 63	1/2-13	1.46 37	0.87 22	0.75 19	0.63 16	1.02 26	0.09 40
970067	VCT.74 FP-1/2-13	2.91 74	1/2-13	1.71 43.5	1.02 26	0.67 17	0.87 22	1.02 26	0.12 56