

WE MAKE THE CUT™



Kett Tool KD-400 18 Gauge Double Cut Shear

Features:

- 5.0 amp pistol grip, variable speed, 2500 rpm motor
- Replaceable A-2 tool steel shear blades
- Cuts cold-rolled mild steel up to 18 gauge, most grades of stainless steel to 20 gauge
- Cuts up to 300 inches per minute
- With the 7/32" waste strip, you get a clean, burr free cut
- Lightweight and easily maneuverable - can cut a 6" radius

Specifications:

Amps 5.0	Minimum Cutting Radius 6 inches
RPM 0 to 2,500	Cold-rolled Mild Steel 18 gauge
Power Source 120V	Stainless Steel 20 gauge
Shear Head 60-20 Aluminum	Length 14 inches
Cutting Speed 300 inches per minute	Weight 4 pounds
	Other Configurations 90 PSI Pneumatic

Kett Tool Company
5055 Madison Road
Cincinnati, OH 45227
(513) 271-0333

www.kett-tool.com
info@kett-tool.com

KETT
TOOL COMPANY

