

# WE MAKE THE CUT™



## Kett Tool KD-440 14 Gauge Double Cut Shear

### Features:

- 5.0 amp pistol grip, variable speed, 2500 rpm motor
- Replaceable A-2 tool steel shear blades
- Cuts cold-rolled mild steel up to 14 gauge, most grades of stainless steel up to 16 gauge
- Cuts up to 170 inches per minute
- With the 7/32" waste strip, you get a clean, burr free cut
- Lightweight and easily maneuverable - can cut a 7" radius

### Specifications:

<b>Amps</b> 5.0	<b>Minimum Cutting Radius</b> 7 inches
<b>RPM</b> 0 to 2,500	<b>Cold-rolled Mild Steel</b> 14 gauge
<b>Power Source</b> 120V	<b>Stainless Steel</b> 16 gauge
<b>Shear Head</b> 40-20 Steel	<b>Length</b> 14 inches
<b>Cutting Speed</b> 170 inches per minute	<b>Weight</b> 4 pounds
	<b>Other Configurations</b> 90 PSI Pneumatic

Kett Tool Company  
5055 Madison Road  
Cincinnati, OH 45227  
(513) 271-0333

[www.kett-tool.com](http://www.kett-tool.com)  
[info@kett-tool.com](mailto:info@kett-tool.com)

