

INSL-X[®]

SAFETY DATA SHEET

Revision Date: 18-Jan-2022

Revision Number: 1

1. PRODUCT AND COMPANY IDENTIFICATION

Product Name INSL-X MULTI-SURFACE WATERPROOFER CLEAR
Product Code WPS-1000
Alternate Product Code UA3700
Product Class Water thinned paint
Color Clear
Recommended use Surface coating
Restrictions on use No information available

Manufacturer
Benjamin Moore & Co.
101 Paragon Drive
Montvale, NJ 07645
Phone: 1-866-708-9180
www.insl-x.com

Emergency Telephone
CHEMTREC: +1 703-741-5970 / 1-800-424-9300
+1 703-527-3887 (outside US & Canada)

2. HAZARDS IDENTIFICATION

Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Serious eye damage/eye irritation	Category 2A
Skin sensitization	Category 1

Label elements

Warning

Hazard statements

Causes serious eye irritation
May cause an allergic skin reaction



Appearance liquid

Odor mild, ammonia-like

Precautionary Statements - Prevention

Wash face, hands and any exposed skin thoroughly after handling
Avoid breathing dust/fume/gas/mist/vapors/spray
Contaminated work clothing should not be allowed out of the workplace
Wear protective gloves/protective clothing/eye protection/face protection

Eyes

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.
Continue rinsing
If eye irritation persists: Get medical advice/attention

Skin

IF ON SKIN: Wash with plenty of soap and water
If skin irritation or rash occurs: Get medical advice/attention
Wash contaminated clothing before reuse

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not applicable

Other information

No information available

3. COMPOSITION INFORMATION ON COMPONENTS

Chemical name	CAS No.	Weight-%
Tridecanoylethoyle, branched	69011-36-5	0.5 - 1
Centrimonium chloride	112-02-7	0.1 - 0.5
3-aminopropyltriethoxy silane	919-30-2	0.1 - 0.5

4. FIRST AID MEASURES

General Advice	No hazards which require special first aid measures.
Eye Contact	Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.
Skin Contact	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes.
Inhalation	Move to fresh air. If symptoms persist, call a physician.
Ingestion	Clean mouth with water and afterwards drink plenty of water. Consult a physician if necessary.
Most Important Symptoms/Effects	None known.
Notes To Physician	Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Protective equipment and precautions for firefighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.
Specific Hazards Arising From The Chemical	Closed containers may rupture if exposed to fire or extreme heat.
Sensitivity to mechanical impact	No
Sensitivity to static discharge	No
Flash Point Data	
Flash point (°F)	Not applicable
Flash Point (°C)	Not applicable
Method	Not applicable
Flammability Limits In Air	
Lower flammability limit:	Not applicable
Upper flammability limit:	Not applicable

NFPA **Health:** 2 **Flammability:** 0 **Instability:** 0 **Special:** Not Applicable

NFPA Legend

0 - Not Hazardous
1 - Slightly
2 - Moderate
3 - High
4 - Severe

The ratings assigned are only suggested ratings, the contractor/employer has ultimate responsibilities for NFPA ratings where this system is used.

Additional information regarding the NFPA rating system is available from the National Fire Protection Agency (NFPA) at www.nfpa.org.

6. ACCIDENTAL RELEASE MEASURES

Personal Precautions	Avoid contact with skin, eyes and clothing. Ensure adequate ventilation.
Other Information	Prevent further leakage or spillage if safe to do so.
Environmental precautions	See Section 12 for additional Ecological Information.
Methods for Cleaning Up	Soak up with inert absorbent material. Sweep up and shovel into suitable containers for disposal.

7. HANDLING AND STORAGE

Handling	Avoid contact with skin, eyes and clothing. Avoid breathing vapors, spray mists or
-----------------	--

sanding dust. In case of insufficient ventilation, wear suitable respiratory equipment.

Storage Keep container tightly closed. Keep out of the reach of children.

Incompatible Materials No information available

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Limits

No exposure limits have been established for this product.

Legend

ACGIH - American Conference of Governmental Industrial Hygienists Exposure Limits

OSHA - Occupational Safety & Health Administration Exposure Limits

N/E - Not Established

Engineering Measures Ensure adequate ventilation, especially in confined areas.

Personal Protective Equipment

Eye/Face Protection Safety glasses with side-shields. If splashes are likely to occur, wear:. Tightly fitting safety goggles.

Skin Protection Protective gloves and impervious clothing.

Respiratory Protection In case of insufficient ventilation wear suitable respiratory equipment.

Hygiene Measures Avoid contact with skin, eyes and clothing. Remove and wash contaminated clothing before re-use. Wash thoroughly after handling.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	liquid
Odor	mild ammonia-like
Odor Threshold	No information available
Density (lbs/gal)	8.2 - 8.5
Specific Gravity	0.98 - 1.02
pH	No information available
Viscosity (cps)	No information available
Solubility(ies)	No information available
Water solubility	No information available
Evaporation Rate	No information available
Vapor pressure	No information available
Vapor density	No information available
Wt. % Solids	1 - 5
Vol. % Solids	1 - 5
Wt. % Volatiles	95 - 100
Vol. % Volatiles	95 - 100
VOC Regulatory Limit (g/L)	< 100
Boiling Point (°F)	212
Boiling Point (°C)	100
Freezing point (°F)	32

Freezing Point (°C)	0
Flash point (°F)	Not applicable
Flash Point (°C)	Not applicable
Method	Not applicable
Flammability (solid, gas)	Not applicable
Upper flammability limit:	Not applicable
Lower flammability limit:	Not applicable
Autoignition Temperature (°F)	No information available
Autoignition Temperature (°C)	No information available
Decomposition Temperature (°F)	No information available
Decomposition Temperature (°C)	No information available
Partition coefficient	No information available

10. STABILITY AND REACTIVITY

Reactivity	Not Applicable
Chemical Stability	Stable under normal conditions.
Conditions to avoid	Prevent from freezing.
Incompatible Materials	No materials to be especially mentioned.
Hazardous Decomposition Products	None under normal use.
Possibility of hazardous reactions	None under normal conditions of use.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Principal Routes of Exposure Eye contact, skin contact and inhalation.

Acute Toxicity

Product Information No information available

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Eye contact	Causes serious eye irritation.
Skin contact	Prolonged or repeated contact may dry skin and cause irritation. May cause sensitization by skin contact.
Inhalation	May cause irritation of respiratory tract.
Ingestion	Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.
Sensitization	May cause sensitization of susceptible persons
Neurological Effects	No information available.

Mutagenic Effects	No information available.
Reproductive Effects	No information available.
Developmental Effects	No information available.
Target organ effects	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Other adverse effects	No information available.
Aspiration Hazard	No information available

Numerical measures of toxicity

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral) 50000 mg/kg

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Tridecanoylethoyle, branched 69011-36-5	> 2000 mg/kg (Rat)	= 5960 mg/kg (Rabbit)	> 1.6 mg/L (Rat) 4 h
Centrimonium chloride 112-02-7	= 410 mg/kg (Rat)	= 4300 mg/kg (Rabbit)	-
3-aminopropyltriethoxy silane 919-30-2	= 1780 mg/kg (Rat)	= 4290 mg/kg (Rabbit) = 4 mL/kg (Rabbit)	> 7.35 mg/L (Rat) 4 h

Chronic Toxicity

Carcinogenicity

There are no known carcinogenic chemicals in this product above reportable levels.

12. ECOLOGICAL INFORMATION

Ecotoxicity Effects

The environmental impact of this product has not been fully investigated.

Product Information

Acute Toxicity to Fish

No information available

Acute Toxicity to Aquatic Invertebrates

No information available

Acute Toxicity to Aquatic Plants

No information available

Persistence / Degradability

No information available.

Bioaccumulation

No information available.

Mobility in Environmental Media

No information available.

Ozone

No information available

Component Information

Acute Toxicity to Fish

No information available

Acute Toxicity to Aquatic Invertebrates

No information available

Acute Toxicity to Aquatic Plants

No information available

13. DISPOSAL CONSIDERATIONS

Waste Disposal Method

Dispose of in accordance with federal, state, and local regulations. Local requirements may vary, consult your sanitation department or state-designated environmental protection agency for more disposal options.

14. TRANSPORT INFORMATION

DOT

Not regulated

ICAO / IATA

Not regulated

IMDG / IMO

Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA: United States

Yes - All components are listed or exempt.

DSL: Canada

Yes - All components are listed or exempt.

Federal Regulations

SARA 311/312 hazardous categorization

Acute health hazard	Yes
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product

contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372:

None

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product contains the following HAPs:

None

US State Regulations

California Proposition 65

 **WARNING:** This product can expose you to chemicals including Toluene, which are known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

State Right-to-Know

Chemical name	Massachusetts	New Jersey	Pennsylvania
Toluene	X	X	X

Legend

X - Listed

16. OTHER INFORMATION

HMIS - **Health:** 2 **Flammability:** 0 **Reactivity:** 0 **PPE:** -

HMIS Legend

- 0 - Minimal Hazard
- 1 - Slight Hazard
- 2 - Moderate Hazard
- 3 - Serious Hazard
- 4 - Severe Hazard
- * - Chronic Hazard

X - Consult your supervisor or S.O.P. for "Special" handling instructions.

Note: The PPE rating has intentionally been left blank. Choose appropriate PPE that will protect employees from the hazards the material will present under the actual normal conditions of use.

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings are not required on MSDSs under 29 CFR 1910.1200, the preparer, has chosen to provide them. HMIS® ratings are to be used only in conjunction with a fully implemented HMIS® program by workers who have received appropriate HMIS® training. HMIS® is a registered trade and service mark of the NPCA. HMIS® materials may be purchased exclusively from J. J. Keller (800) 327-6868.

WARNING! If you scrape, sand, or remove old paint, you may release lead dust. LEAD IS TOXIC. EXPOSURE TO LEAD DUST CAN CAUSE SERIOUS ILLNESS, SUCH AS BRAIN DAMAGE, ESPECIALLY IN CHILDREN. PREGNANT WOMEN SHOULD ALSO AVOID EXPOSURE. Wear a NIOSH approved respirator to control lead

exposure. Clean up carefully with a HEPA vacuum and a wet mop. Before you start, find out how to protect yourself and your family by contacting the National Lead Information Hotline at 1-800-424-LEAD or log on to www.epa.gov/lead.

Prepared By Product Stewardship Department
Benjamin Moore & Co.
101 Paragon Drive
Montvale, NJ 07645
800-225-5554

Revision Date: 18-Jan-2022
Revision Summary Not available

Disclaimer

The information contained herein is presented in good faith and believed to be accurate as of the effective date shown above. This information is furnished without warranty of any kind. Employers should use this information only as a supplement to other information gathered by them and must make independent determination of suitability and completeness of information from all sources to assure proper use of these materials and the safety and health of employees. Any use of this data and information must be determined by the user to be in accordance with applicable federal, provincial, and local laws and regulations.

End of Safety Data Sheet