

A00328 MST VOC ECONOMY SILICONE 16net10

Version 4.0

Revision Date 04/14/2017

Print Date 05/02/2017

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : A00328 MST VOC ECONOMY SILICONE 16net10

Material number : 00000000001033570

Manufacturer or supplier's details

Company : Zep Inc.

Address : 1310 Seaboard Industrial Blvd., NW
Atlanta, GA 30318

Telephone : 404-352-1680

Emergency telephone numbers**For SDS Information** : Compliance Services 1-877-428-9937**For a Medical Emergency** : 877-541-2016 Toll Free - All Calls Recorded**For a Transportation Emergency** : CHEMTREC: 800-424-9300 - All Calls Recorded.
In the District of Columbia 202-483-7616**Recommended use of the chemical and restrictions on use**

Recommended use : Lubricant

SECTION 2. HAZARDS IDENTIFICATION**Emergency Overview**

Appearance	Aerosol containing a liquefied gas
Colour	clear, colourless
Odour	characteristic

GHS ClassificationFlammable aerosols : Category 1
Gases under pressure : Liquefied gas
Aspiration hazard : Category 1**GHS label elements**

Hazard pictograms :



Signal word : Danger

Hazard statements : H222 Extremely flammable aerosol.
H280 Contains gas under pressure; may explode if heated.
H304 May be fatal if swallowed and enters airways.Precautionary statements : **Prevention:**
P210 Keep away from heat/sparks/open flames/hot surfaces.
No smoking.
P211 Do not spray on an open flame or other ignition source.
P251 Pressurized container: Do not pierce or burn, even after

A00328 MST VOC ECONOMY SILICONE 16net10

Version 4.0

Revision Date 04/14/2017

Print Date 05/02/2017

use.

Response:

P301 + P310 IF SWALLOWED: Immediately call a POISON CENTER/doctor.

Storage:

P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.

Disposal:

Dispose of contents/container in accordance with local regulation.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

Chemical name	CAS-No.	Concentration [%]
Distillates (petroleum), hydrotreated light	64742-47-8	>= 30 - < 50
propane	74-98-6	>= 30 - < 50
butane	106-97-8	>= 20 - < 30
Solvent naphtha (petroleum), heavy aliph.	64742-96-7	>= 1 - < 5

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

- General advice : Move out of dangerous area.
Show this safety data sheet to the doctor in attendance.
Symptoms of poisoning may appear several hours later.
Do not leave the victim unattended.
- If inhaled : If unconscious place in recovery position and seek medical advice.
If symptoms persist, call a physician.
- In case of skin contact : Wash off immediately with plenty of water for at least 15 minutes.
If on clothes, remove clothes.
If skin irritation persists, call a physician.
- In case of eye contact : If in eyes, rinse with water for 15 minutes.
Remove contact lenses.
Protect unharmed eye.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
- If swallowed : Keep respiratory tract clear.
DO NOT induce vomiting unless directed to do so by a physician or poison control center.
Never give anything by mouth to an unconscious person.
If symptoms persist, call a physician.
Take victim immediately to hospital.
- Most important symptoms and effects, both acute and : Aspiration may cause pulmonary oedema and pneumonitis.
Symptoms may include shortness of breath, dry cough, and

A00328 MST VOC ECONOMY SILICONE 16net10

Version 4.0

Revision Date 04/14/2017

Print Date 05/02/2017

SECTION 7. HANDLING AND STORAGE

- Advice on safe handling : Do not breathe vapours or spray mist.
 Avoid exposure - obtain special instructions before use.
 Avoid contact with skin and eyes.
 For personal protection see section 8.
 Smoking, eating and drinking should be prohibited in the application area.
 Dispose of rinse water in accordance with local and national regulations.
 Always replace cap after use.
 Provide sufficient air exchange and/or exhaust in work rooms.
 Take precautionary measures against static discharges.
- Conditions for safe storage : BEWARE: Aerosol is pressurized. Keep away from direct sun exposure and temperatures over 50 °C. Do not open by force or throw into fire even after use. Do not spray on flames or red-hot objects.
 Keep in a dry, cool and well-ventilated place.
 No smoking.
 Observe label precautions.
 Electrical installations / working materials must comply with the technological safety standards.
- Materials to avoid : Oxidizing agents

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION
Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Distillates (petroleum), hydrotreated light	64742-47-8	TWA	500 ppm 2,000 mg/m ³	OSHA Z-1
		TWA	400 ppm 1,600 mg/m ³	OSHA P0
		TWA (Mist)	5 mg/m ³	OSHA Z-1
		TWA (Mist)	5 mg/m ³	OSHA P0
		TWA (Mist)	5 mg/m ³	NIOSH REL
		ST (Mist)	10 mg/m ³	NIOSH REL
		PEL (particulate)	5 mg/m ³	CAL PEL
propane	74-98-6	TWA	1,000 ppm	ACGIH
		TWA	1,000 ppm 1,800 mg/m ³	NIOSH REL
		TWA	1,000 ppm 1,800 mg/m ³	OSHA Z-1
		TWA	1,000 ppm 1,800 mg/m ³	OSHA P0
		PEL	1,000 ppm	CAL PEL

A00328 MST VOC ECONOMY SILICONE 16net10

Version 4.0

Revision Date 04/14/2017

Print Date 05/02/2017

			1,800 mg/m3	
butane	106-97-8	TWA	800 ppm 1,900 mg/m3	NIOSH REL
		TWA	800 ppm 1,900 mg/m3	OSHA P0
		PEL	800 ppm 1,900 mg/m3	CAL PEL

Hazardous components without workplace control parameters

Engineering measures : effective ventilation in all processing areas

Personal protective equipment

Respiratory protection : Use respiratory protection unless adequate local exhaust ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.

Hand protection

Material
Remarks

: Protective gloves
: The suitability for a specific workplace should be discussed with the producers of the protective gloves.

Eye protection

: Ensure that eyewash stations and safety showers are close to the workstation location.
Safety glasses

Skin and body protection

: Impervious clothing
Choose body protection according to the amount and concentration of the dangerous substance at the work place.

Hygiene measures

: When using do not eat or drink.
When using do not smoke.
Wash hands before breaks and at the end of workday.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : Aerosol containing a liquefied gas

Colour : clear, colourless

Odour : characteristic

Odour Threshold : No data available

pH : Not applicable

Melting point/freezing point : Not applicable

Boiling point : Not applicable

Flash point :
No data available

Evaporation rate : < 1

Flammability (solid, gas) : Extremely flammable aerosol.

A00328 MST VOC ECONOMY SILICONE 16net10

Version 4.0

Revision Date 04/14/2017

Print Date 05/02/2017

Upper explosion limit	: No data available
Lower explosion limit	: No data available
Vapour pressure	: No data available
Relative vapour density	: No data available
Density	: 0.785 g/cm ³
Solubility(ies)	
Water solubility	: insoluble
Solubility in other solvents	: not determined
Partition coefficient: n-octanol/water	: No data available
Auto-ignition temperature	: not determined
Thermal decomposition	: No data available
Viscosity	
Viscosity, kinematic	: No data available
Heat of combustion	: 46.7 kJ/g

SECTION 10. STABILITY AND REACTIVITY

Reactivity	: Stable
Chemical stability	: Stable under normal conditions.
Possibility of hazardous reactions	: Vapours may form explosive mixture with air. No decomposition if stored and applied as directed.
Conditions to avoid	: Extremes of temperature and direct sunlight. Heat, flames and sparks.
Incompatible materials	: Oxidizing agents
Hazardous decomposition products	: Carbon oxides

SECTION 11. TOXICOLOGICAL INFORMATION**Potential Health Effects**

Aggravated Medical Condition	: None known.
Symptoms of Overexposure	: Aspiration may cause pulmonary oedema and pneumonitis. Symptoms may include shortness of breath, dry cough, and irritation of the nose, eyes, lips, mouth, and throat.

A00328 MST VOC ECONOMY SILICONE 16net10

Version 4.0

Revision Date 04/14/2017

Print Date 05/02/2017

Carcinogenicity:

IARC	No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
ACGIH	No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.
OSHA	No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Acute toxicity**Product:**

Acute oral toxicity	: Acute toxicity estimate : > 5,000 mg/kg Method: Calculation method
Acute dermal toxicity	: Acute toxicity estimate : > 5,000 mg/kg Method: Calculation method

Components:**Distillates (petroleum), hydrotreated light:**

Acute oral toxicity	: LD50 Rat: > 5,000 mg/kg
Acute inhalation toxicity	: LC50 Rat: > 4.6 mg/l Exposure time: 6 h
Acute dermal toxicity	: LD50 Rat: > 2,000 mg/kg

propane:

Acute inhalation toxicity	: LC50 Mouse: 1,237 mg/l Exposure time: 2 h
	LC50 Rat: 658 mg/l Exposure time: 4 h
	LC50 Rat: 1,355 mg/l

butane:

Acute inhalation toxicity	: LC50 Mouse: 1,237 mg/l Exposure time: 2 h
	LC50 Rat: 1,355 mg/l

Skin corrosion/irritation**Product:**

A00328 MST VOC ECONOMY SILICONE 16net10

Version 4.0

Revision Date 04/14/2017

Print Date 05/02/2017

Remarks: May cause skin irritation and/or dermatitis.

Serious eye damage/eye irritation

Product:

Remarks: May irritate eyes.

Respiratory or skin sensitisation

No data available

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

Distillates (petroleum), hydrotreated light:

propane:

butane:

Solvent naphtha (petroleum), heavy aliph.:

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

Product:

May be fatal if swallowed and enters airways.

Further information

Product:

Remarks: Solvents may degrease the skin.

Components:

Distillates (petroleum), hydrotreated light:

Remarks: No data available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

No data available

A00328 MST VOC ECONOMY SILICONE 16net10

Version 4.0

Revision Date 04/14/2017

Print Date 05/02/2017

Persistence and degradability

No data available

Bioaccumulative potential
Product:

Partition coefficient: n-octanol/water : Remarks: No data available

Components:
butane :

Partition coefficient: n-octanol/water : Pow: 2.89

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation 40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances

Remarks This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information : An environmental hazard cannot be excluded in the event of unprofessional handling or disposal., Harmful to aquatic life with long lasting effects.

Components:
Distillates (petroleum), hydrotreated light :

Additional ecological information : No data available

SECTION 13. DISPOSAL CONSIDERATIONS
Disposal methods

 Waste from residues : The product should not be allowed to enter drains, water courses or the soil.
Do not contaminate ponds, waterways or ditches with chemical or used container.
Dispose of in accordance with local regulations.

 Contaminated packaging : Empty remaining contents.
Dispose of as unused product.
Do not re-use empty containers.
Do not burn, or use a cutting torch on, the empty drum.

A00328 MST VOC ECONOMY SILICONE 16net10

Version 4.0

Revision Date 04/14/2017

Print Date 05/02/2017

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
ORM-D, CONSUMER COMMODITY

Transportation Regulation: IMDG (Vessel):
UN1950, AEROSOLS, FLAMMABLE, 2.1, - Limited quantity

Transportation Regulation: IATA (Cargo Air):
UN1950, AEROSOLS, FLAMMABLE, 2.1, - Limited quantity

Transportation Regulation: IATA (Passenger Air):
UN1950, AEROSOLS, FLAMMABLE, 2.1, - Limited quantity

Transportation Regulation: TDG (Canada):
UN1950, AEROSOLS, FLAMMABLE, 2.1, - Limited quantity

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

SECTION 15. REGULATORY INFORMATION

TSCA list : No substances are subject to a Significant New Use Rule.
No substances are subject to TSCA 12(b) export notification requirements.

EPCRA - Emergency Planning and Community Right-to-Know Act
CERCLA Reportable Quantity

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Sudden Release of Pressure Hazard
Acute Health Hazard
Fire Hazard

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop 65 This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

A00328 MST VOC ECONOMY SILICONE 16net10

Version 4.0

Revision Date 04/14/2017

Print Date 05/02/2017

The components of this product are reported in the following inventories:

TSCA On TSCA Inventory
DSL All components of this product are on the Canadian DSL

For information on the country notification status for other regions please contact the manufacturer's regulatory group.


Inventory Acronym and Validity Area Legend:

TSCA (USA), DSL (Canada), NDSL (Canada)

SECTION 16. OTHER INFORMATION

Further information

NFPA:



HMIS III:

HEALTH	3
FLAMMABILITY	4
PHYSICAL HAZARD	2

0 = not significant, 1 = Slight,
 2 = Moderate, 3 = High
 4 = Extreme, * = Chronic

OSHA - GHS Label Information:

Hazard pictograms :



Signal word :

Danger:

Hazard statements :

Extremely flammable aerosol. Contains gas under pressure; may explode if heated.
 May be fatal if sw allowed and enters airways.

Precautionary statements :

Prevention: Keep away from heat/sparks/open flames/hot surfaces. No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use.

Response: IF SWALLOWED: Immediately call a POISON CENTER/doctor.

Storage: Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.

Disposal: Dispose of contents/container in accordance with local regulation.

Version:	4.0
Revision Date:	04/14/2017
Print Date:	05/02/2017

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this

A00328 MST VOC ECONOMY SILICONE 16net10

Version 4.0

Revision Date 04/14/2017

Print Date 05/02/2017

document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®, Zep Professional®, Enforcer®, National Chemical™, Selig™, Misty®, Next Dimension™, Petro®, i-Chem®, TimeMist®, TimeWick™, MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National™, FC Forward Chemicals®, Rexodan®, Mykal™, and a number of private labeled brands.