Safety Data Sheet

Issue Date 20-Sep-2018	Revision/Review Date: 20-Sep-2018	Version
	1. IDENTIFICATION	
<u>Product Identifier</u> Product Name	Boardwalk Industrial Strength Carpet Spotter	
<u>Other Means of Identification</u> Product Code	BWK4821	
Recommended Use of the Chemic Recommended Use	cal and Restrictions on Use All-purpose stain and spot remover. For industrial use	
Details of the Supplier of the Safe Manufactured for Boardwalk®/ Essendant Co. One Parkway North Deerfield, IL 60015	<u>etv Data Sheet</u>	
<u>Emergency Telephone Number</u> Company Phone Number Emergency Telephone (24 hr)	Phone: 1-844-828-5617 INFOTRAC 1-352-323-3500 (International) 1-800-535-5053 (North America)	
	2. HAZARDS IDENTIFICATION	
Appearance Blue	Physical State Liquid	Odor None
<u>Classification</u>		
Serious Eye Damage/Eye Irritation	Ca	tegory 2 Sub-category B
ignal Word Varning		
lazard Statements Causes eye irritation.		
recautionary Statements - Preven /ash face, hands and any exposed s		
recautionary Statements - Respon IN EYES: Rinse cautiously with wa eye irritation persists: Get medical a	ter for several minutes. Remove contact lenses, if present	t and easy to do. Continue rinsing.
recautionary Statements - Storag		
recautionary Statements - Dispos ispose of contents/container to an a		
ther Hazards one known.		
nknown Acute Toxicity		

Unknown Acute Toxicity

None known.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%
Water	7732-18-5	60-100

Boardwalk Industrial Strength Carpet Spotter		evision/Review Date: 20-Sep-2018
Diethylene Glycol Monomethyl Ether	111-77-3	1-5
Poly(Oxyethylene/Oxypropylene) Glycol Copolymer (Polyoxyalkylene Glycol Polyether Polyol)	9003-11-6	1-5
Sodium Thiosulfate	10102-17-7	1-5

If Chemical Name/CAS No is "proprietary" and/or Weight-% is listed as a range, the specific chemical identity and/or percentage of composition has been withheld as a trade secret.

	4. FIRST-AID MEASURES
First Aid Measures	
Eye Contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If irritation develops or persists seek medical attention.
Skin Contact	Wash off immediately with plenty of water for at least 15 minutes.
Inhalation	Remove to fresh air.
Ingestion	Clean mouth with water and drink afterwards plenty of water. If any discomfort persists, obtain medical attention.
Most Important Symptoms and Ef	fects
Symptoms	Contact with eyes may cause irritation and redness.
Indication of Any Immediate Medic	cal Attention and Special Treatment Needed
Notes to Physician	Treat symptomatically.
	5. FIRE-FIGHTING MEASURES
Suitable Extinguishing Media Water spray (fog). Carbon dioxide (C	CO2). Water. Foam.
<u>Unsuitable Extinguishing Media</u> Not determined.	
Specific Hazards Arising from the None known.	Chemical
Hazardous Combustion Products Normal products of combustion.	
Protective Equipment and Precau As in any fire, wear self-contained be protective gear.	tions for Firefighters reathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full
	6. ACCIDENTAL RELEASE MEASURES
Personal Precautions, Protective	Equipment and Emergency Procedures
Personal Precautions	Wear protective clothing as described in Section 8 of this safety data sheet.
Environmental Precautions	Prevent from entering into soil, ditches, sewers, waterways and/or groundwater. See Section 12, Ecological Information. See Section 13, Disposal Considerations, for additional information. See Section 12 for additional Ecological Information.
Methods and Material for Contain	ment and Cleaning Up

Methods for Containment	Prevent from spreading or entering drains, ditches or rivers by using sand, earth, or other
	appropriate barriers.

Revision/Review Date: 20-Sep-2018

Contain and collect with an inert absorbent and place into an appropriate container for disposal. Rinse area with clean water and dry before permitting traffic.

7. HANDLING AND STORAGE

Precautions for Safe Handling

Advice on Safe Handling	Handle in accordance with good industrial hygiene and safety practice. Use personal protection recommended in Section 8. For industrial and commercial use only. Avoid contact with skin, eyes or clothing.
Conditions for Safe Storage. Inc	uding Any Incompatibilities
Storage Conditions	Keep container tightly closed and store in a cool, dry and well-ventilated place. Protect from freezing. Keep out of the reach of children.
Incompatible Materials	None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
None known			

Appropriate Engineering Controls

Solubility in other solvents

Engineering Controls Ensure adequate ventilation, especially in confined areas. Good general room ventilation (equivalent to outdoors) should be adequate under normal conditions. Eyewash stations. Showers.

Individual Protection Measures, such as Personal Protective Equipment

Eye/Face Protection Eye protection should be used when splashing may occur.

Skin and Body Protection Wear protective gloves when handling this product.

Respiratory Protection Under normal conditions, respirator is not normally required.

General Hygiene Considerations Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on Basic Physical and Chemical Properties

Physical State Appearance Color	Liquid Clear Blue		Odor Odor Threshold	No added fragrance Not determined
Property pH (concentrate) Melting Point/Freezing Point Boiling Point/Boiling Range Flash Point Evaporation Rate Flammability (Solid, Gas) Upper Flammability Limits Lower Flammability Limit Vapor Pressure Vapor Density Specific Gravity Water Solubility		Values 9.4-9.9 Approximately 32°F Approximately 212°F Not applicable Not determined Liquid-not applicable Not applicable Not applicable Not applicable Not determined Not determined 1.01 Completely soluble	<u>Remark</u>	s ∙ Method _

Not determined

Not determined Not determined Not determined Not determined Not an explosive Not determined

10. STABILITY AND REACTIVITY

Reactivity

Not reactive under normal conditions.

Chemical Stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to Avoid

Keep out of reach of children. Avoid excessive heat, sparks, or open flames. Keep from freezing.

Incompatible Materials

Strong oxidizing agents, acids, and alkalis.

Hazardous Decomposition Products

Thermal decomposition may produce oxides of carbon, sodium, and hydrogen sulfide.

11. TOXICOLOGICAL INFORMATION

Information on Likely Routes of Exposure

Product Information

Eye Contact	Avoid contact with eyes.
Skin Contact	Avoid contact with skin.
Inhalation	Avoid breathing vapors or mists.
Ingestion	Do not taste or swallow.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Diethylene Glycol Monomethyl Ether 111-77-3	5500mg/kg (Rat)	650mg/kg (Rabbit)	-
Poly(Oxyethylene/Oxypropylene) Glycol Copolymer (Polyoxyalkylene Glycol Polyether Polyol) 9003-11-6	>2000mg/kg (Rat)	-	-
Sodium Thiosulfate 10102-17-7	2700 mg/kg (Mouse)	-	-

Information on Physical. Chemical and Toxicological Effects

Symptoms

Please see section 4 of this SDS for symptoms.

Delayed and Immediate Effects as well as Chronic Effects from Short and Long-Term Exposure

Carcinogenicity

This product does not contain any carcinogens or potential carcinogens as listed by OSHA, IARC or NTP.

Numerical Measures of Toxicity

Not determined

12. ECOLOGICAL INFORMATION

Ecotoxicity

The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Component Information

Chemical Name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Diethylene Glycol Monomethyl Ether 111-77-3	-	-	-	-
Poly(Oxyethylene/Oxypropylene) Glycol Copolymer (Polyoxyalkylene Glycol Polyether Polyol) 9003-11-6	>100mg/L (72hr)	>100mg/L (96hr)	-	>100mg/L (48hr)
Sodium Thiosulfate 10102-17-7	-	-	-	-

Persistence/Degradability

Not expected to persist.

Bioaccumulation

Not expected to bioaccumulate.

<u>Mobility</u>

Not determined

Other Adverse Effects

Not determined

	13. DISPOSAL CONSIDERATIONS
Waste Treatment Methods	
Disposal of Wastes	Disposal should be in accordance with applicable regional, national and local laws and regulations.
Contaminated Packaging	Disposal should be in accordance with applicable regional, national and local laws and regulations.
	14. TRANSPORT INFORMATION
Note	Please see current shipping paper for most up to date shipping information, including exemptions and special circumstances.
DOT	Not regulated. (NOI Non-Hazardous)
IATA	Not regulated.
IMDG	Not regulated.

15. REGULATORY INFORMATION

International Inventories

Canada – Domestic Substances List (DSL) TSCA (Toxic Substances Control Act) All ingredients are listed or exempt. All ingredients are listed or exempt.

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

CERCLA None Listed

SARA 311/312 Hazard Categories

Immediate (Acute) Health.

<u>SARA 313</u>

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains the following chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372:

Diethylene Glycol Monomethyl Ether: 2%

CWA (Clean Water Act)

None known.

US State Regulations

None known

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

The following ingredients appear on various state right to know lists and/or California's Proposition 65 List:

Chemical Name	State List
Diethylene Glycol Monomethyl Ether 111-77-3	MA, PA

AZ- Arizona Ambient Air Quality Guidelines	IL- Illinois Toxic Air Contaminate- Carcinogenic		
CT- Connecticut Hazardous Air Pollutants	MA- Massachusetts Right to Know List		
CA- California Director's List of Hazardous Substances	MN- Minnesota Hazardous Substances List		
CAP65- California Prop65	NJ- New Jersey Right to Know List		
FL- Florida Substances List	PA- Pennsylvania Right to Know List		
ID- Idaho Non-Carcinogen Toxic Air Pollutants	RI- Rhode Island Hazardous Substances List		

16. OTHER INFORMATION

<u>NFPA</u> <u>HMIS</u>	Health Hazards Not determined Health Hazards 1	Flammability Not determined Flammability 0	Instability Not determined Physical Hazards 0	Special Hazards Not determined Personal Protection Not determined
Issue Date Revision/Review Date: Revision Note	20-Sep-2018 20-Sep-2018 Version 1.0			

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

Keep Out of Reach of Children. For Industrial and Institutional Use Only.

*Denotes changes from last version.

End of Safety Data Sheet