

CRYSTAL LIGHT ON THE GO POWDERED SOFT DRINK

Dot #:

423810

Mfr #:

10043000007973

GTIN:

10043000007973

Supplier:

Kraft US (0044710044602)

Description:

CRYSTAL LIGHT ON THE GO POWDERED SOFT DRINK

Images and Attachments

Product Information

Classification:

Drinks Flavoured - Not Ready to Drink (10000202)

Dimensions (HxWxD):

6.12 x 6 x 8.75 Inch

Weight Gross / Net:

1.62 Pound / 0.68 Pound

Origin:

(US) UNITED STATES

Storage Temperature:

-50° to 150°

Pallet Configuration:

Ti: Hi:

Servings Per Container:

75

Features and Benefits (Case GTIN: 10043000007973)**Features:**

Increase variety of health & wellness oriented beverages within a small footprint and without taking up additional cooler space. The Crystal Light brand is widely recognized by consumers and is the #1 selling noncarbonated sugar-free fruit drink mix. On The Go products can be merchandised to promote sale of high margin bottled water or as an up-sell to offset cost of patron request for free cup of water.

Preparation and Cooking:

Reconstitute - Tear open stick packet, pour into 20 oz. water (bottle or cup), shake or stir to mix. Can be mixed in 16.9 oz. of water for a slightly stronger flavor.

Serving Suggestions:

blank

Storage:

BOX/CARTON Corrugated or Solid Ambient Prevailing Conditions

Features and Benefits (Inner GTIN: 00043000023419)**Storage:**

BOX/CARTON Fiber Ambient Prevailing Conditions

Features and Benefits (Consumer or Base GTIN: 00043000007976)**Storage:**

WRAPPER Plastic Ambient Prevailing Conditions

Nutritionals and Ingredients (Case GTIN: 10043000007973)

Representation of label(s). The actual nutritional label(s) on the package may vary slightly

Nutrition Facts (Unprepared)			
Serving Size	1.1 g		
Servings Per Container	75		
Amount Per Serving			
Calories	5.0	Calories from fat	0.0
		% Daily Value*	
Saturated Fat	0.0 g		0.0%
Trans Fat	0.0 g		
Cholesterol	0.0 mg		0.0%
Sodium	0.0 mg		0.0%
Potassium	20.0 mg		1.0%
Total Carbohydrate	0.0 g		0.0%
Dietary Fiber	0.0 g		0.0%
Sugar	0.0 g		
Protein	0.0 g		
Calcium			0.0%
Iron			0.0%
Phosphorous			0.0%
(-) Information is currently not available for this nutrient.			
* Percent Daily Values are based on a 2,000 calorie diet.			
Your daily values may be higher or lower depending on your calorie needs:**			
** Percent Daily Values listed below are intended for adults and children over 4 years of age. Foods represented or purported to be for use by infants, children less than 4 years of age, pregnant women, or lactating women shall use the RDI's that are specified for the intended group provided by the FDA.			
	Calories:	2,000	2,500
Total Fat	Less than	65g	80g
Sat. Fat	Less than	20g	25g
Cholesterol	Less than	300mg	300mg
Sodium	Less than	2400mg	2400mg
Potassium		3500mg	3500mg
Total Carbohydrates		300mg	3500mg
Dietary Fiber		25mg	30mg
Calories per gram:			
	Fat 9	Carbohydrate 4	Protein 4

Ingredients: INGREDIENTS: CITRIC ACID, INSTANT TEA, CORN SYRUP SOLIDS*, ASPARTAME**, MALTODEXTRIN, CONTAINS LESS THAN 2% OF NATURAL AND ARTIFICIAL FLAVOR, MAGNESIUM OXIDE, ACESULFAME POTASSIUM, RED 40, YELLOW 5, BLUE 1, SODIUM

BENZOATE (PRESERVES FRESHNESS).* ADDS A TRIVIAL AMOUNT OF SUGAR** PHENYLKETONURICS: CONTAINS PHENYLALANINE

Nutritionals and Ingredients (Inner GTIN: 00043000023419)

Representation of label(s). The actual nutritional label(s) on the package may vary slightly

Nutrition Facts (Unprepared)			
Serving Size	1.1 g		
Servings Per Container	75		
Amount Per Serving			
Calories	5.0	Calories from fat	0.0
		% Daily Value*	
Saturated Fat	0.0 g		0.0%
Trans Fat	0.0 g		
Cholesterol	0.0 mg		0.0%
Sodium	0.0 mg		0.0%
Potassium	20.0 mg		1.0%
Total Carbohydrate	0.0 g		0.0%
Dietary Fiber	0.0 g		0.0%
Sugar	0.0 g		
Protein	0.0 g		
Calcium			0.0%
Iron			0.0%
Phosphorous			0.0%
(-) Information is currently not available for this nutrient.			
* Percent Daily Values are based on a 2,000 calorie diet. Your daily values may be higher or lower depending on your calorie needs:**			
** Percent Daily Values listed below are intended for adults and children over 4 years of age. Foods represented or purported to be for use by infants, children less than 4 years of age, pregnant women, or lactating women shall use the RDI's that are specified for the intended group provided by the FDA.			
	Calories:	2,000	2,500
Total Fat	Less than	65g	80g
Sat. Fat	Less than	20g	25g
Cholesterol	Less than	300mg	300mg
Sodium	Less than	2400mg	2400mg
Potassium		3500mg	3500mg
Total Carbohydrates		300mg	3500mg
Dietary Fiber		25mg	30mg
Calories per gram:			
	Fat 9	Carbohydrate 4	Protein 4

Ingredients: INGREDIENTS: CITRIC ACID, INSTANT TEA, CORN SYRUP SOLIDS*, ASPARTAME**, MALTODEXTRIN, CONTAINS LESS THAN 2% OF NATURAL AND ARTIFICIAL FLAVOR, MAGNESIUM OXIDE, ACESULFAME POTASSIUM, RED 40, YELLOW 5, BLUE 1, SODIUM BENZOATE (PRESERVES FRESHNESS). * ADDS A TRIVIAL AMOUNT OF SUGAR** PHENYLKETONURICS: CONTAINS PHENYLALANINE

Nutritionals and Ingredients (Consumer or Base GTIN: 00043000007976)

Representation of label(s). The actual nutritional label(s) on the package may vary slightly

Nutrition Facts (Unprepared)			
Serving Size 1.1 g			
Amount Per Serving			
Calories	5.0	Calories from fat	0.0
		% Daily Value*	
Saturated Fat	0.0 g		0.0%
Trans Fat	0.0 g		
Cholesterol	0.0 mg		0.0%
Sodium	0.0 mg		0.0%
Potassium	20.0 mg		1.0%
Total Carbohydrate	0.0 g		0.0%
Dietary Fiber	0.0 g		0.0%
Sugar	0.0 g		
Protein	0.0 g		
Calcium			0.0%
Iron			0.0%
Phosphorous		0.0%	
(-) Information is currently not available for this nutrient.			
* Percent Daily Values are based on a 2,000 calorie diet. Your daily values may be higher or lower depending on your calorie needs:**			
** Percent Daily Values listed below are intended for adults and children over 4 years of age. Foods represented or purported to be for use by infants, children less than 4 years of age, pregnant women, or lactating women shall use the RDI's that are specified for the intended group provided by the FDA.			
	Calories:	2,000	2,500
Total Fat	Less than	65g	80g
Sat. Fat	Less than	20g	25g
Cholesterol	Less than	300mg	300mg
Sodium	Less than	2400mg	2400mg
Potassium		3500mg	3500mg
Total Carbohydrates		300mg	3500mg
Dietary Fiber		25mg	30mg

Calories per gram:		
Fat 9	Carbohydrate 4	Protein 4

Ingredients: INGREDIENTS: CITRIC ACID, INSTANT TEA, CORN SYRUP SOLIDS*, ASPARTAME**, MALTODEXTRIN, CONTAINS LESS THAN 2% OF NATURAL AND ARTIFICIAL FLAVOR, MAGNESIUM OXIDE, ACESULFAME POTASSIUM, RED 40, YELLOW 5, BLUE 1, SODIUM BENZOATE (PRESERVES FRESHNESS).* ADDS A TRIVIAL AMOUNT OF SUGAR** PHENYLKETONURICS: CONTAINS PHENYLALANINE

Allergens and Diet (Case GTIN: 1004300007973)

Allergen Information Not Available

Suitable For Diet
 Kosher Yes
 Organic Not Organic

Allergens and Diet (Inner GTIN: 00043000023419)

Allergen Information Not Available

Suitable For Diet
 Kosher Yes
 Organic Not Organic

Allergens and Diet (Consumer or Base GTIN: 0004300007976)

Allergen Information Not Available

Suitable For Diet
 Kosher Yes
 Organic Not Organic

Powered by [Sync/PDI](#)

This communication is intended for the use of the addressee only and may contain information that is privileged or confidential. If you are not the addressee, you are hereby notified that any dissemination, distribution or use of this communication is prohibited. If you received this communication in error, please destroy it, all copies and any attachments and notify the sender as soon as possible. Any comments, statements or opinions expressed in this communication do not necessarily reflect those of Kraft Heinz Company, its subsidiaries and affiliates.

Ce message est uniquement destiné au destinataire et pourrait contenir des renseignements privilégiés ou confidentiels. Si vous n'êtes pas le destinataire prévu, sachez que toute diffusion, distribution ou utilisation de ce message est interdite. Si vous avez reçu ce message par erreur, nous vous prions d'en aviser l'expéditeur dès que possible et de détruire le message, ainsi que toute copie ou pièce jointe, le cas échéant. Tout commentaire, énoncé ou opinion exprimés dans ce message ne reflètent pas nécessairement ceux de la Kraft Heinz Company, ni de ses filiales ou sociétés affiliées.

