

SAFETY DATA SHEET

Issuing Date 08-Jun-2015

Revision Date 05-Jun-2015

Revision Number 4



The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publically available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is © 2014 UL LLC. All rights reserved.

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Name Li-ion Polymer Battery 502030

Other means of identification

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use LITHIUM ION BATTERIES

Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier Name SHENZHEN FUERXIN TECHNOLOGY CO.,LTD

Supplier Address 5/F, 1st Building, No.264, Baoshi East Road, Shuitian Community, Shuitian Town, Bao'an District, Shenzhen, Guangdong, China
Shenzhen
Guangdong
518108
CN

Supplier Phone Number Phone:+86-0755-29452478

Supplier Email wenjun.li@wsct-cert.org

Emergency telephone number

Company Emergency Phone Number +86-18682462178

2. HAZARDS IDENTIFICATION

Classification

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200). This product is an article which is a sealed battery and as such does not require an MSDS per the OSHA hazard communication standard unless ruptured. The hazards indicated are for a ruptured battery.

Acute toxicity - Dermal	Category 4
Skin corrosion/irritation	Category 1 Sub-category B



Serious eye damage/eye irritation	Category 1
Carcinogenicity	Category 2
Specific target organ toxicity (repeated exposure)	Category 1

GHS Label elements, including precautionary statements**Emergency Overview**

Signal word	Danger	
Hazard Statements Harmful in contact with skin Causes severe skin burns and eye damage Suspected of causing cancer		
		
<p>This product is an article which contains a chemical substance. Safety information is given for exposure to the article as sold. Intended use of the product should not result in exposure to the chemical substance. This is a battery. In case of rupture: the above hazards exist.</p>		
Appearance Silver	Physical state Solid containing liquid Solid	Odor No information available

Precautionary Statements - Prevention

Obtain special instructions before use
 Do not handle until all safety precautions have been read and understood
 Use personal protective equipment as required
 Do not breathe dust/fume/gas/mist/vapors/spray
 Wash face, hands and any exposed skin thoroughly after handling
 Do not eat, drink or smoke when using this product

Precautionary Statements - Response

Specific treatment (see .? on this label)
 Immediately call a POISON CENTER or doctor/physician
 Specific treatment (see supplemental first aid instructions on this label)

Eyes

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 Immediately call a POISON CENTER or doctor/physician

Skin

Call a POISON CENTER or doctor/physician if you feel unwell
 Wash contaminated clothing before reuse
 IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower

Inhalation

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
 Immediately call a POISON CENTER or doctor/physician

Ingestion

IF SWALLOWED: Rinse mouth. DO NOT induce vomiting

Precautionary Statements - Storage

Store locked up

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not applicable

Unknown Toxicity

28 % of the mixture consists of ingredient(s) of unknown toxicity

Other information

May be harmful if swallowed

Very toxic to aquatic life with long lasting effects

Interactions with Other Chemicals

No information available.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical name	CAS No	Weight-%	Trade Secret
Supplier Trade Secret	Trade Secret	15 - 40	*
Supplier Trade Secret	Trade Secret	10 - 30	*
Supplier Trade Secret	Trade Secret	5 - 10	*
Supplier Trade Secret	Trade Secret	3 - 7	*

*The exact percentage (concentration) of composition has been withheld as a trade secret

4. FIRST AID MEASURES**First aid measures****General Advice**

First aid is upon rupture of sealed battery.

Eye contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Do not rub affected area. Remove contact lenses, if present and easy to do. Continue rinsing. Seek immediate medical attention/advice.

Skin contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Seek immediate medical attention/advice.

Inhalation

Remove to fresh air. If breathing has stopped, give artificial respiration. Get medical attention immediately. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. If breathing is difficult, (trained personnel should) give oxygen. Delayed pulmonary edema may occur. Get medical attention immediately if symptoms occur.

Ingestion

Do NOT induce vomiting. Rinse mouth immediately and drink plenty of water. Never give anything by mouth to an unconscious person. Call a physician or poison control center immediately.



Self-protection of the first aider Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination. Avoid contact with skin, eyes or clothing. Avoid direct contact with skin. Use barrier to give mouth-to-mouth resuscitation. Use personal protective equipment as required. Wear personal protective clothing (see section 8).

Most important symptoms and effects, both acute and delayed

Most Important Symptoms and Effects Coughing and/ or wheezing. Itching. Burning sensation.

Indication of any immediate medical attention and special treatment needed

Notes to Physician Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated. Do not give chemical antidotes. Asphyxia from glottal edema may occur. Marked decrease in blood pressure may occur with moist rales, frothy sputum, and high pulse pressure.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

CAUTION: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

The product causes burns of eyes, skin and mucous membranes. Thermal decomposition can lead to release of irritating gases and vapors.

Hazardous Combustion Products

Carbon oxides.

Explosion Data

Sensitivity to Mechanical Impact No.

Sensitivity to Static Discharge No.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions	Attention! Corrosive material. Avoid contact with skin, eyes or clothing. Ensure adequate ventilation. Use personal protective equipment as required. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak.
Other Information	Refer to protective measures listed in Sections 7 and 8.

Environmental precautions

Environmental precautions	Refer to protective measures listed in Sections 7 and 8. Prevent further leakage or spillage if safe to do so. Should not be released into the environment. Do not allow to enter into soil/subsoil. Prevent product from entering drains.
----------------------------------	--

Methods and material for containment and cleaning up

Methods for containment	Prevent further leakage or spillage if safe to do so.
Methods for cleaning up	Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Handling	In case of rupture: Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Use personal protection equipment.
-----------------	--

Conditions for safe storage, including any incompatibilities

Storage	Keep containers tightly closed in a dry, cool and well-ventilated place. Protect from moisture. Store locked up. Keep out of the reach of children. Store away from other materials.
Incompatible Products	Acids. Bases. Oxidizing agent.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Supplier Trade Secret	TWA: 0.02 mg/m ³	-	
Supplier Trade Secret	TWA: 2.5 mg/m ³ F	TWA: 2.5 mg/m ³ F TWA: 2.5 mg/m ³ dust (vacated) TWA: 2.5 mg/m ³	
Supplier Trade Secret	TWA: 0.2 mg/m ³ fume TWA: 1 mg/m ³ Cu dust and mist	TWA: 0.1 mg/m ³ fume TWA: 1 mg/m ³ dust and mist (vacated) TWA: 0.1 mg/m ³ Cu dust, fume, mist	IDLH: 100 mg/m ³ dust, fume and mist TWA: 1 mg/m ³ dust and mist TWA: 0.1 mg/m ³ fume

Supplier Trade Secret	TWA: 1 mg/m ³ respirable fraction	TWA: 15 mg/m ³ total dust TWA: 5 mg/m ³ respirable fraction (vacated) TWA: 15 mg/m ³ total dust (vacated) TWA: 5 mg/m ³ respirable fraction (vacated) TWA: 5 mg/m ³ Al Aluminum	TWA: 10 mg/m ³ total dust TWA: 5 mg/m ³ respirable dust
-----------------------	--	--	--

ACGIH TLV: American Conference of Governmental Industrial Hygienists - Threshold Limit Value OSHA PEL: Occupational Safety and Health Administration - Permissible Exposure Limits Immediately Dangerous to Life or Health

Other Exposure Guidelines Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992) See section 15 for national exposure control parameters

Appropriate engineering controls

Engineering Measures Showers
Eyewash stations
Ventilation systems

Individual protection measures, such as personal protective equipment

Eye/face protection None required for consumer use. If there is a risk of contact.. Face protection shield.

Skin and body protection None required for consumer use. If there is a risk of contact.. Wear protective gloves and protective clothing. Long sleeved clothing. Chemical resistant apron. Impervious gloves.

Respiratory protection No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Wear suitable gloves and eye/face protection. Do not eat, drink or smoke when using this product. Take off contaminated clothing and wash before reuse. Contaminated work clothing should not be allowed out of the workplace. Regular cleaning of equipment, work area and clothing is recommended. Wash hands before breaks and immediately after handling the product. For environmental protection, remove and wash all contaminated protective equipment before re-use.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties

Physical state	Solid containing liquid, Solid	Odor	No information available
Appearance	Silver	Odor Threshold	No information available
Color	No information available		

<u>Property</u>	<u>Values</u>	<u>Remarks Method</u>
pH	No data available	None known
Melting / freezing point	No data available	None known
Boiling point / boiling range	No data available	None known
Flash Point	No data available	None known
Evaporation Rate	No data available	None known
Flammability (solid, gas)	No data available	None known
Flammability Limit in Air		
Upper flammability limit	No data available	
Lower flammability limit	No data available	
Vapor pressure	No data available	None known
Vapor density	No data available	None known
Specific Gravity	No data available	None known
Water Solubility	Immiscible in water	None known



Solubility in other solvents	No data available	None known
Partition coefficient: n-octanol/water	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature	No data available	None known
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	None known
Explosive properties	No data available	
Oxidizing properties	No data available	

Other Information

Softening Point	No data available
VOC Content (%)	No data available
Particle Size	No data available
Particle Size Distribution	

10. STABILITY AND REACTIVITY

Reactivity

No data available.

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to avoid

Exposure to air or moisture over prolonged periods.

Incompatible materials

Acids. Bases. Oxidizing agent.

Hazardous Decomposition Products

Carbon oxides.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure**Product Information**

Product does not present an acute toxicity hazard based on known or supplied information. In case of rupture:.

Inhalation

Specific test data for the substance or mixture is not available. Corrosive by inhalation. (based on components). Inhalation of corrosive fumes/gases may cause coughing, choking, headache, dizziness, and weakness for several hours. Pulmonary edema may occur with tightness in the chest, shortness of breath, bluish skin, decreased blood pressure, and increased heart rate. Inhaled corrosive substances can lead to a toxic edema of the lungs. Pulmonary edema can be fatal. May cause irritation of respiratory tract.

Eye contact

Specific test data for the substance or mixture is not available. Causes burns. (based on components). Corrosive to the eyes and may cause severe damage including blindness. Causes serious eye damage. May cause irreversible damage to eyes.

Skin contact

Specific test data for the substance or mixture is not available. Corrosive. (based on components). Causes burns. May be absorbed through the skin in harmful amounts. Harmful in contact with skin.

Ingestion

Specific test data for the substance or mixture is not available. Causes burns. (based on

components). Ingestion causes burns of the upper digestive and respiratory tracts. May cause severe burning pain in the mouth and stomach with vomiting and diarrhea of dark blood. Blood pressure may decrease. Brownish or yellowish stains may be seen around the mouth. Swelling of the throat may cause shortness of breath and choking. May cause lung damage if swallowed. May be fatal if swallowed and enters airways. Ingestion may cause irritation to mucous membranes. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.

Component Information

Information on toxicological effects

Symptoms Erythema (skin redness). Burning. May cause blindness. Coughing and/ or wheezing.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.

Mutagenic Effects No information available.

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical name	ACGIH	IARC	NTP	OSHA
Supplier Trade Secret	A3	Group 2B		X

ACGIH (American Conference of Governmental Industrial Hygienists)

A3 - Animal Carcinogen

IARC (International Agency for Research on Cancer)

Group 2B - Possibly Carcinogenic to Humans

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity No information available.

STOT - single exposure No information available.

STOT - repeated exposure Causes damage to organs through prolonged or repeated exposure. Based on classification criteria from the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200), this product has been determined to cause systemic target organ toxicity from chronic or repeated exposure. (STOT RE).

Chronic Toxicity No known effect based on information supplied. Chronic exposure to corrosive fumes/gases may cause erosion of the teeth followed by jaw necrosis. Bronchial irritation with chronic cough and frequent attacks of pneumonia are common. Gastrointestinal disturbances may also be seen. Contains a known or suspected carcinogen. Avoid repeated exposure. Prolonged exposure may cause chronic effects. May cause adverse liver effects.

Target Organ Effects Respiratory system. Eyes. Skin. Gastrointestinal tract (GI). Central Vascular System (CVS). Kidney. Liver. Lungs.

Aspiration Hazard No information available.

Numerical measures of toxicity Product Information

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral)
2,034.00 mg/kg



ATEmix (dermal)

1,220.00 mg/kg (ATE)

12. ECOLOGICAL INFORMATION**Ecotoxicity**

Harmful to aquatic life. Very toxic to aquatic life with long lasting effects.

Chemical name	Toxicity to Algae	Toxicity to Fish	Toxicity to Microorganisms	Daphnia Magna (Water Flea)
Supplier Trade Secret	96h EC50: 0.031 - 0.054 mg/L (Pseudokirchneriella subcapitata) 72h EC50: 0.0426 - 0.0535 mg/L (Pseudokirchneriella subcapitata)	96h LC50: 0.0068 - 0.0156 mg/L (Pimephales promelas) 96h LC50: = 1.25 mg/L (Lepomis macrochirus) 96h LC50: = 0.052 mg/L (Oncorhynchus mykiss) 96h LC50: = 0.2 mg/L (Pimephales promelas) 96h LC50: < 0.3 mg/L (Pimephales promelas) 96h LC50: = 0.112 mg/L (Poecilia reticulata) 96h LC50: = 0.3 mg/L (Cyprinus carpio) 96h LC50: = 0.8 mg/L (Cyprinus carpio)		48h EC50: = 0.03 mg/L

Persistence and Degradability

No information available.

Bioaccumulation

No information available

Other adverse effects

No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal methods

This material, as supplied, is not a hazardous waste according to Federal regulations (40 CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local regulations for additional requirements.

Contaminated Packaging

Dispose of contents/containers in accordance with local regulations.

California Hazardous Waste Codes 141

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical name	California Hazardous Waste
Supplier Trade Secret	Toxic
Supplier Trade Secret	Toxic
Supplier Trade Secret	Ignitable powder

14. TRANSPORT INFORMATION

Note:

The transportation of primary lithium cells and batteries is regulated by the International Civil Aviation Organization, International Air Transport Association, International Maritime Dangerous Goods Code and the US Department of Transportation. The batteries must meet the following criteria for shipment: 1. Air shipments must meet the requirements listed in Special Provision A45 of the International Air Transport Association Dangerous Goods Regulations. 2. Meet the requirements for the US Department of Transportation listed in 49 CFR 173.185. 3. The transport of primary lithium batteries is prohibited aboard passenger aircraft. Refer to the Federal Register December 15, 2004 (Hazardous Materials; Prohibited on the Transportation of Primary Lithium Batteries and Cells Aboard Passenger Aircraft; Final Rule)
Lithium batteries shipped as "Lithium batteries", "Lithium batteries packed with equipment", or "Lithium batteries contained in equipment" may not be classified as "Dangerous Goods" when shipped in accordance with "special provision A45 of IATA-DGR" or "special provision 188 of IMO-IMDG Code"

DOT NOT REGULATED
Proper Shipping Name NON-REGULATED
Hazard Class N/A
Emergency Response Guide Number 147

TDG Not regulated

MEX Not regulated

ICAO Not regulated

IATA Not regulated
Proper Shipping Name NON REGULATED
Hazard Class N/A



IMDG/IMO	Not regulated
Hazard Class	N/A
EmS-No.	F-A, S-I
RID	Not regulated
ADR	Not regulated
ADN	Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA	Complies
DSL	All components are listed either on the DSL or NDSL.

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
 DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical name	CAS No	Weight-%	SARA 313 - Threshold Values %
Supplier Trade Secret -		15 - 40	0.1
Supplier Trade Secret -		5 - 10	1.0
Supplier Trade Secret -		3 - 7	1.0

SARA 311/312 Hazard Categories

Acute Health Hazard	No
Chronic Health Hazard	No
Fire Hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

Chemical name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Supplier Trade Secret		X	X	

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical name	Hazardous Substances RQs	Extremely Hazardous Substances RQs	RQ
Supplier Trade Secret	5000 lb		RQ 5000 lb final RQ RQ 2270 kg final RQ

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.



U.S. State Right-to-Know Regulations

Chemical name	New Jersey	Massachusetts	Pennsylvania	Rhode Island	Illinois
Supplier Trade Secret	X		X	X	X
Supplier Trade Secret	X	X	X	X	X
Supplier Trade Secret	X	X	X	X	

International Regulations

Mexico

National occupational exposure limits

Component	Carcinogen Status	Exposure Limits
Supplier Trade Secret (5 - 10)		Mexico: TWA= 1 mg/m ³ Mexico: TWA= 0.2 mg/m ³ Mexico: STEL= 2 mg/m ³
Supplier Trade Secret (3 - 7)		Mexico: TWA= 10 mg/m ³

Mexico - Occupational Exposure Limits - Carcinogens

Canada

WHMIS Hazard Class

Not determined

16. OTHER INFORMATION

NFPA	Health Hazards 1	Flammability 0	Instability 0	Physical and Chemical Hazards - Personal Protection X
HMS	Health Hazards 0	Flammability 0	Physical Hazard 0	

Prepared By Product Stewardship
23 British American Blvd.
Latham, NY 12110
1-800-572-6501

Issuing Date 08-Jun-2015
Revision Date 05-Jun-2015
Revision Note No information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet

