

# WE MAKE THE CUT™



## Kett Tool KS-426 Panel Saw

### Features:

- 5.0 amp pistol grip, variable speed, 2500 rpm motor
- Replaceable high-speed steel saw blades
- Cuts cold-rolled mild steel up to 16 gauge, aluminum to 0.100", plastic, and other rigid materials
- Adjustable depth of cut up to  $\frac{3}{8}$ " - available with 279-1 small cable guide accessory
- Plunge cuts for smooth, safe cutting
- Lightweight and easily maneuverable

### Specifications:

**Amps** 5.0  
**RPM** 0 to 2,500  
**Power Source** 120V  
**Saw Unit** KS-26  
**Maximum Depth of Cut**  $\frac{3}{8}$ "

**Rigid Materials** 5/16"  
**Cold-rolled Mild Steel** 16 gauge  
**Aluminum** 0.100 inches  
**Length** 17 inches  
**Weight** 7 pounds  
**Other Configurations** 90 PSI Pneumatic

Kett Tool Company  
5055 Madison Road  
Cincinnati, OH 45227  
(513) 271-0333

[www.kett-tool.com](http://www.kett-tool.com)  
[info@kett-tool.com](mailto:info@kett-tool.com)



