# Safety Data Sheet



Revision Number: 002.2

1. PRODUCT AND COMPANY IDENTIFICATION

Product name: Product type:

**Restriction of Use:** 

Company address:

Henkel Corporation

Rocky Hill, Connecticut 06067

One Henkel Way

Loctite® Super Glue Control™ UltraGel™ Not available.

None identified

IDH number:

1363589

Item number:1363589Region:United StatesContact information:Telephone: +1 (800) 624-7767MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCYPhone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887

## 2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW		
WARNING:	COMBUSTIBLE LIQUID.	
	CAUSES SKIN IRRITATION.	
	MAY CAUSE AN ALLERGIC SKIN REACTION.	
	CAUSES SERIOUS EYE IRRITATION.	
	MAY CAUSE RESPIRATORY IRRITATION.	

HAZARD CLASS	HAZARD CATEGORY
FLAMMABLE LIQUID	4
SKIN IRRITATION	2
EYE IRRITATION	2A
SKIN SENSITIZATION	1
SPECIFIC TARGET ORGAN TOXICITY - SINGLE EXPOSURE	3

PICTOGRAM(S)

#### **Precautionary Statements**

Prevention:	Keep away from heat, sparks, open flames, hot surfaces - no smoking. Avoid breathing vapors, mist, or spray. Wash thoroughly after handling. Use only outdoors or in a well-ventilated area. Contaminated work clothing should not be allowed out of the workplace. Wear protective
	gloves, eve protection, and face protection.
Response:	IF ON SKIN: Wash with plenty of soap and water. IF INHALED: Remove person to fresh air and keep comfortable for breathing.
	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. Call a poison control center or physician if you feel unwell. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing. In case of fire: Use foam, dry chemical or carbon dioxide to extinguish.
Storage:	Store in a well-ventilated place. Keep container tightly closed. Store in a well-ventilated place. Keep cool. Store locked up.
Disposal:	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

#### See Section 11 for additional toxicological information.

### 3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Ethyl 2-cyanoacrylate	7085-85-0	60 - 100
Treated fumed silica	67762-90-7	1 - 5
Thickener	Proprietary	1 - 5

\* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES				
Inhalation:	Move to fresh air. If symptoms persist, seek medical advice.			
Skin contact:	Do not pull bonded skin apart. Soak in warm soapy water. Gently peel apart using a blunt instrument. If skin is burned due to the rapid generation of heat by a large drop, seek medical attention. If lips are bonded, apply warm water to the lips and encourage wetting and pressure from saliva in mouth. Peel or roll lips apart. Do not pull lips apart with direct opposing force.			
Eye contact:	Immediately flush with plenty of water for at least 15 minutes. Get medical attention. If eyelids are bonded closed, release eyelashes with warm water by covering with a wet pad. Do not force eye open. Cyanoacrylate will bond to eye protein and will cause a lachrymatory effect which will help to debond the adhesive. Keep eye covered until debonding is complete, usually within 1-3 days. Medical attention should be sought in case solid particles of polymerized cyanoacrylate trapped behind the eyelid caused abrasive damage.			
Ingestion:	Ensure breathing passages are not obstructed. The product will polymerize rapidly and bond to the mouth making it almost impossible to swallow. Saliva will separate any solidified product in several hours. Prevent the patient from swallowing any separated mass.			
Symptoms:	See Section 11.			
Notes to physician:	Surgery is not necessary to separate accidentally bonded tissues. Experience has shown that bonded tissues are best treated by passive, non-surgical first aid. If rapid curing has caused thermal bums they should be treated symptomatically after adhesive is removed.			
5. FIRE FIGHTING MEASURES				
Extinguishing media:	Carbon dioxide, foam, powder			
Special firefighting procedures:	Fire fighters should wear positive pressure self-contained breathing apparatus (SCBA).			
Unusual fire or explosion hazards:	Not available.			

#### Hazardous combustion products:

Trace amounts of toxic and/or irritating fumes may be released and the use of breathing apparatus is recommended.

### 6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.	
Clean-up methods:	Do not use cloths for mopping up. Flood with water to complete polymerization and scrape off the floor. Cured material can be disposed of as non-hazardous waste.	
7. HANDLING AND STORAGE		

Handling:

Avoid contact with eyes, skin and clothing. Avoid breathing vapors or mists of this product. Wash thoroughly after handling. Avoid contact with fabric or paper goods. Contact with these materials may cause rapid polymerization which can generate smoke and strong irritating vapors, and cause thermal burns.

Storage:

Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

For information on product shelf life, please review labels on container or check the Technical Data Sheet.

### 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	nent(s) ACGIH TLV OSHA PEL		AIHA WEEL	OTHER
Ethyl 2-cyanoacrylate	0.2 ppm TWA	None	None	None
Treated fumed silica	10 mg/m3 TWA Inhalable dust. 3 mg/m3 TWA Respirable fraction.	15 mg/m3 TWA Total dust. 5 mg/m3 TWA Respirable fraction.	None	None
Thickener	None	None	None	None
Engineering controls:	Use positive down-draft exhaust ventilation if general ventilation is insufficient to maintain vapor concentration below established exposure limits.			
Respiratory protection:	ction: Use NIOSH approved respirator if there is potential to exceed exposure limit(s).			ceed exposure
Eye/face protection:	Safety goggles or safety glasses with side shields.			
Skin protection:	Use nitrile gloves and aprons as necessary to prevent contact. Do not use PVC, nylon or cotton.			

## 9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state: Color: Odor: Odor threshold: pH: Vapor pressure: Boiling point/range: Melting point/ range: Vapor density: Flash point: Clear Colorless Irritating Not available. < 0.2 mm hg > 300 °F (> 148.9 °C) None Not available. Not available. 80 - 93 °C (176°F - 199.4 °F) Tagliabue closed cup Flammable/Explosive limits - lower: Flammable/Explosive limits - upper: Autoignition temperature: Evaporation rate: Solubility in water: Partition coefficient (n-octanol/water): VOC content: Viscosity: Decomposition temperature: Not available. Not available. Not available. Not available. Polymerises in presence of water. Not available. Not available. Not available. Not available.

## **10. STABILITY AND REACTIVITY**

Stability:	Stable under recommended storage conditions.		
Hazardous reactions:	Rapid exothermic polymerization will occur in the presence of water, amines, alkalis and alcohols.		
Hazardous decomposition products:	None		
Incompatible materials:	Water, Amines, Alkalis, Alcohols.		
Reactivity:	Not available.		
Conditions to avoid:	None if used for intended purpose.		
	11. TOXICOLOGICAL INFORMATION		

Relevant routes of exposure:

Skin, Inhalation, Eyes

#### Potential Health Effects/Symptoms

Inhalation:	Exposure to vapors above the established exposure limit results in respiratory irritation, which	
	may lead to difficulty in breathing and tightness in the chest.	
Skin contact:	Bonds skin in seconds. May cause skin irritation. Cyanoacrylates have been reported to cause allergic reaction but due to rapid polymerization at the skin surface, an allergic response is rare. Cyanoacrylates generate heat on solidification. In rare circumstances a large drop will burn the	
	skin. Cured adhesive does not present a health hazard even if bonded to the skin.	
Eye contact:	Irritating to eyes. Causes excessive tearing. Eyelids may bond.	
Ingestion:	Not expected to be harmful by ingestion. Rapidly polymerizes (solidifies) and bonds in mouth. It	
	is almost impossible to swallow.	

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects	
Ethyl 2-cyanoacrylate	None	Irritant, Allergen, Respiratory	
Treated fumed silica	ned silica None Irritant		
Thickener	None	Irritant	

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Ethyl 2-cyanoacrylate	No	No	No
Treated fumed silica	No	No	No
Thickener	No	No	No

## **12. ECOLOGICAL INFORMATION**

**Ecological information:** 

Not available.

## **13. DISPOSAL CONSIDERATIONS**

Information provided is for unused product only.

Recommended method of disposal:	Dispose of according to Federal, State and local governmental regulations.

Hazardous waste number:

It is the responsibility of the user to determine if an item is hazardous as defined in the Resource Conservation and Recovery Act (RCRA) at the time of disposal. Product uses, transformations, mixtures, processes, etc., may render the resulting material hazardous, under the criteria of ignitability, corrosivity, reactivity and toxicity characteristics of the Toxicity Characteristics Leaching Procedure (TCLP) 40 CFR 261.20-24.

## 14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Gro	und (49 CFR)
Proper shipping name:	Combu

`	Combustible liquid, n.o.s.	(Cyanoacrylate ester)
	Combustible Liquid	(,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,
	NA 1993	

International Air Transportation (ICAO/IATA)	
Proper shipping name:	

Hazard class or division: Identification number: Packing group:

Hazard class or division:

Identification number:

Packing group:

Exceptions:

Aviation regulated liquid, n.o.s. (Cyanoacrylate ester) 9 UN 3334 III Not more than 500 ml (each inner package) - Unrestricted

Water Transportation (IMO/IMDG) Proper shipping name: Hazard class or division: Identification number: Packing group:

Not regulated None None None

#### **15. REGULATORY INFORMATION**

**United States Regulatory Information** 

TSCA 8 (b) Inventory Status: TSCA 12 (b) Export Notification:	All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory. None above reporting de minimis	
CERCLA/SARA Section 302 EHS: CERCLA/SARA Section 311/312: CERCLA/SARA Section 313:	None above reporting de minimis Immediate Health, Fire, Reactive None above reporting de minimis	
California Proposition 65:	This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.	
Canada Regulatory Information		
CEPA DSL/NDSL Status:	Contains one or more components listed on the Non-Domestic Substances List. All other components are listed on or are exempt from listing on the Domestic Substances List. Components listed on the NDSL must be tracked by all Canadian Importers of Record as required by Environment Canada. They may be imported into Canada in limited quantities.	

Please contact Regulatory Affairs for additional details.

### 16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: This Safety Data Sheet contains changes from the previous version in Section(s):

Prepared by: Kyra Kozak Woods, Manager, Regulatory Affairs

**Issue date:** 12/16/2014

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.