

WE MAKE THE CUT™



Kett Tool P-2040 14 Gauge Double Cut Shear

Features:

- 90 PSI straight handle, variable speed, 2500 rpm motor
- Replaceable A-2 tool steel shear blades
- Cuts cold-rolled mild steel up to 14 gauge, most grades of stainless steel to 16 gauge
- Cuts up to 170 inches per minute
- With the 7/32" waste strip, you get a clean, burr free cut
- Lightweight and easily maneuverable - can cut a 7" radius

Specifications:

CFM 16	Minimum Cutting Radius 7 inches
RPM 0 to 2,500	Cold-rolled Mild Steel 14 gauge
Power Source 90 PSI compressed air	Stainless Steel 16 gauge
Shear Head 40-20 Steel	Length 10.5 inches
Cutting Speed 170 inches per minute	Weight 3.5 pounds
	Other Configurations 90 PSI pistol grip 120V Electric pistol grip

Kett Tool Company
5055 Madison Road
Cincinnati, OH 45227
(513) 271-0333

www.kett-tool.com
info@kett-tool.com

KETT
TOOL COMPANY

