

WE MAKE THE CUT™



Kett Tool P-540 14 Gauge Double Cut Shear

Features:

- 90 PSI pistol grip, variable speed, 2200 rpm motor
- Replaceable A-2 tool steel shear blades
- Cuts cold-rolled mild steel up to 14 gauge, most grades of stainless steel to 16 gauge
- Cuts up to 180 inches per minute
- With the 7/32" waste strip, you get a clean, burr free cut
- Lightweight and easily maneuverable - can cut a 7" radius

Specifications:

CFM 16	Minimum Cutting Radius 7 inches
RPM 0 to 2,200	Cold-rolled Mild Steel 14 gauge
Power Source 90 PSI compressed air	Stainless Steel 16 gauge
Shear Head 40-20 Steel	Length 10.5 inches
Cutting Speed 180 inches per minute	Weight 4 pounds
	Other Configurations 90 PSI straight handle 120V Electric pistol grip

Kett Tool Company
5055 Madison Road
Cincinnati, OH 45227
(513) 271-0333

www.kett-tool.com

info@kett-tool.com

KETT
TOOL COMPANY

