

NESCAFÉ®

LOW LABOR SOLUTION FOR
SPECIALTY COFFEE SERVED ON DEMAND



NESCAFÉ® ULTIMATE BARISTA

INCREASE CUSTOMER SATISFACTION WITH THE BEAN-TO-CUP SPECIALTY COFFEE BREWER, NESCAFÉ® ULTIMATE BARISTA

Consumers state that freshness, flavor, and consistency are essential for a good cup of coffee. They also prefer specialty coffees that are ground and brewed*. Meet customer demand with the **NESCAFÉ® Ultimate Barista** coffee machine. At the simple push of a button, this **bean-to-cup brewer** freshly grinds whole beans, then consistently brews and dispenses a variety of high-quality, fresh-tasting coffee and great-tasting instant hot beverages with minimal waste.



FEATURES/SPECIFICATIONS

- 33.46 in H x 16.25 in W x 22.25 in D
- Grinds, brews, and dispenses
- Up to 25 beverages
- 3 beverage sizes
- 40-150 cups per day
- Intuitive touchscreen
- Easy-to-clean design
- UL/NSF Certified
- **NEW!** Cashless and touchless options

COFFEE PROGRAM SUPPORT

- Free on-loan with minimum purchase
- Machine and water filter installation
- Corrective maintenance
- Customer service & troubleshooting
- Marketing & merchandising materials
- Branded cups and lids

Espresso • Cappuccino • Café Latte • Café Americano • Long Espresso • Hot Chocolate
Chocolate with Milk • Café Mocha • Vanilla Cocoa • French Vanilla • French Vanilla with Milk
Café Vanilla • Café Con Leche • Flat White • Cortadito • Decaf Offerings • Black Coffee
Black Coffee (16oz) • Hot Water • Steamed Milk



WE CAN BREW A BRIGHT NEW FUTURE, ONE CUP AT A TIME

NESCAFÉ Grown Respectfully helps protect the future of coffee for those who enjoy drinking it, growing it – and selling it. NESCAFÉ understands foodservice operations have their own corporate social responsibility goals. That’s why we offer customer communication and manufacturing practices to help comply with corporate sustainability. With NESCAFÉ, every cup counts.



IMPROVING QUALITY OF LIFE FOR **FARMERS**

Helping them to plant and grow healthier, disease-resistant coffee plants that produce more coffee beans – so they have more to sell.



HELPING FARMING **COMMUNITIES**

Empowering farmers to develop their own nurseries and encouraging younger family members to continue their farming heritage.



RESPECTING OUR **PLANET**

Bringing in new farming techniques that protect and conserve natural resources – and helps you too – by plugging you into a pipeline of NESCAFÉ coffees.



MACHINE INFORMATION

height	33.46 in
height w/bean hopper lid open	43.31 in
width	16.25 in
depth	22.25 in
depth with door open	33.75 in
weight	90 lbs
canisters	4
roast & ground bean capacity	2.6 pounds
user interface	7-inch touch screen
water tank capacity	20-oz boiler capacity
minimum/maximum dispense temp range	min temp is 20° below set temp
warm-up time	5 minutes
dispensing selections	up to 25

PLUMBING & ELECTRICAL REQUIREMENTS

water line size	3/8-in line with 3/4-in female hose connector
water pressure	7.3 psi minimum/123.3 psi maximum (.5 bar minimum/8.5 bar maximum)
electrical requirements	120 V
frequency	60 Hz



NESCAFÉ CLASSICO 100% ARABICA ROAST & GROUND COFFEE

Brews a medium roast cup using sustainably grown coffee beans. Savor the perfect blend of rich, acidic caramel notes with medium body and a hint of fruity undertones.

NESCAFÉ COFFEE AND COCOA PRODUCTS

Choose from a variety of roast and ground and soluble coffees using sustainably grown and sourced coffee beans.

	Globe No.	GTIN	Shelf Life (days)	Case Configuration				Pallet Configuration		
				Net Wt. (lbs.)	Gross Wt. (lbs.)	Cube (lbs.)	Length x Width x Height (inches)	Tl x Hl	Ttl Cs.	Length x Width x Height (inches)
NESTLÉ® Premium Hot Choc Mix 4x1.75lb	12234626	00028000103439	540	7.0	7.6	0.31	11.00 x 7.15 x 6.85	22 x 6	132	48.0 x 40.0 x 40.9
NESCAFÉ Espresso Roast 4x250g	12249472	00028000787912	540	2.2	2.7	0.33	12.80 x 6.80 x 6.60	21 x 7	147	48.0 x 40.0 x 46.4
NESTLÉ Carnation Instant Nonfat Dry Milk 4x22.75oz	12428935	00050000229284	365	5.69	6.86	0.427	10.7 x 10.6 x 6.5	16 x 7	112	42.75 x 42.25 x 45.5
NESCAFÉ French Vanilla Powder 6x2lb	12025548	00028000990190	540	12.0	13.34	0.551	10.9 x 10.4 x 8.4	16 x 5	80	42.6 x 42.5 x 42.0
NESCAFÉ Whole Bean Espresso 6X2.2lb	12338492	07891000246313	365	13.2	14.64	1.294	16.35 x 12.6 x 10.85	8 x 5	40	48 x 40 x 64.3
NESCAFÉ Decaf 4x250g	12333388	00028000862138	540	2.2	2.84	0.258	12 x 6 x 6.2	24 x 7	168	48 x 40 x 48.4
NESCAFÉ Classico 100% Arabica Roast & Ground	12467579	00028000255732	365	12	13.2	0.805	14.4 x 10.5 x 9.2	11 x 5	51	48 x 40 x 46
NESTLÉ ABUELITA™ Hot Cocoa Mix 6x2lb	12080293	00050000202003	540	12	13.34	0.551	0.9 x 10.4 x 8.4	16 x 5	80	42.5 x 42.5 x 41.9



NESCAFÉ®

For more information, go to nestleprofessional.com
or call 1-800-288-8682.
To order, contact your Nestlé Professional Sales Representative.

CUSTOMIZED TECHNICAL SUPPORT



Enhanced
In-Cup Quality



Machine
Installation



Staff
Training



Machine
Corrective
Maintenance



We have a range of solutions that will delight all your customers

