

1. Identification

Product identifier	Protection That Lives On Microban Professional Brand 24 Hour Keeps Killing 99.9% of Bacteria For Up To 24 Hours Multi-Purpose Cleaner		
Other means of identification			
Product code	30110-005		
Recommended use	Multi-Purpose Cleaner		
Recommended restrictions	None known.		
Manufacturer/Importer/Supplier/Distributor information			
Company name	Microban Products Company		
Address	11400 Vanstory Drive Huntersville, NC 28078 USA		
Telephone	704-875-0806		
Email	infoleads@microban.com		
Emergency phone number	(24 hr Emergency) 1-800-535-5053 or 1-352-323-3500		

2. Hazard(s) identification

Physical hazards	Not classified.		
Health hazards	Serious eye damage/eye irritation	Category 2B	
Environmental hazards	Hazardous to the aquatic environment, acute hazard	Category 1	
	Hazardous to the aquatic environment, long-term hazard	Category 1	
OSHA defined hazards	Not classified.		
Label elements			



Signal word	Warning		
Hazard statement	Causes eye irritation. Very toxic to aquatic life with long lasting effects.		
Precautionary statement			
Prevention	Wash thoroughly after handling. Avoid release to the environment.		
Response	If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. Collect spillage.		
Storage	Store away from incompatible materials.		
Disposal	Dispose of contents/container in accordance with local/regional/national/international regulations.		
Hazard(s) not otherwise classified (HNOC)	None known.		
Supplemental information	None.		

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
ALCOHOLS, C9-11, ETHOXYLATED		68439-46-3	<1
Ethanol		64-17-5	<1

Chemical name	Common name and synonyms	CAS number	%
Quaternary Ammonium Compounds, Benzyl-c12-16-alkyldimethyl, Chlorides		68424-85-1	<1
DIDECYL DIMETHYL AMMONIUM CHLORIDE		7173-51-5	<0.5

4. First-aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Wash off with soap and water. Get medical attention if irritation develops and persists.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Ingestion	Rinse mouth. Get medical attention if symptoms occur.
Most important symptoms/effects, acute and delayed	Irritation of eyes. Exposed individuals may experience eye tearing, redness, and discomfort.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	Move containers from fire area if you can do so without risk.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Prevent entry into waterways, sewer, basements or confined areas. Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water. Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling	Avoid contact with eyes. Avoid prolonged exposure. Provide adequate ventilation. Wear appropriate personal protective equipment. Avoid release to the environment. Observe good industrial hygiene practices.
Conditions for safe storage, including any incompatibilities	Store in tightly closed container. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

The following constituents are the only constituents of the product which have a PEL, TLV or other recommended exposure limit. At this time, the other constituents have no known exposure limits.

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
Ethanol (CAS 64-17-5)	PEL	1900 mg/m3 1000 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
Ethanol (CAS 64-17-5)	STEL	1000 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Ethanol (CAS 64-17-5)	TWA	1900 mg/m3 1000 ppm

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection Wear appropriate chemical resistant gloves.

Other Wear suitable protective clothing.

Respiratory protection In case of insufficient ventilation, wear suitable respiratory equipment.

Thermal hazards Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state Liquid.
Form Liquid.
Color Clear water-white to Slightly Off-White.

Odor Not available.

Odor threshold Not available.

pH 9 - 10.5

Melting point/freezing point Not available.

Initial boiling point and boiling range Not available.

Flash point Not available.

Evaporation rate Not available.

Flammability (solid, gas) Not applicable.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) Not available.

Flammability limit - upper (%) Not available.

Explosive limit - lower (%) Not available.

Explosive limit - upper (%)	Not available.
Vapor pressure	Not available.
Vapor density	Not available.
Relative density	Not available.
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Explosive properties	Not explosive.
Oxidizing properties	Not oxidizing.
Specific gravity	1 - 1.01

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Prolonged inhalation may be harmful.
Skin contact	No adverse effects due to skin contact are expected.
Eye contact	Causes eye irritation.
Ingestion	Expected to be a low ingestion hazard.

Symptoms related to the physical, chemical and toxicological characteristics Irritation of eyes. Exposed individuals may experience eye tearing, redness, and discomfort.

Information on toxicological effects

Acute toxicity Based on available data, the classification criteria are not met.

Components	Species	Test Results
-------------------	----------------	---------------------

DIDECYL DIMETHYL AMMONIUM CHLORIDE (CAS 7173-51-5)

Acute

Dermal

LD50	Rabbit	2730 mg/kg
------	--------	------------

Ethanol (CAS 64-17-5)

Acute

Inhalation

LC50	Mouse	39 mg/l, 4 Hours
------	-------	------------------

Oral

LD50	Rat	6.2 g/kg
------	-----	----------

Skin corrosion/irritation Prolonged skin contact may cause temporary irritation.

Serious eye damage/eye irritation Causes eye irritation.

Respiratory or skin sensitization

Respiratory sensitization Not a respiratory sensitizer.

Skin sensitization This product is not expected to cause skin sensitization.

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity Not classifiable as to carcinogenicity to humans.

IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity This product is not expected to cause reproductive or developmental effects.

Specific target organ toxicity - single exposure Not classified.

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard Not an aspiration hazard.

Chronic effects Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity Very toxic to aquatic life with long lasting effects.

Components		Species	Test Results
ALCOHOLS, C9-11, ETHOXYLATED (CAS 68439-46-3)			
Aquatic			
Crustacea	EC50	Water flea (Daphnia magna)	2.9 - 8.5 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas)	6 - 12 mg/l, 96 hours
DIDECYL DIMETHYL AMMONIUM CHLORIDE (CAS 7173-51-5)			
Aquatic			
Fish	LC50	White sturgeon (Acipenser transmontanus)	0.001 - 0.01 mg/l, 96 hours
Ethanol (CAS 64-17-5)			
Aquatic			
Crustacea	EC50	Water flea (Daphnia magna)	7.7 - 11.2 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas)	> 100 mg/l, 96 hours
Quaternary Ammonium Compounds, Benzyl-c12-16-alkyldimethyl, Chlorides (CAS 68424-85-1)			
Aquatic			
<i>Acute</i>			
Crustacea	EC50	Daphnia magna	< 1 mg/l, 48 hours

Persistence and degradability No data is available on the degradability of any ingredients in the mixture.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)

Ethanol -0.31

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national/international regulations.

Local disposal regulations Dispose in accordance with all applicable regulations.

Hazardous waste code	The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information

DOT	Not regulated as dangerous goods.
IATA	Not regulated as dangerous goods.
IMDG	Not regulated as dangerous goods.
Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not established.
General information	Per IATA DGR Special Provision A197, IMDG Code 2.10.2.7, and 49 CFR § 171.4(c), this product, as packaged, is not regulated as a Marine Pollutant due to package size. Regulated as UN3082, Environmentally Hazardous Substance, Liquid, N.O.S., Class 9, Packing Group III if single or inner package size exceeds 5 liters and/or outer packaging exceeds 30kg.

15. Regulatory information

US federal regulations	This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
-------------------------------	--

Toxic Substances Control Act (TSCA)

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Ethanol (CAS 64-17-5) Listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical

Yes

Classified hazard categories Serious eye damage or eye irritation

SARA 313 (TRI reporting)

Not regulated.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA)

None known.

FEMA Priority Substances Respiratory Health and Safety in the Flavor Manufacturing Workplace

Ethanol (CAS 64-17-5) Low priority

FIFRA Information

This chemical is a pesticide product registered by the Environmental Protection Agency and is subject to certain labeling requirements under federal pesticide law. These requirements differ from the classification criteria and hazard information required for safety data sheets, and for workplace labels of non-pesticide chemicals.

US state regulations

California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 2016 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins. For more information go to www.P65Warnings.ca.gov.

16. Other information, including date of preparation or last revision

Issue date 13-November-2017

Revision date 07-March-2019

Version # 04

HMIS® ratings Health: 1
Flammability: 0
Physical hazard: 0

NFPA ratings Health: 1
Flammability: 0
Instability: 0

NFPA ratings



Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

Revision information

Toxicological Information: Toxicological Data
Transport Information: Agency Name, Packaging Type, and Transport Mode Selection
Transport information: General information
Regulatory information: Safe Drinking Water Act (SDWA)