

SAFETY DATA SHEET



Issuing Date: 12-Mar-2015

Revision Date: 12-Mar-2015

Version 1

1. IDENTIFICATION

Product Name Dawn Ultra Power Dissolver

Product ID: 95446855_RET_NG

Product Type: Finished Product - Consumer (Retail) Use Only

Recommended Use Dish Care

Restrictions on Use Use only as directed on label.

Manufacturer PROCTER & GAMBLE - Fabric and Home Care Division. Ivorydale Technical Centre.
5289 Spring Grove Avenue, Cincinnati, Ohio 45217-1087 USA

E-mail Address pgsds.im@pg.com

Emergency Telephone Transportation (24 HR)
CHEMTREC - 1-800-424-9300
(U.S./ Canada) or 1-703-527-3887
Mexico toll free in country: 800-681-9531

2. HAZARD IDENTIFICATION

"Consumer Products", as defined by the US Consumer Product Safety Act and which are used as intended (typical consumer duration and frequency), are exempt from the OSHA Hazard Communication Standard (29 CFR 1910.1200). This SDS is being provided as a courtesy to help assist in the safe handling and proper use of the product.

This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:

Hazard Category

Skin corrosion/irritation Category 1
Eye Damage / Irritation Category 1

Signal Word DANGER

Hazard Statements Causes severe skin burns and eye damage

Hazard pictograms



Precautionary Statements - Prevention Do not breathe mist
Wash hands thoroughly after handling

Wear protective gloves and eye protection
Use with ventilation.

Precautionary Statements - Response

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
Immediately call a POISON CENTER or doctor/physician
IF SWALLOWED: Rinse mouth. DO NOT induce vomiting.
Drink 1 or 2 glasses of water
IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower
IF INHALED: Remove to fresh air and keep at rest in a position comfortable for breathing

Precautionary Statements - Storage

None

Precautionary Statements - Disposal

None

Hazards not otherwise classified (HNOC)

None

3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Chemical Name	Synonyms	Trade Secret	CAS-No	Weight %
Dipropylene Glycol Butoxy Ether	-	No	29911-28-2	5 - 10
Phenoxyethanol	-	No	122-99-6	5 - 10
2-Aminoethanol	-	No	141-43-5	5 - 10
Benzenesulfonic acid, (1-methylethyl)-, sodium salt (1:1)	-	No	28348-53-0	1 - 5
Amine oxides, C10-16-alkyldimethyl	-	No	70592-80-2	1 - 5
Limonene	-	No	5989-27-5	0.1 - 1.0

4. FIRST AID MEASURES

First aid measures for different exposure routes**Eye contact**

Rinse with plenty of water. Call a physician immediately.

Skin contact

Rinse with plenty of water. Get medical attention if irritation develops and persists.

Ingestion

Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur.

Inhalation

IF INHALED: Remove to fresh air and keep at rest in a position comfortable for breathing. Call a physician or poison control center immediately.

Most important symptoms/effects, acute and delayed

None under normal use conditions.

Indication of immediate medical attention and special treatment needed, if necessary**Notes to Physician**

Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing mediaDry chemical, CO₂, alcohol-resistant foam or water spray.

Unsuitable Extinguishing Media	None.
Special hazard	None known.
Special protective equipment for fire-fighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.
Specific hazards arising from the chemical	None.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Use personal protective equipment. Do not get in eyes, on skin, or on clothing.

Advice for emergency responders Use personal protective equipment as required.

Methods and materials for containment and cleaning up

Methods for containment Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal.

Methods for cleaning up Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible products None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	CAS-No	ACGIH TLV	OSHA PEL	Mexico PEL
2-Aminoethanol	141-43-5	STEL: 6 ppm TWA: 3 ppm	TWA: 3 ppm TWA: 6 mg/m ³ (vacated) TWA: 3 ppm (vacated) TWA: 8 mg/m ³ (vacated) STEL: 6 ppm (vacated) STEL: 15 mg/m ³	Mexico: TWA 3 ppm Mexico: TWA 8 mg/m ³ Mexico: STEL 6 ppm Mexico: STEL 15 mg/m ³

Chemical Name	CAS-No	Alberta	Quebec	Ontario TWAEV	British Columbia
Phenoxyethanol	122-99-6			TWA: 25 ppm TWA: 141 mg/m ³ Skin	
2-Aminoethanol	141-43-5	TWA: 3 ppm TWA: 7.5 mg/m ³ STEL: 6 ppm STEL: 15 mg/m ³	TWA: 3 ppm TWA: 7.5 mg/m ³ STEL: 6 ppm STEL: 15 mg/m ³	TWA: 3 ppm STEL: 6 ppm	TWA: 3 ppm STEL: 6 ppm

No relevant exposure guidelines for other ingredients

Exposure controls

Engineering Measures

Distribution, Workplace and Household Settings:

Ensure adequate ventilation

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction

Personal Protective Equipment

Eye Protection

Distribution, Workplace and Household Settings:

Requires Eye Protection

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Safety glasses with side-shields
If splashes are likely to occur, wear:
Tightly fitting safety goggles

Hand Protection

Distribution, Workplace and Household Settings:

Protective gloves

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Protective gloves

Skin and Body Protection

Distribution, Workplace and Household Settings:

Wear suitable protective clothing

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Wear suitable protective clothing

Respiratory Protection

Distribution, Workplace and Household Settings:

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

In case of insufficient ventilation wear suitable respiratory equipment

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State @20°C

liquid

Appearance

opaque

Odor

Scented

Odor threshold

No information available

Property

Values

Note

pH value

13

Melting/freezing point

No information available

Boiling point/boiling range

No information available

Flash point

> 82.22 °C / > 180 °F

Evaporation rate

No information available

Flammability (solid, gas)

No information available

Flammability Limits in Air

Upper flammability limit

No information available

Lower Flammability Limit

No information available

Vapor pressure

No information available

Vapor density

No information available

Relative density

1.03 - 1.06

Water solubility	100%
Solubility in other solvents	No information available
Partition coefficient: n-octanol/water	No information available
Autoignition temperature	No information available
Decomposition temperature	No information available
Viscosity of Product	No information available

VOC Content (%) Products comply with US state and federal regulations for VOC content in consumer products.

10. STABILITY AND REACTIVITY

Reactivity	None under normal use conditions.
Stability	Stable under normal conditions.
Hazardous polymerization	Hazardous polymerization does not occur.
Hazardous Reactions	None under normal processing.
Conditions to Avoid	None under normal processing.
Materials to avoid	None in particular.
Hazardous Decomposition Products	None under normal use.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Inhalation	No known effect.
Skin contact	May cause burns.
Ingestion	No known effect.
Eye contact	Risk of serious damage to eyes.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Acute toxicity	No known effect.
Skin corrosion/irritation	Causes severe burns.
Serious eye damage/eye irritation	Risk of serious damage to eyes.
Skin sensitization	No known effect.
Respiratory sensitization	No known effect.
Germ cell mutagenicity	No known effect.
Neurological Effects	No known effect.
Reproductive toxicity	No known effect.
Developmental toxicity	No known effect.
Teratogenicity	No known effect.
STOT - single exposure	No known effect.
STOT - repeated exposure	No known effect.
Target Organ Effects	No known effect.
Aspiration hazard	No known effect.
Carcinogenicity	No known effect.

Component Information

Chemical Name	CAS-No	LD50 Oral	LD50 Dermal	LC50 Inhalation
Dipropylene Glycol Butoxy Ether	29911-28-2	2610 mg/kg bw (Similar to OECD 401; standard acute method; rat)	> 2000 mg/kg bw (OECD 402; standard acute method; rat)	> 2.04 mg/L air (OECD 403; standard acute method; rat)
Phenoxyethanol	122-99-6	1850 mg/kg (rat)	2214 mg/kg (rat)	> 1 mg/L (OECD 412, rat)
2-Aminoethanol	141-43-5	1089 mg/kg bw (Similar to OECD 401; standard acute method; rat)	1000 mg/kg (rabbit)	-

Benzenesulfonic acid, (1-methylethyl)-, sodium salt (1:1)	28348-53-0	5160.00 mg/kg (rat)	-	-
Amine oxides, C10-16-alkyldimethyl	70592-80-2	1330.00 mg/kg (rat)	-	-

12. ECOLOGICAL INFORMATION

Ecotoxicity

The product is not expected to be hazardous to the environment.

Persistence and degradability No information available.

Bioaccumulative potential No information available.

Mobility No information available.

Other adverse effects No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment

Waste from Residues / Unused Products Products covered by this MSDS, in their original form, when disposed as waste, are corrosive hazardous waste, D002, according to Federal RCRA regulations (40 CFR 261). Disposal should be in accordance with local, state and federal regulations.

Contaminated packaging Disposal should be in accordance with applicable regional, national and local laws and regulations.

California Hazardous Waste Codes (non-household setting) 331

14. TRANSPORT INFORMATION

DOT

UN no UN3266
UN Proper shipping name Corrosive liquid, basic, inorganic, n.o.s.
Description UN3266, Corrosive liquid, basic, inorganic, n.o.s., (monoethanolamine, sodium hydroxide), 8, III
Hazard Class 8
Packing Group III
Marine pollutant Yes.

IMDG

UN Number UN3266
UN Proper shipping name Corrosive liquid, basic, inorganic, n.o.s.
Description UN3266, Corrosive liquid, basic, inorganic, n.o.s., (monoethanolamine, sodium hydroxide), 8, III
Transport hazard class(es) 8
Packing Group III

IATA

UN no UN3266
UN Proper shipping name Corrosive liquid, basic, inorganic, n.o.s.
Description UN3266, Corrosive liquid, basic, inorganic, n.o.s., (monoethanolamine, sodium hydroxide), 8, III
Hazard Class 8
Packing Group III

15. REGULATORY INFORMATION

U.S. Federal Regulations**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372:

Chemical Name	CAS-No	SARA 313 - Threshold Values %
Phenoxyethanol	122-99-6	1.0

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302):

Chemical Name	CAS-No	Hazardous Substances RQs	Extremely Hazardous Substances RQs	CERCLA/SARA 302 TPQ
Sodium hydroxide	1310-73-2	1000 lb	-	

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product contains the following substance(s) which are either listed as hazardous air pollutants (HAPS) or VOC's per the Clean Air Act:

Chemical Name	CAS-No	CAA (Clean Air Act) - 1990 Hazardous Air Pollutants
Phenoxyethanol	122-99-6	X

Clean Water Act

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42):

Chemical Name	CAS-No	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Sodium hydroxide	1310-73-2	1000 lb	-	-	X

California Proposition 65

This product is not subject to warning labeling under California Proposition 65.

U.S. State Regulations (RTK)

Chemical Name	CAS-No	New Jersey
Phenoxyethanol	122-99-6	X
2-Aminoethanol	141-43-5	X

Chemical Name	CAS-No	Massachusetts
2-Aminoethanol	141-43-5	X

Chemical Name	CAS-No	Pennsylvania
Phenoxyethanol	122-99-6	X
2-Aminoethanol	141-43-5	X
Sodium hydroxide	1310-73-2	X

International Inventories**United States**

All intentionally-added components of this product(s) are listed on the US TSCA Inventory.

Canada

This product is in compliance with CEPA for import by P&G.

Legend

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

CEPA - Canadian Environmental Protection Act

16. OTHER INFORMATION

Issuing Date: 12-Mar-2015

Revision Date: 12-Mar-2015

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of SDS