

# BreakDown ™<sup>MC</sup> Odor Eliminator Concentrate Fresh

**Revision:** 2020-02-17 **Version:** 02.0

# 1. IDENTIFICATION

Product name: BreakDown TM/MC

Odor Eliminator Concentrate Fresh

**Product Code:** 94291110 **SDS #:** MS0800262

Recommended use: • Industrial/Institutional

Odor Control

• This product is intended to be diluted prior to use

Uses advised against:

Uses other than those identified are not recommended

Manufacturer, importer, supplier:

US Headquarters Diversey, Inc. 1300 Altura Rd., Suite 125 Fort Mill, SC 29708 Phone: 1-888-352-2249

SDS Internet Address: https://sds.diversey.com

Canadian Headquarters Diversey Canada, Inc. 6150 Kennedy Road Unit 3 Mississauga, Ontario L5T 2J4 Phone: 1-800-668-7171

Emergency telephone number: 1-800-851-7145; 1-651-917-6133 (Int'l)

## 2. HAZARDS IDENTIFICATION

# Classification for the undiluted product

This product is not classified as hazardous according to OSHA 29CFR 1910.1200 (HazCom 2012-GHS) and Canadian Hazardous Products Regulations (HPR) (WHMIS 2015-GHS).

Hazard Statements
None required.
Precautionary Statements
None required.

<u>Health hazards not otherwise classified (HHNOC)</u> - Not applicable <u>Physical hazards not otherwise classified (PHNOC)</u> - Not applicable

# Classification for the diluted product @ 1:20

This product, when diluted as stated on the label, is not classified as hazardous according to OSHA 29CFR 1910.1200 (HazCom 2012-GHS) and Canadian Hazardous Products Regulations (HPR) (WHMIS 2015-GHS).

#### **Hazard and Precautionary Statements**

None required.

# 3. COMPOSITION/INFORMATION ON INGREDIENTS

# **Classified Ingredients**

<u> </u>						
Ingredient(s)	CAS#	Weight %				
Alcohol, C9-C11, ethoxylated	68439-46-3	1 - 5%				
Sodium lauryl sulfate	68585-47-7	> 0.1 - < 1%				

# 4. FIRST AID MEASURES

## **Undiluted Product:**

**Eyes:** Rinse with plenty of water. If irritation occurs and persists, get medical attention.

Skin: No specific first aid measures are required.

<u>Inhalation:</u> No specific first aid measures are required.

Ingestion: Rinse mouth with water.

Most Important Symptoms/Effects: No information available.

Immediate medical attention and special treatment needed Not applicable.

# **Diluted Product:**

Eyes: Rinse with plenty of water.

<u>Skin:</u> No specific first aid measures are required <u>Inhalation:</u> No specific first aid measures are required

Ingestion: IF SWALLOWED: Call a Poison Center (1-800-851-7145) or doctor/physician if you feel unwell.

## 5. FIRE-FIGHTING MEASURES

**Specific methods:** No special methods required

Suitable extinguishing media: The product is not flammable. Extinguish fire using agent suitable for surrounding fire.

Specific hazards: None known.

Special protective equipment for firefighters: As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH

(approved or equivalent) and full protective gear.

Extinguishing media which must not be used for safety reasons: No information available.

#### **6. ACCIDENTAL RELEASE MEASURES**

Personal precautions: Put on appropriate personal protective equipment (see Section 8.).

Environmental precautions Clean-up methods - large spillage. Absorb spill with inert material (e.g. dry sand or earth), then place in

a chemical waste container. Use a water rinse for final clean-up.

#### 7. HANDLING AND STORAGE

Handling: Avoid contact with skin and eyes. FOR COMMERCIAL AND INDUSTRIAL USE ONLY.

Storage: Keep tightly closed in a dry, cool and well-ventilated place.

Aerosol Level (if applicable): Not applicable.

# 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Guidelines: This product, as supplied, does not contain any hazardous materials with occupational exposure limits

established by the region specific regulatory bodies.

#### <u>Undiluted Product:</u>

and clean-up methods:

#### Engineering measures to reduce exposure:

Good general ventilation should be sufficient to control airborne levels.

#### Personal Protective Equipment

It is the responsibility of the employer to determine the potential risk of exposure to hazardous chemicals for employees in the workplace in order to determine the necessity, selection, and use of personal protective equipment.

Eye protection:

Hand protection:

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

Skin and body protection:

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

Hygiene measures:

Handle in accordance with good industrial hygiene and safety practice.

# **Diluted Product:**

#### Engineering measures to reduce exposure:

Good general ventilation should be sufficient to control airborne levels.

Personal Protective Equipment

Eye protection:

Hand protection:

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

Skin and body protection:

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

Hygiene measures:

Handle in accordance with good industrial hygiene and safety practice.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State: LiquidColor:HazyRedEvaporation Rate:No information availableOdor:Perfumed

Odor threshold:No information available.Boiling point/range:Not determinedMelting point/range:Not determinedDecomposition temperature:Not determined

Autoignition temperature: No information available Solubility: Completely Soluble

Solubility in other solvents: No information available

Density: 0.998 Kg/L

Rulk density: No information available

Vapor density: No information available

Vapor pressure: No information available

**Bulk density:** No information available **Vapor pressure:** No information available. **Flash point (°F):** > 200 °F > 93 °C **Partition coefficient (n-octanol/water):** No information available

Viscosity: 5 Elemental Phosphorus: 0.00 % by wt.

VOC: 0 % \* pH: ≈ 7.5

Flammability (Solid or Gas): Not applicable

Corrosion to metals: Not corrosive to metals

Sustained combustion: Not applicable

**Explosion limits: - upper:** Not determined **- lower:** Not determined

Dilution pH: ≈ 7.1

Dilution Flash Point (°F): > 200 °F > 93 °C

VOC % by wt. at use dilution: 0 %

\* - Title 17, California Code of Regulations, Division 3, Chapter 1, Subchapter 8.5, Article 2, Consumer Products, Sections 94508

# 10. STABILITY AND REACTIVITY

Reactivity:
Stability:
Hazardous decomposition products:
Not Applicable
The product is stable
None reasonably foreseeable.

Materials to avoid: Do not mix with any other product or chemical unless specified in the use directions.

Conditions to avoid: No information available.

#### 11. TOXICOLOGICAL INFORMATION

## Information on likely routes of exposure:

Skin contact, Inhalation, Eye contact

Delayed, immediate, or chronic effects and symptoms from short and long-term exposure

**Skin contact:** Unlikely to be irritant in normal use. **Eye contact:** May be mildly irritating to eyes.

Ingestion: No information available. Inhalation: No information available. Sensitization: No known effects. Target Organs (SE): None known Target Organs (RE): None known

<u>Carcinogen Listings:</u> D-limonene is flagged as an IARC 2B because it could be included as part of the generic hydrocarbon group. However, the IARC monograph specifically states that d-limonene has no carcinogenic effects. Therefore, it is not considered a carcinogen.

Numerical measures of toxicity

**ATE - Oral (mg/kg):** >5000

BreakDown TMMC 3 of 5

# 12. ECOLOGICAL INFORMATION

Ecotoxicity: No information available.

Persistence and Degradability: No information available.

Bioaccumulation: No information available.

## 13. DISPOSAL CONSIDERATIONS

Waste from residues / unused products (undiluted product): This product, as sold, if discarded or disposed, is not a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Under RCRA, it is the responsibility of the user of the product to determine, at the time of disposal, whether the waste solution meets RCRA criteria for hazardous waste. Dispose in compliance with all Federal, state, provincial, and local laws and regulations.

Waste from residues / unused products (diluted product): This product, when diluted as stated on this SDS, is not a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Under RCRA, it is the responsibility of the user of the product to determine, at the time of disposal, whether the waste solution meets RCRA criteria for hazardous waste. Dispose in compliance with all Federal, state, provincial, and local laws and regulations.

RCRA Hazard Class (undiluted product): Not Regulated RCRA Hazard Class (diluted product): Not Regulated Contaminated Packaging: Do not re-use empty containers.

## 14. TRANSPORT INFORMATION

**DOT/TDG/IMDG:** The information provided below is the full transportation classification for this product. This description does not account for the package size(s) of this product, that may fall under a quantity exception, according to the applicable transportation regulations. When shipping dangerous goods, please consult with your internal, certified hazardous materials specialist to determine if any exceptions can be applied to your shipment.

DOT (Ground) Bill of Lading Description: NOT REGULATED

IMDG (Ocean) Bill of Lading Description: NOT REGULATED

## 15. REGULATORY INFORMATION

#### International Inventories at CAS# Level

All components of this product are listed on the following inventories: U.S.A. (TSCA), Canada (DSL/NDSL).

#### RIGHT TO KNOW (RTK)

Ingredient(s)	CAS#	MARTK:	NJRTK:	PARTK:	RIRTK:
Water	7732-18-5	-	-	=	•
Alcohol, C9-C11, ethoxylated	68439-46-3	-	-	=	-
Sodium xylene sulfonate	1300-72-7	-	-	=	-
Dipropylene glycol	25265-71-8	-	-	X	-
Sodium lauryl sulfate	68585-47-7	-	-	-	-

#### CERCLA/ SARA

# Canadian Regulations

1			
	Ingredient(s)	CAS#	NPRI
	d-Limonene	5989-27-5	X

# **16. OTHER INFORMATION**

BreakDown TMMC 4 of 5
Odor Eliminator Concentrate Fresh

## NFPA (National Fire Protection Association)

Rating Scale: (Low Hazard) 0 - 4 (Extreme Hazard)

Health 0 Flammability 0 Instability 0 Special Hazards -

# **Diluted Product:**

Health 0 Flammability 0 Instability 0 Special Hazards -

**Revision:** 2020-02-17

Version: 02.0

Reason for revision: Not applicable

Prepared by: North American Regulatory Affairs

Additional advice: • Contains an added fragrance, see "Odor" heading in section 9 for specific description

Notice to Reader: This document has been prepared using data from sources considered technically reliable. It does not constitute a warranty, express or implied, as to the accuracy of the information contained within. Actual conditions of use and handling are beyond seller's control. User is responsible to evaluate all available information when using product for any particular use and to comply with all Federal, State, Provincial and Local laws and regulations.

BreakDown TM/MC
Odor Eliminator Concentrate Fresh