


NAVIGATORTM

PLATINUM DIGITAL

Made using the most modern papermaking technology and under strict quality monitoring and control systems from pulp production to paper converting, **Navigator Platinum Digital** ensures the **highest printing quality and performance in all digital applications.**

Specially engineered to deliver high quality printing results, **Navigator Platinum Digital** combines extra brightness with a unique thickness, **empowering your every output.**

Navigator Platinum Digital offers **incredible results** and superior quality consistency over time, every time.



Advanced color printing paper

HIGH QUALITY FIBRE - By using the best quality fibre - *Eucalyptus globulus* - Navigator guarantees optimum paper characteristics for digital printing. It's smoother, more opaque and has an excellent thickness / stiffness ratio, which allows for jam-free printing and a better printing quality, even in duplex applications using color.

ENVIRONMENT - Our commitment is to the highest environmental standards and continuous improvement in our forest management practices. Our responsible forest stewardship ensures the renewable supply of *Eucalyptus globulus* fiber and the preservation of biodiversity.

ULTIMATE BRIGHTNESS:

GE Brightness 99 - ISO Brightness 112

CIE Brightness 169

MULTIFUNCTIONAL

100% SATISFACTION:

Product replacement guarantee.

ISO 14001, ISO 9001 AND ISO 9706

Premium aesthetics:

- Optimal toner/ ink adhesion
- High levels of sheet uniformity
- Accurate sheet dimension

Advanced color printing benefits:

- Full color spectrum
- Excellent contrast
- Sharp colors



Available in the following sizes:

20 lb 8 1/2 x 11" | 11x17" | 8 1/2 x 14" | A4

24 lb 8 1/2 x 11" | 11x17" | 12x18"

28 lb 8 1/2 x 11" | 11x17" | 12x18"

32 lb 8 1/2 x 11"



**DIGITAL
EXCELLENT
PERFORMANCE**