



Wiwax^{TM/MC}

Cleaning & Maintenance Emulsion

Wiwax^{TM/MC} Cleaning & Maintenance Emulsion is a unique blend of waxes, polymers and detergents to effectively clean and maintain rubber as well as linoleum, asphalt, marble, stone, concrete and slate flooring.

Features & Benefits

- Provides a clean floor with a shiny appearance
- An integral part of a comprehensive floor care program for cleaning, stripping and sealing rubber floors
- Provides protection when used on a regular basis

Applications

- For use as a rubber floor maintainer
- Can also be used on linoleum, asphalt, marble, stone, concrete and slate flooring
- Can be used for the rejuvenation, restoration and daily cleaning of stone and concrete flooring





Use Instructions

Automatic Scrubbing Machines

1. Dust mop or sweep.
2. Blockade areas to be cleaned. Floors will be very slippery until dry.
3. Add four (4) oz. per gallon (30mL per liter) of this product to lukewarm water. Scrub floor with product. Trail mop excessive wet areas behind scrubber. Do not rinse floor after cleaning.
4. Let floor dry completely.

Mop and Bucket Cleaning

1. Dust mop or sweep.
2. Blockade areas to be cleaned. Floors will be very slippery until dry.
3. Add two (2) oz. per gallon (15 mL per liter) of this product to lukewarm water. Mop floor clean with this product. Pick up soil and excess cleaner with a tightly wrung-out cleaning mop. Do not rinse floor after cleaning.
4. Let floor dry completely.

Stone/Concrete Floor Daily cleaning (Automatic Scrubbing Machine):

1. Dust mop or sweep floor.
2. Blockade areas to be cleaned. Floors will be very slippery until dry.
3. Add (1) oz. per gallon of this product to warm water. Scrub floor with product and TwisterTM Intellipad[®]. Trail mop excessive wet areas behind scrubber. Do not rinse floor after cleaning.
4. Let floor dry completely.

Stone/Concrete Floor Rejuvenation (Mop and Bucket method):

1. Dust mop or sweep floor.
2. Blockade areas to be cleaned. Floors will be very slippery until dry.
3. Clean floor with a neutral floor cleaner according to label directions.

4. Add thirteen (13) oz. per gallon (101 mL per liter) of this product to lukewarm water. Pick up soil and excess cleaner with a tightly wrung-out cleaning mop. Do not rinse floor after cleaning.
5. Let air dry.
6. For optimal gloss, burnish the floor with TwisterTM Intellipad[®].

Stone/Concrete Restoration:

1. Dust mop or sweep floor.
2. Blockade areas to be cleaned. Floors will be very slippery until dry.
3. Clean floor with a neutral floor cleaner according to label directions.
4. Dilute this product with lukewarm water at a 1:1 dilution ratio. Apply up to 2 coats using a string mop or flat mop until desired shine is achieved. Be sure to evenly cover the entire floor. Do not rinse floor after cleaning.
5. Let air dry.
6. For optimal gloss, burnish the floor with TwisterTM Intellipad[®].

Best Results

- Do not use on surfaces colder than 50°F/10°C.
- To avoid contamination, do not return unused product to original container.

Note: Floors will be slippery when wet or contaminated with foreign materials. Promptly clean-up spills and foreign materials. Not intended for use in outdoor areas. Meets ASTM D-2047 requirements for slip resistance. **Rubber Floors:** For optimum appearance, alternate use of this product at standard dilution and Profi^{TM/MC} Degreaser once desired shine is achieved. On heavily worn rubber floors apply up to three coats of Wiwax^{TM/MC} emulsion cleaner using the mop and bucket cleaning instructions with a 1:1 dilution ratio until desired shine is achieved. If high gloss is desired, apply instead, three coats of Carefree Floor Finish.

Technical data	Wiwax ^{TM/MC}
Color/Form	Milky white, liquid
pH	8.5 (Concentrate)
Scent	Characteristic
Shelf Life	2 Years

Product	Pack size	Dilution	Product code
Wiwax ^{TM/MC}	4 x 1 gal. / 3.78 L Containers	1:32, 1:64	94512767 

Safe handling

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use; and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDS are available online at www.diversey.com or by calling 888.352.2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate.