

Version 3.1

Revision Date 12/06/2016

Print Date 12/28/2017

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name	:	BZ7593 ZC HARDWOOD LAM CLN ZUHLF128 4/1G
Material number	:	0000000001041692
Manufacturer or supplier's o	leta	ils
Company	:	Zep Inc.
Address	:	1310 Seaboard Industrial Blvd., NW Atlanta, GA 30318
Telephone	:	404-352-1680

Emergency telephone numbers

For SDS Information	:	Compliance Services 1-877-428-9937
For a Medical Emergency	:	877-541-2016 Toll Free - All Calls Recorded
For a Transportation	:	CHEMTREC: 800-424-9300 - All Calls Recorded.
Emergency		In the District of Columbia 202-483-7616

Recommended use of the chemical and restrictions on use

Recommended use : Floor Care

SECTION 2. HAZARDS IDENTIFICATION

Emergency Overview

Appearance	liquid
Colour	colourless
Odour	pleasant

GHS Classification

Not a hazardous substance or mixture.

GHS label elements

Not a hazardous substance or mixture.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

Chemical name	CAS-No.	Concentration [%]
2-(2-butoxyethoxy)ethanol	112-34-5	>= 1 - < 5

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

General advice

: Do not leave the victim unattended.



rsion 3.1	Revision Date 12/06/2016	Print Date 12/28/2017
	Show this safety data sheet to the Move out of dangerous area. Do not leave the victim unattend	
If inhaled	: If unconscious place in recovery advice. If symptoms persist, call a physic	
In case of skin contact	: If on clothes, remove clothes. If skin irritation persists, call a ph Wash off immediately with plenty minutes.	
In case of eye contact	 Remove contact lenses. Protect unharmed eye. If eye irritation persists, consult a If in eyes, rinse with water for 15 	
If swallowed	 Keep respiratory tract clear. Never give anything by mouth to If symptoms persist, call a physic DO NOT induce vomiting unless physician or poison control center 	cian. s directed to do so by a
Most important symptoms and effects, both acute and delayed	: Effects may be delayed, sympto skin irritation. Overexposure may cause mild e	
Notes to physician	: Treat symptomatically. Symptor	ms may be delayed.

SECTION 5. FIREFIGHTING MEASURES

Suitable extinguishing media	:	Water spray jet Alcohol-resistant foam Carbon dioxide (CO2) Dry chemical
Unsuitable extinguishing media	:	High volume water jet
Specific hazards during firefighting	:	Do not allow run-off from fire fighting to enter drains or water courses.
Hazardous combustion products	:	Carbon dioxide (CO2) Carbon monoxide Smoke
Specific extinguishing methods	:	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Further information	:	Standard procedure for chemical fires. Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Special protective equipment for firefighters	:	Wear self-contained breathing apparatus for firefighting if necessary.



Version 3.1

Revision Date 12/06/2016

Print Date 12/28/2017

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures	: Ensure adequate ventilation. Use personal protective equipment. Evacuate personnel to safe areas.
Environmental precautions	 If the product contaminates rivers and lakes or drains inform respective authorities. Prevent further leakage or spillage if safe to do so. Prevent product from entering drains.
Methods and materials for containment and cleaning up	: Wipe up with absorbent material (e.g. cloth, fleece). Keep in suitable, closed containers for disposal.

SECTION 7. HANDLING AND STORAGE

Advice on safe handling	For personal protection see section 8. Smoking, eating and drinking should be prohibited application area.	n the
Conditions for safe storage	Electrical installations / working materials must com the technological safety standards. Keep in a dry, cool and well-ventilated place.	ply with
	Electrical installations / working materials must com the technological safety standards.	ply with
Materials to avoid	No materials to be especially mentioned.	

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
2-(2-butoxyethoxy)ethanol	112-34-5	TWA (Inhalable fraction and vapor)	10 ppm	ACGIH

Engineering measures : effective ventilation in all processing areas

Personal protective equipment

Respiratory protection : In case of insufficient ventilation, wear suitable respiratory equipment.

Hand protection



Version 3.1	Revision Date 12/06/2016	Print Date 12/28/2017
Remarks	: The suitability for a specific workpl with the producers of the protective	
Eye protection	: Safety glasses Eye wash bottle with pure water	
Skin and body protection	: Impervious clothing	
Hygiene measures	: General industrial hygiene practice	9.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	:	liquid
Colour	:	colourless
Odour	:	pleasant
Odour Threshold	:	No data available
рН	:	8.5 - 9.0
Melting point/freezing point	:	No data available
Boiling point	:	100 °C
Flash point	:	
		does not flash
Evaporation rate	:	1
Upper explosion limit	:	Not applicable
Lower explosion limit	:	Not applicable
Vapour pressure	:	not determined
Density	:	0.99 g/cm3
Solubility(ies)		
Water solubility	:	soluble
Partition coefficient: n- octanol/water	:	No data available
Auto-ignition temperature	:	not determined
Thermal decomposition	:	No data available
Viscosity		
Viscosity, kinematic	:	No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity

- : Stable
- Chemical stability : Stable under normal conditions.



Version 3.1	Revision Date 12/06/2016	Print Date 12/28/2017
Possibility of hazardous reactions	: Stable under recommended storage No hazards to be specially mention	
Conditions to avoid	: No data available	
Incompatible materials	: None.	
Hazardous decomposition products	: Carbon oxides	

SECTION 11. TOXICOLOGICAL INFORMATION

Potential Health Effects

Aggravated Medical Condition Symptoms of Overexposure	 None known. Effects may be delayed, symptoms may include minor eye or skin irritation.
Carcinogenicity:	
IARC	No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No component of this product present at levels greater than or

by NTP.

equal to 0.1% is identified as a known or anticipated carcinogen

Acute toxicity

No data available

Skin corrosion/irritation

No data available

Serious eye damage/eye irritation

No data available

Respiratory or skin sensitisation

No data available

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

2-(2-butoxyethoxy)ethanol:



Version 3.1

Revision Date 12/06/2016

Print Date 12/28/2017

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

No data available

Further information

Product:

Remarks: No data available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

No data available

Persistence and degradability

No data available Bioaccumulative potential

Product:

Partition coefficient: n- octanol/water	: Remarks: No data available
Components:	
2-(2-butoxyethoxy)ethanol :	
Partition coefficient: n-	: Pow: 1
octanol/water	

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation	40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances
Remarks	This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).
Additional ecological information	: No data available



Version 3.1

Revision Date 12/06/2016

Print Date 12/28/2017

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods	
Waste from residues	 Dispose of in accordance with local regulations. Do not contaminate ponds, waterways or ditches with chemical or used container. The product should not be allowed to enter drains, water courses or the soil.
Contaminated packaging	 Empty remaining contents. Do not re-use empty containers. Dispose of as unused product.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA): NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IMDG (Vessel): NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Cargo Air): NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Passenger Air): NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: TDG (Canada): NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

SECTION 15. REGULATORY INFORMATION

TSCA list

: No substances are subject to a Significant New Use Rule. No substances are subject to TSCA 12(b) export notification requirements.

EPCRA - Emergency Planning and Community Right-to-Know Act

CERCLA Reportable Quantity

This material does not contain any components with a CERCLA RQ.



Version 3.1	 Revision Date 12/06/2016	Print Date 12/28/2017

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.


SARA 311/312 Hazard	s : No SARA Hazards
SARA 302	: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.
SARA 313	: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.
California Prop 65	This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.
The components of this product are reported in the following inventories:	
TSCA DSL	On TSCA Inventory This product contains one or more components that are listed on the Canadian NDSL. All other components are on the Canadian DSL.

For information on the country notification status for other regions please contact the manufacturer's regulatory group.

Inventory Acronym and Validity Area Legend:

TSCA (USA), DSL (Canada), NDSL (Canada)

SECTION 16. OTHER INFORMATION



OSHA - GHS Label Information:

Not a hazardous substance or mixture.



Version 3.1

Revision Date 12/06/2016

Print Date 12/28/2017

Version:	3.1
Revision Date:	12/06/2016
Print Date:	12/28/2017

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®,Zep Professional®, Enforcer®, National Chemical[™], Selig[™], Misty®, Next Dimension[™], Petro®, i-Chem®, TimeMist®, TimeWick[™], MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National[™], FC Forward Chemicals®,Rexodan®, Mykal[™], and a number of private labeled brands.