

A07238 ZEP COM SMK ELM ZUSOE16 20N16 STK

Version 3.0

Revision Date 03/07/2017

Print Date 04/27/2017

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : A07238 ZEP COM SMK ELM ZUSOE16 20N16 STK

Material number : 00000000001044121

Manufacturer or supplier's details

Company : Zep Inc.

Address : 1310 Seaboard Industrial Blvd., NW
Atlanta, GA 30318

Telephone : 404-352-1680

Emergency telephone numbers
For SDS Information : Compliance Services 1-877-428-9937

For a Medical Emergency : 877-541-2016 Toll Free - All Calls Recorded

For a Transportation Emergency : CHEMTREC: 800-424-9300 - All Calls Recorded.
In the District of Columbia 202-483-7616

Recommended use of the chemical and restrictions on use

Recommended use : Air Care

Note: This product is labeled as a consumer product in accordance with the United States Consumer Product Safety Commission regulations. The warnings presented below in this Safety Data Sheet (SDS) comply with the 2012 OSHA Hazard Communication Standard (GHS - Globally Harmonized System of Classification and Labeling). The requirements for the labeling and warnings of consumer products may differ from those required for GHS based hazard communication.

SECTION 2. HAZARDS IDENTIFICATION
Emergency Overview

Appearance	Aerosol containing a liquefied gas
Colour	opaque
Odour	pleasant

GHS Classification

 Flammable aerosols : Category 2
 Gases under pressure : Liquefied gas
 Skin sensitisation : Category 1

GHS label elements

Hazard pictograms :



Signal word : Warning

 Hazard statements : H223 Flammable aerosol.
 H280 Contains gas under pressure; may explode if heated.
 H317 May cause an allergic skin reaction.

A07238 ZEP COM SMK ELM ZUSOE16 20N16 STK

Version 3.0

Revision Date 03/07/2017

Print Date 04/27/2017

Precautionary statements : **Prevention:**
 P210 Keep away from heat/sparks/open flames/hot surfaces. No smoking.
 P211 Do not spray on an open flame or other ignition source.
 P251 Pressurized container: Do not pierce or burn, even after use.
 P261 Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.
 P272 Contaminated work clothing should not be allowed out of the workplace.
 P280 Wear protective gloves.

Response:
 P302 + P352 IF ON SKIN: Wash with plenty of soap and water.
 P333 + P313 If skin irritation or rash occurs: Get medical advice/ attention.
 P363 Wash contaminated clothing before reuse.

Storage:
 P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.

Disposal:
 Dispose of contents/container in accordance with local regulation.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

Chemical name	CAS-No.	Concentration [%]
alkanes, C12-14-iso-	68551-19-9	>= 10 - < 20
butane	106-97-8	>= 10 - < 20
propane	74-98-6	>= 1 - < 5
dodecyl methacrylate	142-90-5	>= 1 - < 5
benzyl salicylate	118-58-1	>= 0.1 - < 1

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

General advice : Move out of dangerous area.
 Show this safety data sheet to the doctor in attendance.
 Do not leave the victim unattended.

If inhaled : If unconscious place in recovery position and seek medical advice.
 If symptoms persist, call a physician.

In case of skin contact : If skin irritation persists, call a physician.
 If on skin, rinse well with water.
 Wash off immediately with plenty of water for at least 15 minutes.

In case of eye contact : In case of contact, immediately flush eyes with plenty of water for at least 15 minutes.
 Remove contact lenses.

A07238 ZEP COM SMK ELM ZUSOE16 20N16 STK

Version 3.0

Revision Date 03/07/2017

Print Date 04/27/2017

- Protect unharmed eye.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
- If swallowed : DO NOT induce vomiting unless directed to do so by a physician or poison control center.
If a person vomits when lying on his back, place him in the recovery position.
If conscious, drink plenty of water.
- Most important symptoms and effects, both acute and delayed : Effects are immediate and delayed.
Symptoms may include irritation, redness, pain, and rash.
May cause an allergic skin reaction.
Review section 2 of SDS to see all potential hazards.
- Notes to physician : Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during firefighting : Do not allow run-off from fire fighting to enter drains or water courses.
- Hazardous combustion products : Carbon dioxide (CO₂)
Carbon monoxide
Smoke
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
- Further information : Collect contaminated fire extinguishing water separately. This must not be discharged into drains.
Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
For safety reasons in case of fire, cans should be stored separately in closed containments.
Use a water spray to cool fully closed containers.
- Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.
Ensure adequate ventilation.
Remove all sources of ignition.
Evacuate personnel to safe areas.
Beware of vapours accumulating to form explosive

A07238 ZEP COM SMK ELM ZUSOE16 20N16 STK

Version 3.0

Revision Date 03/07/2017

Print Date 04/27/2017

concentrations. Vapours can accumulate in low areas.

- Environmental precautions : Prevent product from entering drains.
Prevent further leakage or spillage if safe to do so.
If the product contaminates rivers and lakes or drains inform respective authorities.
- Methods and materials for containment and cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Sweep up or vacuum up spillage and collect in suitable container for disposal.

SECTION 7. HANDLING AND STORAGE

- Advice on safe handling : Avoid contact with skin and eyes.
For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Provide sufficient air exchange and/or exhaust in work rooms.
Dispose of rinse water in accordance with local and national regulations.
- Conditions for safe storage : BEWARE: Aerosol is pressurized. Keep away from direct sun exposure and temperatures over 50 °C. Do not open by force or throw into fire even after use. Do not spray on flames or red-hot objects.
No smoking.
Containers which are opened must be carefully resealed and kept upright to prevent leakage.
Observe label precautions.
Keep in a dry, cool and well-ventilated place.
Electrical installations / working materials must comply with the technological safety standards.
- Materials to avoid : Oxidizing agents

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
butane	106-97-8	TWA	800 ppm 1,900 mg/m ³	NIOSH REL
		TWA	800 ppm 1,900 mg/m ³	OSHA P0
		PEL	800 ppm 1,900 mg/m ³	CAL PEL
propane	74-98-6	TWA	1,000 ppm	ACGIH
		TWA	1,000 ppm 1,800 mg/m ³	NIOSH REL
		TWA	1,000 ppm	OSHA Z-1

SAFETY DATA SHEET



A07238 ZEP COM SMK ELM ZUSOE16 20N16 STK

Version 3.0

Revision Date 03/07/2017

Print Date 04/27/2017

			1,800 mg/m3	
		TWA	1,000 ppm 1,800 mg/m3	OSHA P0
		PEL	1,000 ppm 1,800 mg/m3	CAL PEL

Engineering measures : effective ventilation in all processing areas

Personal protective equipment

Respiratory protection : Use respiratory protection unless adequate local exhaust ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.

Hand protection

Material

Remarks

: Protective gloves

: The suitability for a specific workplace should be discussed with the producers of the protective gloves.

Eye protection

: Safety glasses

Eye wash bottle with pure water

Skin and body protection

: Impervious clothing

Choose body protection according to the amount and concentration of the dangerous substance at the work place.

Hygiene measures

: When using do not eat or drink.

When using do not smoke.

Wash hands before breaks and at the end of workday.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : Aerosol containing a liquefied gas

Colour : opaque

Odour : pleasant

pH : Not applicable

Melting point/freezing point : Not applicable

Boiling point : not determined

Flash point :

No data available

Evaporation rate

: < 1

Flammability (solid, gas)

: Flammable aerosol.

Vapour pressure

: No data available

Density

: 0.92 g/cm3

Solubility(ies)

Water solubility

: soluble in hot water, soluble in cold water

A07238 ZEP COM SMK ELM ZUSOE16 20N16 STK

Version 3.0

Revision Date 03/07/2017

Print Date 04/27/2017

Solubility in other solvents	: slightly soluble
Partition coefficient: n-octanol/water	: No data available
Auto-ignition temperature	: not determined
Thermal decomposition	: No data available
Viscosity	
Viscosity, kinematic	: No data available
Heat of combustion	: > 20 kJ/g

SECTION 10. STABILITY AND REACTIVITY

Reactivity	: Stable
Chemical stability	: Stable under normal conditions.
Possibility of hazardous reactions	: Vapours may form explosive mixture with air. No decomposition if stored and applied as directed.
Conditions to avoid	: Heat, flames and sparks. Extremes of temperature and direct sunlight.
Incompatible materials	: Oxidizing agents
Hazardous decomposition products	: Carbon oxides

SECTION 11. TOXICOLOGICAL INFORMATION**Potential Health Effects**

Aggravated Medical Condition	: None known.
Symptoms of Overexposure	: Effects are immediate and delayed. Symptoms may include irritation, redness, pain, and rash.

Carcinogenicity:

IARC	No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
ACGIH	No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.
OSHA	No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

A07238 ZEP COM SMK ELM ZUSOE16 20N16 STK

Version 3.0

Revision Date 03/07/2017

Print Date 04/27/2017

NTP

No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Acute toxicity**Components:****butane:**

Acute inhalation toxicity : LC50 Mouse: 1,237 mg/l
Exposure time: 2 h

LC50 Rat: 1,355 mg/l

propane:

Acute inhalation toxicity : LC50 Mouse: 1,237 mg/l
Exposure time: 2 h

LC50 Rat: 658 mg/l
Exposure time: 4 h

LC50 Rat: 1,355 mg/l

benzyl salicylate:

Acute oral toxicity : LD50 Oral Rat: 2,227 mg/kg

Skin corrosion/irritation**Product:**

Remarks: May cause skin irritation and/or dermatitis.

Serious eye damage/eye irritation**Product:**

Remarks: May irritate eyes.

Respiratory or skin sensitisation**Product:**

Remarks: Causes sensitisation.

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

alkanes, C12-14-iso-:**butane:****propane:**

A07238 ZEP COM SMK ELM ZUSOE16 20N16 STK

Version 3.0

Revision Date 03/07/2017

Print Date 04/27/2017

dodecyl methacrylate:
benzyl salicylate:

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

No data available

Further information**Product:**

Remarks: No data available

SECTION 12. ECOLOGICAL INFORMATION**Ecotoxicity**

No data available

Persistence and degradability

No data available

Bioaccumulative potential**Product:**Partition coefficient: n-
octanol/water : Remarks: No data available**Components:****butane :**
Partition coefficient: n-
octanol/water : Pow: 2.89**Mobility in soil**

No data available

Other adverse effects

No data available

Product:Regulation 40 CFR Protection of Environment; Part 82 Protection of
Stratospheric Ozone - CAA Section 602 Class I
SubstancesRemarks This product neither contains, nor was manufactured
with a Class I or Class II ODS as defined by the U.S.
Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A
+ B).Additional ecological : An environmental hazard cannot be excluded in the
information event of unprofessional handling or disposal., Harmful to

A07238 ZEP COM SMK ELM ZUSOE16 20N16 STK

Version 3.0

Revision Date 03/07/2017

Print Date 04/27/2017

aquatic life with long lasting effects.

SECTION 13. DISPOSAL CONSIDERATIONS**Disposal methods**

- Waste from residues : The product should not be allowed to enter drains, water courses or the soil.
Do not contaminate ponds, waterways or ditches with chemical or used container.
Dispose of in accordance with local regulations.
- Contaminated packaging : Empty remaining contents.
Dispose of as unused product.
Do not re-use empty containers.
Do not burn, or use a cutting torch on, the empty drum.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
ORM-D, CONSUMER COMMODITY

Transportation Regulation: IMDG (Vessel):
UN1950, AEROSOLS, 2.1, - Limited quantity

Transportation Regulation: IATA (Cargo Air):
UN1950, Aerosols, flammable, 2.1, - Limited quantity

Transportation Regulation: IATA (Passenger Air):
UN1950, Aerosols, flammable, 2.1, - Limited quantity

Transportation Regulation: TDG (Canada):
UN1950, AEROSOLS, 2.1, - Limited quantity

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

SECTION 15. REGULATORY INFORMATION

- TSCA list** : No substances are subject to a Significant New Use Rule.
No substances are subject to TSCA 12(b) export notification requirements.

EPCRA - Emergency Planning and Community Right-to-Know Act

CERCLA Reportable Quantity

A07238 ZEP COM SMK ELM ZUSOE16 20N16 STK

Version 3.0

Revision Date 03/07/2017

Print Date 04/27/2017

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Fire Hazard
Sudden Release of Pressure Hazard
Acute Health Hazard

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop 65 This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

TSCA On TSCA Inventory
DSL All components of this product are on the Canadian DSL

For information on the country notification status for other regions please contact the manufacturer's regulatory group.


Inventory Acronym and Validity Area Legend:

TSCA (USA), DSL (Canada), NDSL (Canada)

SECTION 16. OTHER INFORMATION

Further information

NFPA:



HMIS III:

HEALTH	3
FLAMMABILITY	3
PHYSICAL HAZARD	2

0 = not significant, 1 = Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA - GHS Label Information:

A07238 ZEP COM SMK ELM ZUSOE16 20N16 STK

Version 3.0

Revision Date 03/07/2017

Print Date 04/27/2017

Hazard pictograms



Signal word

: **Warning:**

Hazard statements

: Flammable aerosol. Contains gas under pressure; may explode if heated. May cause an allergic skin reaction.

Precautionary statements

: **Prevention:** Keep away from heat/sparks/open flames/hot surfaces. No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves.**Response:** IF ON SKIN: Wash with plenty of soap and water. If skin irritation or rash occurs: Get medical advice/ attention. Wash contaminated clothing before reuse.**Storage:** Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.**Disposal:** Dispose of contents/container in accordance with local regulation.

Version:	3.0
Revision Date:	03/07/2017
Print Date:	04/27/2017

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®, Zep Professional®, Enforcer®, National Chemical™, Selig™, Misty®, Next Dimension™, Petro®, i-Chem®, TimeMist®, TimeWick™, MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National™, FC Forward Chemicals®, Rexodan®, Mykal™, and a number of private labeled brands.