



TRADITION™ UPRIGHT

SC899F

MENU

Wide path (16") TRADITION™ upright designed with a chrome hood for added durability in the toughest environments. Lowers cost of ownership with a 2,000 hour motor, shake out bag and chrome brushroll with replaceable bristle strips. Quick Kleen™ fan chamber helps diagnose and clear clogs for easy maintenance. Increase productivity with less downtime with a large-capacity, 18-qt. shake out bag and 50-foot cord.

<p>16" WIDE AREA CLEANING</p>	<p>BUILT TO LAST</p>	<p>COST OF OWNERSHIP</p>
<p>>2,000 HOURS MOTOR LIFE</p>	<p>LOW MAINTENANCE COSTS</p>	

SPECIFICATIONS			
MFG#	SC899F	CLEANING WIDTH	16"
MOTOR	7 amp	CORD LENGTH	50'
CFM	145	SOUND	79 dBA
FILTRATION	n/a	BRUSH ROLL	53273
DUST CONTAINMENT	Shake Out Bag	BELT	52100C-12
DUST CAPACITY	18 qt.	CLEANING TOOLS	n/a
PACKAGING			
UPC	0 23169 12644 2	PACKAGE WEIGHT	22 lbs.
PRODUCT WEIGHT	18 lbs.	PACKAGE DIMENSIONS	20.25" x 16.5" x 10"
WARRANTY	2 Years - Parts & Labor		