



## Safety Data Sheet

Copyright, 2016, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

<b>Document Group:</b>	10-2819-0	<b>Version Number:</b>	25.00
<b>Issue Date:</b>	02/18/16	<b>Supersedes Date:</b>	07/21/14

### SECTION 1: Identification

#### 1.1. Product identifier

3M™ Stainless Steel Cleaner & Polish

#### Product Identification Numbers

ID Number	UPC	ID Number	UPC
61-5000-6132-2	000-48011-14002-0	70-0713-1355-8	000-48011-59158-2
70-0713-1493-7	000-48011-59249-7		

#### 1.2. Recommended use and restrictions on use

##### Recommended use

Metal Polish, Cleans and polishes stainless steel, chrome, aluminum and laminated plastic surfaces.

#### 1.3. Supplier's details

<b>MANUFACTURER:</b>	3M
<b>DIVISION:</b>	Commercial Solutions Division
<b>ADDRESS:</b>	3M Center, St. Paul, MN 55144-1000, USA
<b>Telephone:</b>	1-888-3M HELPS (1-888-364-3577)

#### 1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

### SECTION 2: Hazard identification

#### 2.1. Hazard classification

Flammable Aerosol: Category 1.

Gas Under Pressure: Liquefied gas.

Specific Target Organ Toxicity (single exposure): Category 1.

#### 2.2. Label elements

##### Signal word

Danger

##### Symbols

Flame | Health Hazard |

##### Pictograms



**Hazard Statements**

Extremely flammable aerosol.  
 Contains gas under pressure; may explode if heated.

Causes damage to organs:  
 cardiovascular system |

**Precautionary Statements**

**General:**

Keep out of reach of children.

**Prevention:**

Keep away from heat/sparks/open flames/hot surfaces. - No smoking.  
 Do not spray on an open flame or other ignition source.  
 Pressurized container: Do not pierce or burn, even after use.  
 Do not breathe dust/fume/gas/mist/vapors/spray.  
 Do not eat, drink or smoke when using this product.  
 Wash thoroughly after handling.

**Response:**

IF exposed: Call a POISON CENTER or doctor/physician.  
 Specific treatment (see Notes to Physician on this label).

**Storage:**

Protect from sunlight. Do not expose to temperatures exceeding 50C/122F.  
 Store in a well-ventilated place.  
 Store locked up.

**Disposal:**

Dispose of contents/container in accordance with applicable local/regional/national/international regulations.

**Notes to Physician:**

Exposure may increase myocardial irritability. Do not administer sympathomimetic drugs unless absolutely necessary.

**2.3. Hazards not otherwise classified**

Intentional misuse by deliberately concentrating and inhaling contents can be harmful or fatal.

12% of the mixture consists of ingredients of unknown acute dermal toxicity.  
 35% of the mixture consists of ingredients of unknown acute inhalation toxicity.

**SECTION 3: Composition/information on ingredients**

Ingredient	C.A.S. No.	% by Wt
WATER	7732-18-5	40 - 70 Trade Secret *
WHITE MINERAL OIL (PETROLEUM)	8042-47-5	10 - 30 Trade Secret *
ISOBUTANE	75-28-5	7 - 13 Trade Secret *
SORBITAN OLEATE	1338-43-8	0.5 - 1.5 Trade Secret *
ETHANOLAMINE	141-43-5	0.1 - 1 Trade Secret *

\*The specific chemical identity and/or exact percentage (concentration) of this composition has been withheld as a trade secret.

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

**Inhalation:**

Remove person to fresh air. Get medical attention.

**Skin Contact:**

Wash with soap and water. If you feel unwell, get medical attention.

**Eye Contact:**

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

**If Swallowed:**

Rinse mouth. If you feel unwell, get medical attention.

### 4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

### 4.3. Indication of any immediate medical attention and special treatment required

Exposure may increase myocardial irritability. Do not administer sympathomimetic drugs unless absolutely necessary.

## SECTION 5: Fire-fighting measures

### 5.1. Suitable extinguishing media

Use a fire fighting agent suitable for the surrounding fire.

### 5.2. Special hazards arising from the substance or mixture

Closed containers exposed to heat from fire may build pressure and explode.

### Hazardous Decomposition or By-Products

Substance

Carbon monoxide

Carbon dioxide

Condition

During Combustion

During Combustion

### 5.3. Special protective actions for fire-fighters

No special protective actions for fire-fighters are anticipated.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Evacuate area. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Use only non-sparking tools. Ventilate the area with fresh air. Warning! A motor could be an ignition source and could cause flammable gases or vapors in the spill area to burn or explode. Refer to other sections of this SDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment.

### 6.2. Environmental precautions

Avoid release to the environment.

**6.3. Methods and material for containment and cleaning up**

If possible, seal leaking container. Place leaking containers in a well-ventilated area, preferably an operating exhaust hood, or if necessary outdoors on an impermeable surface until appropriate packaging for the leaking container or its contents is available. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Remember, adding an absorbent material does not remove a physical, health, or environmental hazard. Collect as much of the spilled material as possible using non-sparking tools. Place in a closed container approved for transportation by appropriate authorities. Clean up residue with water. Seal the container. Dispose of collected material as soon as possible.

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

Do not use in a confined area with minimal air exchange. Keep out of reach of children. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use. Do not breathe dust/fume/gas/mist/vapors/spray. Do not get in eyes, on skin, or on clothing. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Avoid contact with oxidizing agents (eg. chlorine, chromic acid etc.)

**7.2. Conditions for safe storage including any incompatibilities**

Protect from sunlight. Do not expose to temperatures exceeding 50C/122F. Store away from heat. Store away from acids. Store away from oxidizing agents.

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Occupational exposure limits**

If a component is disclosed in section 3 but does not appear in the table below, an occupational exposure limit is not available for the component.

Ingredient	C.A.S. No.	Agency	Limit type	Additional Comments
ETHANOLAMINE	141-43-5	ACGIH	TWA:3 ppm;STEL:6 ppm	
ETHANOLAMINE	141-43-5	OSHA	TWA:6 mg/m3(3 ppm)	
ISOBUTANE	75-28-5	ACGIH	STEL:1000 ppm	
Natural gas	75-28-5	ACGIH	Limit value not established:	
MINERAL OILS, HIGHLY-REFINED OILS	8042-47-5	ACGIH	TWA(inhalable fraction):5 mg/m3	A4: Not class. as human carcin
Paraffin oil	8042-47-5	OSHA	TWA(as mist):5 mg/m3	

ACGIH : American Conference of Governmental Industrial Hygienists

AIHA : American Industrial Hygiene Association

CMRG : Chemical Manufacturer's Recommended Guidelines

OSHA : United States Department of Labor - Occupational Safety and Health Administration

TWA: Time-Weighted-Average

STEL: Short Term Exposure Limit

CEIL: Ceiling

**8.2. Exposure controls****8.2.1. Engineering controls**

Do not remain in area where available oxygen may be reduced. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapors/spray. If ventilation is not adequate, use respiratory protection equipment.

**8.2.2. Personal protective equipment (PPE)****Eye/face protection**

Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:  
Safety Glasses with side shields

#### Skin/hand protection

Select and use gloves and/or protective clothing approved to relevant local standards to prevent skin contact based on the results of an exposure assessment. Selection should be based on use factors such as exposure levels, concentration of the substance or mixture, frequency and duration, physical challenges such as temperature extremes, and other use conditions. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible gloves/protective clothing. No chemical protective gloves are required.

Gloves made from the following material(s) are recommended: Nitrile Rubber

#### Respiratory protection

None required.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

<b>General Physical Form:</b>	Liquid
<b>Specific Physical Form:</b>	Aerosol
<b>Odor, Color, Grade:</b>	Thick white emulsion citrus odor
<b>Odor threshold</b>	<i>No Data Available</i>
<b>pH</b>	9 - 11
<b>Melting point</b>	<i>Not Applicable</i>
<b>Boiling Point</b>	> 212 °F
<b>Flash Point</b>	No flash point
<b>Evaporation rate</b>	<i>No Data Available</i>
<b>Flammability (solid, gas)</b>	Not Applicable
<b>Flammable Limits(LEL)</b>	<i>No Data Available</i>
<b>Flammable Limits(UEL)</b>	<i>No Data Available</i>
<b>Vapor Pressure</b>	<i>No Data Available</i>
<b>Vapor Density</b>	<i>No Data Available</i>
<b>Density</b>	0.95 g/ml
<b>Specific Gravity</b>	0.92 - 0.98 [ <i>Ref Std: WATER=1</i> ]
<b>Solubility in Water</b>	Complete
<b>Solubility- non-water</b>	<i>No Data Available</i>
<b>Partition coefficient: n-octanol/ water</b>	<i>No Data Available</i>
<b>Autoignition temperature</b>	<i>No Data Available</i>
<b>Decomposition temperature</b>	<i>No Data Available</i>
<b>Viscosity</b>	1,400 - 4,500 centipoise [ <i>Details: For Liquid</i> ]
<b>Molecular weight</b>	<i>No Data Available</i>
<b>Volatile Organic Compounds</b>	10 - 12 % weight [ <i>Test Method: calculated per CARB title 2</i> ]
<b>Percent volatile</b>	75 - 80 % weight
<b>VOC Less H2O &amp; Exempt Solvents</b>	265 - 295 g/l [ <i>Test Method: calculated per CARB title 2</i> ]

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

This material is considered to be non reactive under normal use conditions.

### 10.2. Chemical stability

Stable.

### 10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

#### 10.4. Conditions to avoid

Heat  
Sparks and/or flames

#### 10.5. Incompatible materials

Strong oxidizing agents  
Strong acids

#### 10.6. Hazardous decomposition products

<u>Substance</u>	<u>Condition</u>
None known.	

Refer to section 5.2 for hazardous decomposition products during combustion.

## SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

### 11.1. Information on Toxicological effects

#### Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

#### Inhalation:

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

May cause additional health effects (see below).

#### Skin Contact:

Contact with the skin during product use is not expected to result in significant irritation.

#### Eye Contact:

Contact with the eyes during product use is not expected to result in significant irritation.

#### Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

#### Additional Health Effects:

#### Single exposure may cause target organ effects:

Cardiac Sensitization: Signs/symptoms may include irregular heartbeat (arrhythmia), faintness, chest pain, and may be fatal.

#### Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

**Acute Toxicity**

Name	Route	Species	Value
Overall product	Dermal		No data available; calculated ATE > 5,000 mg/kg
Overall product	Inhalation-Dust/Mist(4 hr)		No data available; calculated ATE > 12.5 mg/l
Overall product	Ingestion		No data available; calculated ATE > 5,000 mg/kg
WHITE MINERAL OIL (PETROLEUM)	Dermal	Rabbit	LD50 > 2,000 mg/kg
WHITE MINERAL OIL (PETROLEUM)	Ingestion	Rat	LD50 > 5,000 mg/kg
ISOBUTANE	Inhalation-Gas (4 hours)	Rat	LC50 276,000 ppm
SORBITAN OLEATE	Dermal		LD50 estimated to be > 5,000 mg/kg
SORBITAN OLEATE	Ingestion	Rat	LD50 > 39,800 mg/kg
ETHANOLAMINE	Inhalation-Vapor	official classification	LC50 estimated to be 10 - 20 mg/l
ETHANOLAMINE	Dermal	Rabbit	LD50 1,000 mg/kg
ETHANOLAMINE	Ingestion	Rat	LD50 1,720 mg/kg

ATE = acute toxicity estimate

**Skin Corrosion/Irritation**

Name	Species	Value
WHITE MINERAL OIL (PETROLEUM)	Rabbit	No significant irritation
ISOBUTANE	Professional judgement	No significant irritation
ETHANOLAMINE	Rabbit	Corrosive

**Serious Eye Damage/Irritation**

Name	Species	Value
WHITE MINERAL OIL (PETROLEUM)	Rabbit	Mild irritant
ISOBUTANE	Professional judgement	No significant irritation
ETHANOLAMINE	Rabbit	Corrosive

**Skin Sensitization**

Name	Species	Value
WHITE MINERAL OIL (PETROLEUM)	Guinea pig	Not sensitizing
ETHANOLAMINE	Guinea pig	Some positive data exist, but the data are not sufficient for classification

**Respiratory Sensitization**

For the component/components, either no data are currently available or the data are not sufficient for classification.

**Germ Cell Mutagenicity**

Name	Route	Value
WHITE MINERAL OIL (PETROLEUM)	In Vitro	Not mutagenic
ISOBUTANE	In Vitro	Not mutagenic
ETHANOLAMINE	In Vitro	Not mutagenic
ETHANOLAMINE	In vivo	Not mutagenic

**Carcinogenicity**

Name	Route	Species	Value
WHITE MINERAL OIL (PETROLEUM)	Dermal	Mouse	Not carcinogenic

WHITE MINERAL OIL (PETROLEUM)	Inhalation	Multiple animal species	Not carcinogenic
-------------------------------	------------	-------------------------	------------------

## Reproductive Toxicity

### Reproductive and/or Developmental Effects

Name	Route	Value	Species	Test Result	Exposure Duration
WHITE MINERAL OIL (PETROLEUM)	Ingestion	Not toxic to female reproduction	Rat	NOAEL 4,350 mg/kg/day	13 weeks
WHITE MINERAL OIL (PETROLEUM)	Ingestion	Not toxic to male reproduction	Rat	NOAEL 4,350 mg/kg/day	13 weeks
WHITE MINERAL OIL (PETROLEUM)	Ingestion	Not toxic to development	Rat	NOAEL 4,350 mg/kg/day	during gestation
ETHANOLAMINE	Dermal	Not toxic to development	Rat	NOAEL 225 mg/kg/day	during organogenesis
ETHANOLAMINE	Ingestion	Not toxic to development	Rat	NOAEL 616 mg/kg/day	during organogenesis

## Target Organ(s)

### Specific Target Organ Toxicity - single exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
ISOBUTANE	Inhalation	cardiac sensitization	Causes damage to organs	Multiple animal species	NOAEL Not available	
ISOBUTANE	Inhalation	central nervous system depression	May cause drowsiness or dizziness	Human and animal	NOAEL Not available	
ISOBUTANE	Inhalation	respiratory irritation	All data are negative	Mouse	NOAEL Not available	
ETHANOLAMINE	Inhalation	respiratory irritation	May cause respiratory irritation	Human and animal	NOAEL Not available	

### Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
WHITE MINERAL OIL (PETROLEUM)	Ingestion	hematopoietic system	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 1,381 mg/kg/day	90 days
WHITE MINERAL OIL (PETROLEUM)	Ingestion	liver   immune system	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 1,336 mg/kg/day	90 days
ISOBUTANE	Inhalation	kidney and/or bladder	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 4,500 ppm	13 weeks
ETHANOLAMINE	Inhalation	liver   kidney and/or bladder   respiratory system	Some positive data exist, but the data are not sufficient for classification	Multiple animal species	NOAEL 0.656 mg/l	5 weeks
ETHANOLAMINE	Ingestion	hematopoietic system   liver   kidney and/or bladder   respiratory system	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL Not available	

## Aspiration Hazard

Name	Value
WHITE MINERAL OIL (PETROLEUM)	Aspiration hazard



Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

## SECTION 12: Ecological information

### Ecotoxicological information

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

### Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

## SECTION 13: Disposal considerations

### 13.1. Disposal methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Incinerate in a permitted waste incineration facility. As a disposal alternative, utilize an acceptable permitted waste disposal facility. Facility must be capable of handling aerosol cans. Empty drums/barrels/containers used for transporting and handling hazardous chemicals (chemical substances/mixtures/preparations classified as Hazardous as per applicable regulations) shall be considered, stored, treated & disposed of as hazardous wastes unless otherwise defined by applicable waste regulations. Consult with the respective regulating authorities to determine the available treatment and disposal facilities.

EPA Hazardous Waste Number (RCRA): Not regulated

## SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

## SECTION 15: Regulatory information

### 15.1. US Federal Regulations

#### 311/312 Hazard Categories:

Fire Hazard - Yes Pressure Hazard - Yes Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - No

### 15.2. State Regulations

### 15.3. Chemical Inventories

The components of this material are in compliance with the provisions of Australia National Industrial Chemical Notification and Assessment Scheme (NICNAS). Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the new substance notification requirements of CEPA.

The components of this material are in compliance with the China "Measures on Environmental Management of New Chemical Substance". Certain restrictions may apply. Contact the selling division for additional information.

The components of this material are in compliance with the provisions of the Korean Toxic Chemical Control Law. Certain restrictions may apply. Contact the selling division for additional information.

The components of this material are in compliance with the provisions of Japan Chemical Substance Control Law. Certain restrictions may apply. Contact the selling division for additional information.

The components of this material are in compliance with the provisions of Philippines RA 6969 requirements. Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the chemical notification requirements of TSCA.

This product complies with the New Zealand Hazardous Substances and New Organisms Act (1996).

## 15.4. International Regulations

This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

## SECTION 16: Other information

### NFPA Hazard Classification

**Health: 1 Flammability: 3 Instability: 0 Special Hazards: None**  
**Aerosol Storage Code: 1**

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

### HMIS Hazard Classification

**Health: 1 Flammability: 3 Physical Hazard: 0 Personal Protection: X - See PPE section.**

Hazardous Material Identification System (HMIS® IV) hazard ratings are designed to inform employees of chemical hazards in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® IV ratings are to be used with a fully implemented HMIS® IV program. HMIS® is a registered mark of the American Coatings Association (ACA).

<b>Document Group:</b>	10-2819-0	<b>Version Number:</b>	25.00
<b>Issue Date:</b>	02/18/16	<b>Supersedes Date:</b>	07/21/14

**DISCLAIMER:** The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M

3M USA SDSs are available at [www.3M.com](http://www.3M.com)