SAFETY DATA SHEET

Transmacro Amenities
9595 Six Pines Dr. Suite 8210
The Woodlands, TX 77380, USA
EMERGENCY PHONE NUMBER: +1 281 444 7240

Product name: Good Day Bar Soap with PCMX

Product code: PX400150 Review date: 03/05/2020

SDS number: 2020/160 Version: 1

SECTION 1. Product And Company Identification:

Product Name: Good Day Bar Soap with PCMX

Manufacture Identification number: 913210160710245793

Manufacture Company name: Yangzhou Dingji Tourist Products Factory

Manufacture Address: No.7 Weiye RD, Hangji Industrial Park, Yangzhou City, Jiangsu Province,

P.R. China

Telephone number for product safety: 86-514-82084233

Fax :

Name of preparer : Shengli Ji / Director of Lab

SECTION 2. Hazard Identification

EMERGENCY OVERVIEW

CAUTION: This product is a white or light colored soap-based bar with a pleasant fragrance. Direct contact with eyes may cause eye irritation. Repeated or prolonged excessive exposure with skin may cause irritation. No significant environmental effects. Not a fire hazard. Product is stable.

This product is labeled in accordance with guidelines set forth in the Food, Drug, and Cosmetic Act. The use pattern and exposure in the workplace are generally not consistent with those experienced by consumers. The requirements of the Occupational Safety and Health Administration applicable to this Material Safety Data Sheet may differ from the requirements of the FD&C Act and as a result, this MSDS may contain additional health hazard information not pertinent to consumer use and not found on the product label.

REGULATORY STATUS

While this product is not considered to be hazardous under OSHA's Hazard Communication Standard (29 CFR 1900.1200), this MSDS includes valuable information that is critical for safe handling and proper use of this product. This MSDS should be retained and available for employees and other users of this product.

POTENTIAL HEALTH EFFECTS

NOTE: The acute health effects described below are those which could potentially occur for the finished product. They are based on the toxicology information available for the finished product and/or each hazardous ingredient, and are consistent with the product type and the

likelihood of a specific route of exposure. Known chronic health effects related to exposure to a specific ingredient are indicated.

EYE CONTACT: This product may cause irritation with stinging, tearing, and redness.

SKIN CONTACT: Repeated or prolonged excessive exposure may cause irritation.

INGESTION: May cause mild gastrointestinal irritation with nausea, vomiting, diarrhea and abdominal pain.

INHALATION: Dust may cause mucous membrane irritation with sore throat, sneezing, coughing and shortness of breath.

CHRONIC HEALTH EFFECTS: None known.

MEDICAL CONDITIONS GENERALLY RECOGNIZED AS BEING AGGRAVATED BY

EXPOSURE: Pre-existing skin conditions.

POTENTIAL ENVIRONMENTAL EFFECTS

See Section 11: Ecological Information.

SECTION 3. Composition/Information on Ingredients

Based on our hazard evaluation, the following chemical substance(s) in this product have been identified as hazardous.

<u>INGREDIENT</u>	CAS NUMBER	PERCENT (w/w)
Sodium Soap	67701-11-5 & 67701-10-4	60 – 100 %
Glycerin	56-81-5	1 – 5 %
PCMX(Chloroxylenol)	88-04-0	0.2 %

SECTION 4. First Aid Measures

EYES: Rinse eyes immediately with plenty of water, occasionally lifting upper and lower lids, until no evidence of product remains. Get medical attention if pain or irritation persists.

SKIN: Rinse affected area with plenty of water until no evidence of product remains. Get medical attention if irritation persists.

INGESTION: Treat symptomatically and supportively. Maintain airway and respiration. If vomiting occurs, keep head below hips to prevent aspiration. Dilution by rinsing the mouth and giving water or milk to drink is generally recommended. If unconscious, the victim should not be given anything to drink. Contact physician or local poison control center.

INHALATION: Remove from exposure area to fresh air. Keep affected person warm and at rest. Treat symptomatically and supportively. Contact physician or local poison control center. If breathing has stopped, give artificial respiration, and get medical attention immediately.

NOTE TO PHYSICIAN: The physician's judgment should be used to control symptoms and clinical condition based on the individual reactions of the patient.

SECTION 5. Fire - Fighting Measures

FLAMMABLE PROPERTIES

OSHA FLAMMABILITY CLASSIFICATION: Not applicable FLASH POINT: None

UPPER FLAMMABILITY LIMIT: Not applicable LOWER FLAMMABILITY LIMIT: Not

applicable

AUTO-IGNITION TEMPERATURE: Not applicable

FIRE AND EXPLOSION HAZARD: The fire hazard for this product has not been determined. The hazard(s) of the component(s) with the most severe hazard(s) are: Slight fire hazard when exposed to heat or flame. Dust - air mixtures may ignite or explode.

HAZARDOUS DECOMPOSITION PRODUCTS: Thermal decomposition may release toxic and/or hazardous gases.

EXTINGUISHING MEDIA

Dry chemical, carbon dioxide, water spray or regular foam. For larger fires, use water spray, fog or regular foam.

PROTECTION OF FIREFIGHTERS

In case of fire, wear a full-face positive-pressure self-contained breathing apparatus and protective suit. Move container from fire area if you can do it without risk. Do not scatter spilled material with high-pressure water streams. Dike fire-control water for later disposal. Use agents suitable for type of surrounding fire. Avoid breathing vapors, keep upwind.

SECTION 6. Accidental Release Measures

PERSONAL PRECAUTIONS

Wear skin, eye and respiratory protection as recommended in Section 8. Stop or reduce any leaks if it is safe to do so. Spills present a slipping hazard. Keep unnecessary personnel away. Ventilate spill area if possible. Ensure clean-up is conducted by trained personnel only. Make sure area is slip-free before re-opening to traffic.

ENVIRONMENTAL PRECAUTIONS

Small or household quantities may be disposed in regular domestic trash. For larger quantities check with your local disposal authorities.

METHODS FOR CONTAINMENT AND CLEAN UP

SMALL SPILLS: Sweep or scoop up and place into suitable clean, dry containers for reclamation or later disposal. Wash site of spillage thoroughly with water. LARGE SPILLS: Sweep or scoop up. Dispose in suitable waste container. Keep unnecessary people away from spill.

SECTION 7. Handling And Storage

HANDLING:

Do not get in eyes. Do not take internally. Use with adequate ventilation. Keep the containers closed when not in use.

STORAGE:

Store in original containers in a cool dry area. Store away from excessive heat and incompatible substances. Storage areas for large quantities (warehouse) should be well ventilated. Keep the containers tightly closed when not in use.

SECTION 8. Exposure Controls / Personal Protection

This product is a personal care or cosmetic product. The use of this product by consumers is safe under normal and reasonable foreseen use. The information provided below refers to the occupational settings.

WORKER EXPOSURE LIMITS

The following exposure limits exist for the ingredients listed below. The TLV-TWA is the ACGIH Threshold Limit Value – Time Weighted Average. TLV-Ceiling Limit is the ACGIH Threshold Limit Value – Ceiling Limit. PEL-TWA is the OSHA Permissible Exposure Limit.

INGREDIENT CAS NUMBER EXPOSURE LIMIT

Soap Dust = Particles 67701-11-5 & 67701- TLV-TWA: 10 mg/m³ (total dust), TLV-TWA: 3 mg/m³ (respirable Not Otherwise 10-4 fraction), PEL-TWA: 15 mg/m³ (total dust), PEL-TWA: 5 mg/m³

Specified: (respirable fraction),

Glycerin (as mist) 56-81-5 TLV-TWA: 10 mg/m³ (mist), PEL-TWA: 5 mg/m³ (respirable fraction);

15 mg/m³ (total mist)

ENGINEERING CONTROLS: Provide local exhaust or general dilution ventilation to keep exposure to airborne contaminants below the permissible exposure limits where mists or vapors may be generated.

RESPIRATOR: Air contamination monitoring should be carried out where mists or vapors are likely to be generated, to assure that the employees are not exposed to airborne contaminants above the permissible exposure limits. If respiratory protection is required, it must be based on the contamination levels found in the workplace, must not exceed the working limits of the respirator and be jointly approved by the National Institute for Occupational Safety and Health and the Mine Safety and Health Administration (NIOSH-MSHA).

FOR FIRE FIGHTING AND OTHER IMMEDIATELY DANGEROUS TO LIFE OR HEALTH CONDITIONS: Any self-contained breathing apparatus that has a full-face piece and is operated in a pressure-demand or other positive-pressure mode. Any supplied-air respirator that has a full-face piece and is operated in a pressure-demand or other positive-pressure mode in combination with an auxiliary self-contained breathing apparatus operated in pressure demand or other positive-pressure mode.

CLOTHING: Protective clothing is required where repeated or prolonged skin

contact may occur. GLOVES: Protective gloves are required where repeated or prolonged skin contact may occur.

EYE/FACE PROTECTION: Safety glasses are required to prevent eye contact where dusty conditions may occur.

SECTION 9. Physical And Chemical Properties

APPEARANCE: White or light colored soap-based bar

ODOR/ODOR THRESHOLD: Pleasant fragrance PHYSICAL STATE:
pH (@ 25°C): Not available VAPOR DENSITY:
BOILING POINT: Not available VAPOR PRESSURE:

MELTING/FREEZING POINT: Not available FLASH POINT:

FLAMMABLE PROPERTIES: Not flammable SOLUBILITY IN WATER: Nearly complete

DENSITY/SPECIFIC GRAVITY: Not applicable EVAPORATION RATE: Not available

OCTANOL/WATER PARTITION COEFFICIENT (Kow): Not available

VISCOSITY (Dynamic): Not available

SECTION 10. Stability And Reactivity

HEMICAL STABILITY: Stable under normal ambient temperature (70°F, 21°C) and

pressure (1 atm).

CONDITIONS TO AVOID: Avoid contact with incompatible substances and excessive heat.

INCOMPATIBLE MATERIALS: Strong oxidizers, acids and bases.

HAZARDOUS DECOMPOSITION PRODUCTS: Thermal decomposition may release toxic and/or hazardous gases including oxides of carbon and sodium.

POSSIBILITY OF HAZARDOUS REACTIONS: Hazardous polymerization will not occur

SECTION 11. Toxicological Information

RODUCT INFORMATION SUMMARY: This product is a personal care or cosmetic product. The use of this product by consumers is safe under normal and reasonable foreseen use. Direct contact with eyes may cause eye irritation. Repeated or prolonged excessive exposure with skin may cause irritation.

COMPONENT ANALYSIS: The following toxicity information is for the hazardous ingredient(s) when used as technical grade and is provided as reference for the occupational settings.

INGREDIENT LD50 / DRAIZE SCORE TOXICITY / IRRITATION RATING

ACUTE ORAL TOXICITY

Glycerin 12,600 mg/kg (rat) Non-hazardous

ACUTE DERMAL TOXICITY

Glycerin > 10,000 mg/kg (rabbit) Non-hazardous

ACUTE INHALATION TOXICITY

Glycerin > 570 mg/m³ (rat) Toxic

SENSITIZATION: This product is not considered a skin or respiratory sensitizer.

CARCINOGENICITY: None of the ingredients in this product are listed as carcinogens by the International Agency for Research on Cancer (IARC), the National Toxicology Program (NTP) or the Occupational Safety and Health Administration (OSHA).

MUTAGENICITY: None of the ingredients in this product are known to cause mutagenicity.

REPRODUCTIVE/FETAL/DEVELOPMENTAL TOXICITY: None of the ingredients in this product are known as reproductive, fetal, or developmental hazards.

TARGET ORGAN TOXICITY: None of the ingredients in this product are known to have target organ toxicity.

EPIDEMIOLOGICAL INFORMATION: None of the ingredients in this product are known to have health-related information in working populations

SECTION 12. Ecological Information

This product is anticipated to be safe for the environment at concentrations predicted in household settings under normal use conditions.

PRODUCT / INGREDIENT LC50/EC50 (ANIMAL SPECIE) TOXICITY RATING

VERTEBRATES

Glycerin 96-hr LC50: 50 mg/L (Oncorhynchus mykiss) Harmful

INVERTEBRATES

Glycerin 24-hr EC50: > 500 mg/L (Daphnia magna) Practically Non-Hazardous

ENVIRONMENTAL FATE: No environmental fate data exists for the product. The product is anticipated to be rapidly biodegradable.

PERSISTENCE AND DEGRADABILITY: The persistence and degradability of this product has not

been determined. BIOACCUMULATION POTENTIAL: The bioaccumulation potential of this product

has not been determined. MOBILITY: The mobility of this product (in soil and water) has not been determined.

SECTION 13. Disposal Considerations

WASTE NUMBER AND DESCRIPTION: Not applicable, not regulated.

DISPOSAL CONSIDERATIONS: This product is not a RCRA hazardous waste and can be disposed of in accordance with federal, state and local regulations.

SECTION 14. Transport Information

GROUND TRANSPORT

DOT Hazard Class: Not regulated Packing Group: Not applicable DOT Proper Shipping Name: Not applicable Shipping Label Information: Not applicable

UN/NA Number: Not applicable

AIR TRANSPORT (ICAO/IATA)

MARINE TRANSPORT (IMDG/IMO)

ICAO/IATA Hazard Class: Not regulated IMDG/IMO Hazard Class: Not regulated ICAO/IATA Proper Shipping Name: Not applicable IMDG/IMO Proper Shipping Name: Not applicable

SECTION 15. Regulatory Information

UNITED STATES:

OSHA HAZARD COMMUNICATION RULE, 29 CFR 1910.1200:

The Occupational Safety and Health Administration requires Material Safety Data Sheets to provide any hazards that may be associated with the product, and make this information available in the workplace. Since the use pattern and exposure in the workplace are generally not consistent with those experienced by consumers, this MSDS may contain additional health hazard information not pertinent to consumer use.

FOOD AND DRUG ADMINISTRATION:

This product is regulated as a cosmetic under the Food and

Drug Administration. EPA - SARA TITLE III SECTION 313: Not

applicable - Consumer product.

EPA CERCLA/SARA TITLE III SUPERFUND AMENDMENT AND REAUTHORIZATION ACT.

SECTION 16. Other Information

DISCLAIMER: The information contained herein is provided in good faith and is believed to be correct as of the date hereof. However, Transmacro Amenities makes no representation as to the comprehensiveness or accuracy of the information. It is expected that individuals receiving the information will exercise their independent judgment in determining its appropriateness for a particular purpose. Accordingly, Transmacro Amenities will not be responsible for damages of any kind resulting from the use of or reliance upon such information. No representations, or warranties, either expressed or implied of merchantability, fitness for a particular purpose or of any other nature is made hereunder with respect to the information set forth herein or to the product to which the information refers.

*** End ***