SAFETY DATA SHEET

1. Identification

Product identifier **Crisp**

Other means of identification

Product code F426015

Recommended use Chewing Gum Remover

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Manufacturer

Company name	Franklin Cleaning Technology	
Address	One Fuller Way Great Bend, KS 67530 United States	
Telephone	Customer Service	(800) 810-4829
E-mail	Not available.	
Emergency phone number	CHEMTREC	(800) 424-9300
	Emergency	(620) 792-1711
	24 hour Emergency	(800) 424-9300

2. Hazard(s) identification

Physical hazards	Flammable aerosols	Category 1
Health hazards	Not classified.	
Environmental hazards	Not classified.	
OSHA defined hazards	Not classified.	

Label elements



Signal word Danger

Hazard statement Extremely flammable aerosol.

Precautionary statement

Prevention Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use.

Response If exposed or concerned: Get medical advice/attention.

Storage Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

Disposal Dispose of waste and residues in accordance with local authority requirements.

Hazard(s) not otherwise classified (HNOC) None known.

Supplemental information None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
ISOBUTANE		75-28-5	80 - < 90
PROPANE		74-98-6	10 - < 20

*Designates that a specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	If symptoms develop move victim to fresh air. Get medical attention if symptoms persist.
Skin contact	Wash off with soap and water. Get medical attention if irritation develops and persists.
Eye contact	Rinse with water. Get medical attention if irritation develops and persists.
Ingestion	Rinse mouth. Get medical attention if symptoms occur.
Most important symptoms/effects, acute and delayed	Direct contact with eyes may cause temporary irritation.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Powder. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	Contents under pressure. Pressurized container may explode when exposed to heat or flame.
Special protective equipment and precautions for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
Fire-fighting equipment/instructions	Move containers from fire area if you can do so without risk. Containers should be cooled with water to prevent vapor pressure build up. For massive fire in cargo area, use unmanned hose holder or monitor nozzles, if possible. If not, withdraw and let fire burn out.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials. Move containers from fire area if you can do so without risk. In the event of fire and/or explosion do not breathe fumes.
General fire hazards	Extremely flammable aerosol.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Refer to attached safety data sheets and/or instructions for use. Keep combustibles (wood, paper, oil, etc.) away from spilled material. Stop leak if you can do so without risk. Move the cylinder to a safe and open area if the leak is irreparable. Isolate area until gas has dispersed. Use water spray to reduce vapors or divert vapor cloud drift. Prevent entry into waterways, sewer, basements or confined areas. Following product recovery, flush area with water. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling	Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. All equipment used when handling the product must be grounded. Do not re-use empty containers. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Observe good industrial hygiene practices.
Conditions for safe storage, including any incompatibilities	Level 3 Aerosol. Pressurized container. Protect from sunlight and do not expose to temperatures exceeding 50°C/122 °F. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. This material can accumulate static charge which may cause spark and become an ignition source. Refrigeration recommended. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
PROPANE (CAS 74-98-6)	PEL	1800 mg/m3 1000 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
ISOBUTANE (CAS 75-28-5)	STEL	1000 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
ISOBUTANE (CAS 75-28-5)	TWA	1900 mg/m3 800 ppm
PROPANE (CAS 74-98-6)	TWA	1800 mg/m3 1000 ppm

Biological limit values No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection Wear appropriate chemical resistant gloves.

Other Wear suitable protective clothing.

Respiratory protection If permissible levels are exceeded use NIOSH mechanical filter / organic vapor cartridge or an air-supplied respirator.

Thermal hazards Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance Aerosol.

Physical state Gas.

Form Aerosol. Compressed gas.

Color Colorless.

Odor Odorless.

Odor threshold Not available.

pH Not available.

Melting point/freezing point -305.68 °F (-187.6 °C) estimated

Initial boiling point and boiling range -43.78 °F (-42.1 °C) estimated

Flash point -155.0 °F (-103.9 °C) estimated

Evaporation rate Not available.

Flammability (solid, gas) Flammable gas.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) 1.9 % estimated

Flammability limit - upper (%) 8.5 % estimated

Explosive limit - lower (%) Not available.

Explosive limit - upper (%)	Not available.
Vapor pressure	2938.62 hPa estimated
Vapor density	Not available.
Relative density	Not available.
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	842 °F (450 °C) estimated
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Density	4.64 lbs/gal estimated
Flammability class	Flammable IA estimated
Heat of combustion (NFPA 30B)	42.99 kJ/g estimated
Specific gravity	0.56 estimated
VOC (Weight %)	100 %

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	Hazardous polymerization does not occur.
Conditions to avoid	Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents. Nitrates. Fluorine. Chlorine.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Ingestion	Expected to be a low ingestion hazard.
Inhalation	Prolonged inhalation may be harmful.
Skin contact	Contact with liquid may freeze tissue, similar to thermal burn.
Eye contact	Direct contact with eyes may cause temporary irritation.
Symptoms related to the physical, chemical and toxicological characteristics	Direct contact with eyes may cause temporary irritation.

Information on toxicological effects

Acute toxicity Not available.

Product	Species	Test Results
Crisp (CAS Mixture)		
Acute		
Inhalation		
LC50	Mouse	61.9048 mg/l, 1 Hours estimated
	Rat	9017.7939 mg/l, 15 Minutes estimated

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Prolonged skin contact may cause temporary irritation.
Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.

Respiratory or skin sensitization

Respiratory sensitization	Not available.

Skin sensitization This product is not expected to cause skin sensitization.

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity Due to inconclusive data the classification is not possible.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Reproductive toxicity Classification not possible.

Specific target organ toxicity - single exposure Not classified.

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard Not likely, due to the form of the product.

Chronic effects Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential No data available.

Partition coefficient n-octanol / water (log Kow)

ISOBUTANE	2.76
PROPANE	2.36

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Dispose of contents/container in accordance with local/regional/national/international regulations.

Local disposal regulations Dispose in accordance with all applicable regulations.

Hazardous waste code The waste code should be assigned in discussion between the user, the producer and the waste disposal company.

Waste from residues / unused products Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).

Contaminated packaging Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied. Do not re-use empty containers.

14. Transport information

DOT

UN number UN1950

UN proper shipping name Aerosols, flammable, (each not exceeding 1 L capacity)

Transport hazard class(es)

Class 2.1

Subsidiary risk -

Label(s) 2.1

Packing group Not applicable.

Special precautions for user Read safety instructions, SDS and emergency procedures before handling.

Special provisions N82

Packaging exceptions 306

Packaging non bulk None

Packaging bulk None

IATA

UN number UN1950

UN proper shipping name Aerosols, flammable

Transport hazard class(es)

Class	2.1
Subsidiary risk	-

Packing group Not applicable.
Environmental hazards No.
ERG Code 10L
Special precautions for user Read safety instructions, SDS and emergency procedures before handling.
Other information

Passenger and cargo aircraft	Allowed.
Cargo aircraft only	Allowed.

IMDG

UN number UN1950
UN proper shipping name AEROSOLS
Transport hazard class(es)

Class	2
Subsidiary risk	-

Packing group Not applicable.
Environmental hazards

Marine pollutant	No.

EmS F-D, S-U
Special precautions for user Read safety instructions, SDS and emergency procedures before handling.
Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

DOT



IATA; IMDG



15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
All components are on the U.S. EPA TSCA Inventory List.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

ISOBUTANE (CAS 75-28-5)	Listed.
PROPANE (CAS 74-98-6)	Listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories Immediate Hazard - No
Delayed Hazard - No
Fire Hazard - Yes
Pressure Hazard - No
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes

SARA 313 (TRI reporting)

Not regulated.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

ISOBUTANE (CAS 75-28-5)
PROPANE (CAS 74-98-6)

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations

US. Massachusetts RTK - Substance List

ISOBUTANE (CAS 75-28-5)
PROPANE (CAS 74-98-6)

US. New Jersey Worker and Community Right-to-Know Act

ISOBUTANE (CAS 75-28-5)
PROPANE (CAS 74-98-6)

US. Pennsylvania Worker and Community Right-to-Know Law

ISOBUTANE (CAS 75-28-5)
PROPANE (CAS 74-98-6)

US. Rhode Island RTK

ISOBUTANE (CAS 75-28-5)
PROPANE (CAS 74-98-6)

US. California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

16. Other information, including date of preparation or last revision

Issue date 05-06-2015

Version # 01

Disclaimer The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.