



Features & Benefits

- Superior long term reliability
- High current pulse discharge capability
- Wide operating temperature (-40°C to 70°C)
- High safety and energy density


Specifications

Capacity: 1600 mAh Typical


Nominal Voltage: 3V

Weight: Approximately 17g

Dimensions




Pulse Discharge Characteristics




DISCHARGE CURVES (1kohm)


Long Term Discharge 100kΩ (without wake-up pulse)



Discharge Curves (1kohm)



Long Term Discharge 300kΩ (without wake-up pulse)



The data in this document is for descriptive purposes only and is not intended to make or imply any guarantee or warranty.