

SAFETY DATA SHEET



Issuing Date: 21-Apr-2021

Revision date 10-Nov-2021

Revision Number 1.01

1. IDENTIFICATION

Product Name Ultra Dawn Base Blue

Product Identifier 91916379_RET_NG

Product Type: Consumer Test / Registration Sample Use Only

Recommended Use Dish Care.

Restrictions on use Use only as directed on label.

Synonyms C-91916379-001

Details of the supplier of the safety data sheet PROCTER & GAMBLE - Fabric and Home Care Division
Ivorydale Technical Centre
5289 Spring Grove Avenue
Cincinnati, Ohio 45217-1087 USA

Procter & Gamble Inc.
P.O. Box 355, Station A
Toronto, ON M5W 1C5
1-800-331-3774

E-mail Address pgsds.im@pg.com

Emergency Telephone Transportation (24 HR)
CHEMTREC - 1-800-424-9300
(U.S./ Canada) or 1-703-527-3887
Mexico toll free in country: 800-681-9531

2. HAZARD IDENTIFICATION

"Consumer Products", as defined by the US Consumer Product Safety Act and which are used as intended (typical consumer duration and frequency), are exempt from the OSHA Hazard Communication Standard (29 CFR 1910.1200). This SDS is being provided as a courtesy to help assist in the safe handling and proper use of the product.

This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:.

Hazard category

Eye Damage / Irritation Category 2B

Flammable liquids Category 4

Signal word Warning

Hazard statements Causes eye irritation

Physical hazards Combustible liquid

Hazard pictograms None

Precautionary Statements Wash hands thoroughly after handling
Do not eat, drink or smoke when using this product
Keep away from heat/sparks/open flames/hot surfaces. — No smoking

Keep container tightly closed

Precautionary Statements - Response

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 If eye irritation persists: Get medical advice/attention
 If swallowed:
 Drink 1 or 2 glasses of water
 In case of fire: Use water, CO₂, dry chemical, or foam for extinction

Precautionary Statements - Storage Store in a well-ventilated place. Keep cool

Precautionary Statements - Disposal Dispose of contents/container to an approved waste disposal plant

3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Chemical Name	Synonyms	Trade Secret	CAS No	weight-%
Sulfuric acid, mono-C10-16-alkyl esters, sodium salts	Sulfuric acid, mono-C10-16-alkyl esters, sodium salts	No	68585-47-7	20 - 25
Lauramine Oxide	Lauramine Oxide	No	70592-80-2	5 - 10
Alcohol	Ethanol	No	64-17-5	1 - 5
C9-11 Pareth-n	Alcohols, C9-11, ethoxylated	No	68439-46-3	1 - 5
Deceth-n	Poly(oxy-1,2-ethanediyl), alpha-decyl-omega-hydroxy-	No	26183-52-8	1 - 5

Additional information

Actual substance concentrations fall within the ranges stated. Maximum values do not necessarily represent the values present in the formula.

4. FIRST AID MEASURES

Description of first aid measures

Eye contact

Rinse with plenty of water. Get medical attention immediately if irritation persists. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

Skin contact

Rinse with plenty of water. Call a physician if irritation develops and persists.

Ingestion

Rinse mouth. Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur.

Inhalation

Move to fresh air. If symptoms persist, call a physician.

Most important symptoms/effects, acute and delayed

May cause eye irritation

Indication of any immediate medical attention and special treatment needed

Notes to Physician

Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Flammable properties

FLAMMABLE LIQUID AND VAPOR

Suitable extinguishing media	In case of fire: Use water, CO ₂ , dry chemical, or foam for extinction. Dry chemical. Alcohol resistant foam. Carbon dioxide (CO ₂).
Unsuitable Extinguishing Media	Do not use a solid water stream as it may scatter and spread fire.
Special Hazard	combustible liquid. Fumes may catch fire.
Special protective equipment for fire-fighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.
Specific hazards arising from the chemical	None.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions	Use personal protective equipment as required. Do not get in eyes, on skin, or on clothing.
Advice for emergency responders	Use personal protective equipment as required.
Environmental precautions	Do not discharge product into natural waters without pre-treatment or adequate dilution

Methods and material for containment and cleaning up

Methods for containment	Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Prevent further leakage or spillage if safe to do so.
Methods for cleaning up	Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling	Keep away from open flames, hot surfaces and sources of ignition. Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children.
--------------------------------	---

Conditions for safe storage, including any incompatibilities

Technical measures/Storage conditions	Keep away from open flames, hot surfaces and sources of ignition. Store away from other materials.
Storage Conditions	Store in a cool/low-temperature, well-ventilated, dry place away from heat and ignition sources. Keep containers tightly closed in a dry, cool and well-ventilated place.
Incompatible products	None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines	No exposure limits noted for ingredient(s).
----------------------------	---

No relevant exposure guidelines for other ingredients

Appropriate engineering controls

Engineering Measures**Distribution, Workplace and Household Settings:**

Ensure adequate ventilation

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction

Manufacturing Sites:

Not relevant

Personal Protective Equipment**Eye Protection****Distribution, Workplace and Household Settings:**

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Use appropriate eye protection

Manufacturing Sites:

Wear safety glasses with side shields (or goggles)

No special protective equipment required

Hand Protection**Distribution, Workplace and Household Settings:**

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Protective gloves

Skin and Body Protection**Distribution, Workplace and Household Settings:**

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

Wear suitable protective clothing

Respiratory Protection**Distribution, Workplace and Household Settings:**

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):

In case of inadequate ventilation wear respiratory protection

9. PHYSICAL AND CHEMICAL PROPERTIES**Physical state**

Liquid

Appearance

clear To blue

Odor

pleasant (perfume)

Odor threshold

No information available

Property**Values****Remarks****pH**

9

Melting Point / Freezing Point

No information available

Initial boiling point and boiling range

No information available

flash point

69.5 °C / 157.1 °F

Closed cup. Product is an aqueous solution containing <=24% alcohol and >=50% water.

evaporation rate

No information available

Flammability

No information available

Flammability Limit in Air**Upper flammability or explosive limits**

No information available

Lower flammability or explosive limits	No information available
Vapor pressure	No information available
Relative vapor density	No information available
Relative density	No information available
Water solubility	No information available
Partition coefficient	No information available
Autoignition temperature	No information available
Decomposition temperature	No information available
Viscosity	No information available
VOC Content (%)	Products comply with US state and federal regulations for VOC content in consumer products.

10. STABILITY AND REACTIVITY

Reactivity	None under normal use conditions.
Stability	Stable under normal conditions.
Hazardous polymerization	Hazardous polymerization does not occur.
Hazardous Reactions	None under normal processing.
Conditions to Avoid	Keep away from open flames, hot surfaces and sources of ignition.
Incompatible Materials	None in particular.
Hazardous Decomposition Products	None under normal use conditions.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Inhalation	No known effect.
Skin contact	No known effect.
Ingestion	No known effect.
Eye contact	Irritating to eyes. Avoid contact with eyes.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Acute toxicity	No known effect.
Skin corrosion/irritation	No known effect.
Serious eye damage/eye irritation	Irritating to eyes.
Skin sensitization	No known effect.
Respiratory sensitization	No known effect.
Germ cell mutagenicity	No known effect.
Reproductive toxicity	No known effect.
Developmental toxicity	No known effect.
STOT - single exposure	No known effect.
STOT - repeated exposure	No known effect.
Aspiration hazard	No known effect.
Carcinogenicity	No known effect.

Component Information

Chemical Name	CAS No	Oral LD50	Dermal LD50	Inhalation LC50
Alcohol	64-17-5	10470 mg/kg bw (OECD 401)	-	116.9 mg/L air (//OECD 403)
C9-11 Pareth-n	68439-46-3	> 300 - < 2000 mg/kg bw	> 2000 mg/kg bw	-
Deceth-n	26183-52-8	300 mg/kg	>2000 mg/kg	-

12. ECOLOGICAL INFORMATION

ecotoxicity

The product is not expected to be hazardous to the environment.

Persistence and degradability No information available.

Bioaccumulative potential No information available.

Mobility No information available.

Other adverse effects No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Waste from Residues/Unused Products Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Disposal should be in accordance with applicable regional, national and local laws and regulations.

California Hazardous Waste Codes (non-household setting) 331

14. TRANSPORT INFORMATION

DOT

Product is not regulated for transport by ground in retail packaging per 49 CFR 173.150(f)(2)

IMDG Not regulated

IATA Not regulated

15. REGULATORY INFORMATION

U.S. FEDERAL REGULATIONS**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product does not contain any substances regulated as hazardous air pollutants (HAPS) under Section 112 of the Clean Air Act Amendments of 1990.

Clean Water Act

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

U.S. State Regulations (RTK)

Chemical Name	CAS No	New Jersey
Alcohol	64-17-5	X

Chemical Name	CAS No	Massachusetts
Alcohol	64-17-5	X

Chemical Name	CAS No	Pennsylvania
Alcohol	64-17-5	X

California Proposition 65

This product is not subject to warning labeling under California Proposition 65.

International Inventories**United States**

All intentionally-added components of this product(s) are listed on the US TSCA Inventory

Canada

This product is in compliance with CEPA for import by P&G

Legend

United States Toxic Substances Control Act Section 8(b) Inventory (TSCA)

CEPA - Canadian Environmental Protection Act

16. OTHER INFORMATION**HMIS****NFPA**

Issuing Date: 21-Apr-2021

Revision date 10-Nov-2021

Disclaimer.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet