


## Thermoplastic Utility Pumps

**UTM01602K** | 1/6 HP | 1500 GPH

**UTM02502K** | 1/3 HP | 2000 GPH



- Corrosion-resistant, reinforced thermoplastic construction
- Bottom suction design filters debris and removes water down to 1/4"
- 1" minimum water level for the pump to prime and operate
- 1" NPT discharge with garden hose adapter included
- Oil-filled motor for continuous lubrication
- Handle designed for easy portability




### Performance

Model No.	HP	Discharge Flow (GPH)						
		0'	5'	10'	15'	20'	25'	Max. lift
<b>UTM01602K</b>	1/6	1500	1400	1300	1100	750	300	27'
<b>UTM02502K</b>	1/3	2000	1800	1550	1300	1000	600	31'

Application	
Submersible utility pump for general water transfer	
Voltage	115
Hertz	60
Phase	Single
RPM	3450RPM
Motor type	Permanent Split Capacitor (PSC)
Insulation	Class B
Circuit requirements	15 AMP
Duty rating	Continuous*
Shaft seal	Lip seal
Motor Shaft	Stainless steel
Upper motor bearing	Ball bearing
Lower motor bearing	Ball bearing
Cooling	Oil cooled
Motor protection	Auto reset thermal overload protector
*For continuous, the water depth must be at least 6" to prevent the motor from overheating	
Pump Specifications	
Discharge size	1" MNPT & garden hose adapter included
Cord Length	10'
Cord type	SJTW 18AWG/3C, UL list
Pump Housing	Reinforced thermoplastic
Pump Base	Reinforced thermoplastic
Impeller material	Reinforced thermoplastic
Gasket	Rubber
Solids handling	1/8" spherical
Liquid temp.range	32°-95°F
Operation	Non-automatic
Fasteners	Stainless steel

### Performance



Model	HP	Amps	Discharge Height(ft)	0	5	10	15	20	25
				UTM01602K	1/6	2.2	GPM	25	23
			GPH	1500	1400	1300	1100	750	300
UTM02502K	1/3	3	GPM	37	33	29	25	20	13
			GPH	2200	2000	1750	1500	1200	800

### Dimensions

