



TECHNICAL CONCEPTS

CLEAN SEAT

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Date of issue: 03/17/2015 Version: 1.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name : CLEAN SEAT
Product code : RHG 5151
SKU # : FG402312

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture : Container fitted with a sealed spray attachment
Odour agents
For professional use only

1.3. Details of the supplier of the safety data sheet

Rubbermaid Commercial Products LLC
3124 Valley Avenue
Winchester, VA 22601-2694 - USA
T (540) 6678700
www.rubbermaidcommercial.com

1.4. Emergency telephone number

Emergency number : 24-Hour Emergency: INFOTRAC: 1-800535-5063

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

GHS-US classification

Flam. Liq. 3 H226
Skin Irrit. 2 H315
Eye Irrit. 2A H319
STOT SE 3 H335

Full text of H-statements: see section 16

2.2. Label elements

GHS-US labelling

Hazard pictograms (GHS-US) :



GHS02

GHS07

Signal word (GHS-US) :

Warning

Hazard statements (GHS-US) :

H226 - Flammable liquid and vapour
H315 - Causes skin irritation
H319 - Causes serious eye irritation
H335 - May cause respiratory irritation

Precautionary statements (GHS-US) :

P210 - Keep away from heat, hot surfaces, ignition sources. - No smoking
P280 - Wear protective gloves
P303+P361+P353 - If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower
P304+P340 - If inhaled: Remove person to fresh air and keep comfortable for breathing
P305+P351+P338 - If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P312 - Call a doctor if you feel unwell
P332+P313 - If skin irritation occurs: Get medical advice/attention
P337+P313 - If eye irritation persists: Get medical advice/attention

2.3. Other hazards

No additional information available

2.4. Unknown acute toxicity (GHS US)

Not applicable

CLEAN SEAT

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

SECTION 3: Composition/information on ingredients

3.1. Substance

Not applicable

3.2. Mixture

Name	Product identifier	%	GHS-US classification
Alcohol	(CAS No) 64-17-5	20 - 50	Flam. Liq. 2, H225 Skin Irrit. 2, H315 Eye Irrit. 2A, H319 STOT SE 3, H335
ISOPROPYL ALCOHOL	(CAS No) 67-63-0	1 - 10	Acute Tox. 4 (Oral), H302 Acute Tox. 4 (Dermal), H312

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

- First-aid measures general : Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
- First-aid measures after inhalation : Allow breathing of fresh air. Allow the victim to rest.
- First-aid measures after skin contact : Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower.
- First-aid measures after eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
- First-aid measures after ingestion : Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

- Symptoms/injuries after eye contact : Causes serious eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

SECTION 5: Firefighting measures

5.1. Extinguishing media

- Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Sand. Water spray.
- Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

- Fire hazard : Flammable liquid and vapour.
- Explosion hazard : May form flammable/explosive vapour-air mixture.

5.3. Advice for firefighters

- Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire-fighting water from entering environment.
- Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

- General measures : Remove ignition sources. Use special care to avoid static electric charges. No open flames. No smoking.

6.1.1. For non-emergency personnel

- Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

- Protective equipment : Equip cleanup crew with proper protection.
- Emergency procedures : Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

- Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.
- Other information : Can be slippery on hard, smooth walking area.

CLEAN SEAT

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Additional hazards when processed	: Handle empty containers with care because residual vapours are flammable.
Precautions for safe handling	: Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour. No open flames. No smoking. Take precautionary measures against static discharge. Use only non-sparking tools.
Hygiene measures	: Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work.

7.2. Conditions for safe storage, including any incompatibilities

Technical measures	: Comply with applicable regulations.
Storage conditions	: Keep only in the original container in a cool, well ventilated place away from : Heat sources, Ignition sources.
Incompatible products	: Strong bases. Strong acids.
Incompatible materials	: Sources of ignition. Direct sunlight. Heat sources.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

CLEAN SEAT		
ACGIH	Not applicable	
OSHA	Not applicable	
ISOPROPYL ALCOHOL (67-63-0)		
ACGIH	ACGIH TWA (ppm)	200 ppm
ACGIH	ACGIH STEL (ppm)	400 ppm
ACGIH	Remark (ACGIH)	Eye & URT irr; CNS impair
OSHA	OSHA PEL (TWA) (mg/m ³)	980 mg/m ³
OSHA	OSHA PEL (TWA) (ppm)	400 ppm
DNEL	DNEL	500 mg/m ³
Alcohol (64-17-5)		
ACGIH	ACGIH STEL (ppm)	1000 ppm
ACGIH	Remark (ACGIH)	URT irr
OSHA	OSHA PEL (TWA) (mg/m ³)	1900 mg/m ³
OSHA	OSHA PEL (TWA) (ppm)	1000 ppm
DNEL	DNEL	950 mg/m ³

8.2. Exposure controls

Personal protective equipment	: Avoid all unnecessary exposure.
Hand protection	: In case of repeated or prolonged contact wear gloves.
Eye protection	: None under normal use.
Respiratory protection	: None under normal use.
Other information	: Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Appearance	: clear.
Colour	: Colourless

CLEAN SEAT

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Odour	: characteristic
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: >= 78 °C
Flash point	: 26 °C
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: No data available
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Density	: 0.942 - 0.963 g/cm ³
Solubility	: Water: Solubility in water of component(s) of the mixture : • Water (Aqua): 1000000 mg/l • ISOPROPYL ALCOHOL: 1000000 mg/l • Alcohol: 1000000 mg/l • TERPINEOL: 1980 mg/l • BENZYL BENZOATE: 15.4 mg/l • NEROL: 531 mg/l
Log Pow	: No data available
Log Kow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

No additional information available

10.2. Chemical stability

Flammable liquid and vapour. May form flammable/explosive vapour-air mixture.

10.3. Possibility of hazardous reactions

Not established.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures. Open flame. Overheating. Heat. Sparks.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide. May release flammable gases.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity : Not classified

ISOPROPYL ALCOHOL (67-63-0)	
LD50 oral rat	2000 mg/kg
LD50 dermal rat	2000 mg/kg
ATE US (oral)	2000.000 mg/kg bodyweight
ATE US (dermal)	2000.000 mg/kg bodyweight

CLEAN SEAT

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Alcohol (64-17-5)	
LD50 oral rat	7060 mg/kg
LD50 dermal rabbit	> 16000 mg/kg
LC50 inhalation rat (mg/l)	> 20 mg/l/4h
ATE US (oral)	7060.000 mg/kg bodyweight
Skin corrosion/irritation	: Causes skin irritation.
Serious eye damage/irritation	: Causes serious eye irritation.
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
Specific target organ toxicity (single exposure)	: May cause respiratory irritation.
Specific target organ toxicity (repeated exposure)	: Not classified
Aspiration hazard	: Not classified
Potential adverse human health effects and symptoms	: Based on available data, the classification criteria are not met.
Symptoms/injuries after eye contact	: Causes serious eye irritation.

SECTION 12: Ecological information

12.1. Toxicity

ISOPROPYL ALCOHOL (67-63-0)	
LC50 fish 1	100 mg/l
EC50 Daphnia 1	100 mg/l
EC50 other aquatic organisms 1	13299 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	> 1000 mg/l IC50 algae (72 h) mg/l
Alcohol (64-17-5)	
LC50 fish 1	13000 mg/l
EC50 Daphnia 1	9300 mg/l
EC50 other aquatic organisms 1	5012 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	275 mg/l IC50 algae (72 h) mg/l

12.2. Persistence and degradability

CLEAN SEAT	
Persistence and degradability	Not established.
Alcohol (64-17-5)	
Persistence and degradability	Not established.

12.3. Bioaccumulative potential

CLEAN SEAT	
Bioaccumulative potential	Not established.
ISOPROPYL ALCOHOL (67-63-0)	
Log Pow	0.14
Alcohol (64-17-5)	
Log Pow	-0.3
Bioaccumulative potential	Not established.

12.4. Mobility in soil

No additional information available

CLEAN SEAT

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

12.5. Other adverse effects

Effect on ozone layer	:	
Effect on the global warming	:	No known ecological damage caused by this product.
Other information	:	Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste disposal recommendations	:	Dispose in a safe manner in accordance with local/national regulations.
Additional information	:	Handle empty containers with care because residual vapours are flammable.
Ecology - waste materials	:	Avoid release to the environment.

SECTION 14: Transport information

In accordance with DOT	:	
Transport document description	:	UN1170 Ethanol, 3, III
UN-No.(DOT)	:	UN1170
Proper Shipping Name (DOT)	:	Ethanol
Transport hazard class(es) (DOT)	:	3 - Class 3 - Flammable and combustible liquid 49 CFR 173.120
Hazard labels (DOT)	:	3 - Flammable liquid



Packing group (DOT)	:	III - Minor Danger
DOT Special Provisions (49 CFR 172.102)	:	24 - Alcoholic beverages containing more than 70 percent alcohol by volume must be transported as materials in Packing Group II. Alcoholic beverages containing more than 24 percent but not more than 70 percent alcohol by volume must be transported as materials in Packing Group III. B1 - If the material has a flash point at or above 38 C (100 F) and below 93 C (200 F), then the bulk packaging requirements of 173.241 of this subchapter are applicable. If the material has a flash point of less than 38 C (100 F), then the bulk packaging requirements of 173.242 of this subchapter are applicable. IB3 - Authorized IBCs: Metal (31A, 31B and 31N); Rigid plastics (31H1 and 31H2); Composite (31HZ1 and 31HA2, 31HB2, 31HN2, 31HD2 and 31HH2). Additional Requirement: Only liquids with a vapor pressure less than or equal to 110 kPa at 50 C (1.1 bar at 122 F), or 130 kPa at 55 C (1.3 bar at 131 F) are authorized, except for UN2672 (also see Special Provision IP8 in Table 2 for UN2672). T2 - 1.5 178.274(d)(2) Normal..... 178.275(d)(3) TP1 - The maximum degree of filling must not exceed the degree of filling determined by the following: Degree of filling = $97 / (1 + a (tr - tf))$ Where: tr is the maximum mean bulk temperature during transport, and tf is the temperature in degrees celsius of the liquid during filling.
DOT Packaging Exceptions (49 CFR 173.xxx)	:	4b;150
DOT Packaging Non Bulk (49 CFR 173.xxx)	:	203
DOT Packaging Bulk (49 CFR 173.xxx)	:	242
DOT Quantity Limitations Passenger aircraft/rail (49 CFR 173.27)	:	60 L
DOT Quantity Limitations Cargo aircraft only (49 CFR 175.75)	:	220 L
DOT Vessel Stowage Location	:	A - The material may be stowed "on deck" or "under deck" on a cargo vessel and on a passenger vessel.

Additional information

Other information	:	No supplementary information available.
IBC code	:	Not applicable.

ADR

Transport document description	:	UN 1170 ETHANOL SOLUTION (ETHYL ALCOHOL SOLUTION), 3, III, (D/E)
Packing group (ADR)	:	III

CLEAN SEAT

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Class (ADR) : 3 - Flammable liquid
Hazard identification number (Kemler No.) : 30
Classification code (ADR) : F1
Danger labels (ADR) : 3 - Flammable liquids



Orange plates :

Tunnel restriction code (ADR) : D/E
LQ : 5I
Excepted quantities (ADR) : E1

Transport by sea

UN-No. (IMDG) : 1170
Proper Shipping Name (IMDG) : ETHANOL (ETHYL ALCOHOL)
Class (IMDG) : 3 - Flammable liquids
Packing group (IMDG) : III - substances presenting low danger

Air transport

UN-No. (IATA) : 1170
Proper Shipping Name (IATA) : Ethanol
Class (IATA) : 3 - Flammable Liquids
Packing group (IATA) : III - Minor Danger

SECTION 15: Regulatory information

15.1. US Federal regulations

ISOPROPYL ALCOHOL (67-63-0)

Listed on the United States TSCA (Toxic Substances Control Act) inventory
Subject to reporting requirements of United States SARA Section 313

Alcohol (64-17-5)

Not subject to reporting requirements of the United States SARA Section 313
Listed on the United States TSCA (Toxic Substances Control Act) inventory

15.2. International regulations

CANADA

No additional information available

EU-Regulations

No additional information available

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Flam. Liq. 3 H226

Eye Irrit. 2 H319

Full text of hazard classes and H-statements : see section 16

Classification according to Directive 67/548/EEC [DSD] or 1999/45/EC [DPD]

15.2.2. National regulations

15.3. US State regulations

ISOPROPYL ALCOHOL (67-63-0)

U.S. -New York - RTK list Hazardous Substances

CLEAN SEAT

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Alcohol (64-17-5)

U.S. -New York - RTK list Hazardous Substances

SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of H-statements:

Acute Tox. 4 (Dermal)	Acute toxicity (dermal), Category 4
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Eye Irrit. 2A	Serious eye damage/eye irritation, Category 2A
Flam. Liq. 2	Flammable liquids, Category 2
Flam. Liq. 3	Flammable liquids, Category 3
Skin Irrit. 2	Skin corrosion/irritation, Category 2
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Respiratory tract irritation
H225	Highly flammable liquid and vapour
H226	Flammable liquid and vapour
H302	Harmful if swallowed
H312	Harmful in contact with skin
H315	Causes skin irritation
H319	Causes serious eye irritation
H335	May cause respiratory irritation

SDS US GHS HazCom 2012 newell

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product