



## Main

Product or component type	Single Throw Safety Switch
Series name	General duty

## Complementary

Line Rated Current	400 A
Device composition	Neutral (factory installed)
Disconnecter device type	Fusible disconnect
Short-circuit current	100 kA maximum cartridge
Device mounting	Surface
Number of poles	3
Electrical connection	Lugs
[Ue] rated operational voltage	120/240 V AC
Maximum Horse Power Rating	50 Hp 240 V at AC 50-60 Hz for 3 phase conforming to NEC 240.6 125 hp 240 V at AC 50-60 Hz for 3 phase conforming to NEC 430.52
AWG gauge	AWG 1/0...750 kcmil copper or aluminium
Tightening torque	340 Lbf.in (38.41 N.m) (AWG 1/0...750 kcmil) 340 lbf.in (38.41 N.m) (2 x AWG 1/0...2 x 300 kcmil)
Height	45.12 in (1146.05 mm)
Width	24.88 in (631.95 mm)
Depth	8.88 in (225.55 mm)

## Environment

Product certifications	CSA
NEMA degree of protection	NEMA 1 galvanized steel

## Ordering and shipping details

Category	00008 - H&HU SW,2&3P,N1,30-200A
Discount Schedule	DE1
GTIN	00785901404965
Nbr. of units in pkg.	1
Package weight(Lbs)	115 lb(US) (52.16 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	0.97 ft (0.297 m)
Package 1 width	2.16 ft (0.658 m)
Package 1 Length	3.90 ft (1.189 m)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------