




Build up success



Trusted performance that always delivers

Navigator Premium Multipurpose 20lb is key to top productivity with a 99.99% paper jam-free performance. Fewer jams result in a lower cost per printed document and superior, consistent quality – over time, every time.

Improved surface

The improved surface provides excellent printing quality while reducing toner consumption.

Multifunctional

Ideal for: e-mails, reports, memos, drafts, documents, educational material and more



OPTIMAL COLOR CONTRAST



FAST DRYING



ACCURATE ABSORPTION

Extra brightness and opacity

Extra brightness and opacity combined! The results are sharper images and vibrant color, providing excellent printing contrast without show through.

Navigator paper can be used for all your documents, guaranteeing great output with any office equipment.

20lb

8 1/2 x 11" | 8 1/2 x 14" | 11x17"



Premium-quality fiber

By using the best quality fiber – *Eucalyptus globulus* – Navigator guarantees optimum paper characteristics for all printing purposes.

This means using a bulkier sheet, with fewer jams and better toner absorption. It's a thicker, whiter and more opaque paper, ensuring you get the best printing results.

Environment

Our commitment is to the highest environmental standards and continuous improvement in our forest management practices.

Our responsible forest stewardship ensures the renewable supply of *Eucalyptus globulus* fiber and the preservation of biodiversity.



STANDARD SURFACE



NAVIGATOR IMPROVED SURFACE



For best results use the following settings in your printer setup:

1 Select "Plain" paper type. | 2 Select "Better" printing quality. | 3 Adjust color saturation and tone for enhanced images. See your Printer Manual for further instructions.

Navigator allows you to:

- Maximize printing quality
- Save toner
- Protect your office equipment

Bs.Wgt.	Size	Item #	Brightness	Ctns/Pallet	Thickness µm	Caliper	Opacity	M-Wgt	Sheets/Ctn
20 lb.	8 1/2 x 11	NMP1120	97	40	102	4.02	92	10	5,000
20 lb.	8 1/2 x 11	NMP115R	97	70	102	4.02	92	10	2,500
20 lb.	8 1/2 x 14	NMP1420	97	30	102	4.02	92	12.72	5,000
20 lb.	11 x 17	NMP1720	97	40	102	4.02	92	20	2,500
20 lb.	8 1/2 x 11	NMP113HP	97	40	102	4.02	92	10	5,000
20 lb.	8 1/2 x 11	NMP11FP	97	40	102	4.02	92	10	2,500
20 lb.	8 1/2 x 11	NMPFP3HP	97	40	102	4.02	92	10	2,500
20 lb.	A4	NMPA4	97	40	102	4.02	92	10	2,500

20lb



The mark of responsible forestry



EU Ecolabel: PT/011/002