

A07962 TM WILDWOOD FIG 12N6.6

Version 1.0 Revision Date 03/18/2016 Print Date 12/07/2016

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : A07962 TM WILDWOOD FIG 12N6.6

Material number : 0000000001048493

Manufacturer or supplier's details

Company : Zep Inc.

Address : 1310 Seaboard Industrial Blvd., NW

Atlanta, GA 30318

Telephone : 404-352-1680

Emergency telephone numbers

For SDS Information : Compliance Services 1-877-428-9937

For a Medical Emergency : 877-541-2016 Toll Free - All Calls Recorded

For a Transportation : CHEMTREC: 800-424-9300 - All Calls Recorded.

In the District of Columbia 202-483-7616

SECTION 2. HAZARDS IDENTIFICATION

Emergency Overview

Appearance	Aerosol containing a liquefied gas
Colour	colourless
Odour	mild

GHS Classification

Flammable aerosols : Category 1
Gases under pressure : Liquefied gas
Eye irritation : Category 2A
Skin sensitisation : Category 1

Specific target organ toxicity - : Category 3 (Central nervous system)

single exposure

GHS Label element

Hazard pictograms :



Signal word : Danger

Hazard statements : H222 Extremely flammable aerosol.

H280 Contains gas under pressure; may explode if heated.

H317 May cause an allergic skin reaction. H319 Causes serious eye irritation. H336 May cause drowsiness or dizziness.

Precautionary statements : Prevention:

P210 Keep away from heat/sparks/open flames/hot surfaces.

No smoking.



A07962 TM WILDWOOD FIG 12N6.6

Version 1.0 Revision Date 03/18/2016 Print Date 12/07/2016

P211 Do not spray on an open flame or other ignition source.

P251 Pressurized container: Do not pierce or burn, even after use.

P261 Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.

P264 Wash skin thoroughly after handling.

P271 Use only outdoors or in a well-ventilated area.

P272 Contaminated work clothing should not be allowed out of the workplace.

P280 Wear eye protection/ face protection.

P280 Wear protective gloves.

Response:

P302 + P352 IF ON SKIN: Wash with plenty of soap and water. P304 + P340 + P312 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/ physician if you feel unwell. P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P333 + P313 If skin irritation or rash occurs: Get medical advice/ attention.

P337 + P313 If eye irritation persists: Get medical advice/attention.

P363 Wash contaminated clothing before reuse.

Storage:

P403 + P233 Store in a well-ventilated place. Keep container tightly closed.

P405 Store locked up.

P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.

Disposal:

Dispose of contents/container in accordance with local regulation.

Potential Health Effects

Carcinogenicity:

IARC No component of this product present at levels greater than or

equal to 0.1% is identified as probable, possible or confirmed

human carcinogen by IARC.

ACGIH No component of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by ACGIH.

OSHA No component of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by OSHA.

NTP No component of this product present at levels greater than or

equal to 0.1% is identified as a known or anticipated carcinogen

by NTP.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Hazardous components

Chemical Name CAS-No.	Concentration [%]
-----------------------	-------------------



A07962 TM WILDWOOD FIG 12N6.6

Version 1.0 Revision Date 03/18/2016 Print Date 12/07/2016

acetone	67-64-1	>= 70 - < 90
propane	74-98-6	>= 20 - < 30
Oils, sweet orange (terpenes and terpenoids)	68647-72-3	>= 0.1 - < 1

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

General advice : Move out of dangerous area.

Show this safety data sheet to the doctor in attendance.

Do not leave the victim unattended.

If inhaled : Consult a physician after significant exposure.

If unconscious place in recovery position and seek medical

advice.

In case of skin contact : If on skin, rinse well with water.

In case of eye contact : Immediately flush eye(s) with plenty of water.

Remove contact lenses. Protect unharmed eye.

Keep eye wide open while rinsing.

If eye irritation persists, consult a specialist.

If swallowed : Keep respiratory tract clear.

Do not give milk or alcoholic beverages.

Never give anything by mouth to an unconscious person.

If symptoms persist, call a physician.

SECTION 5. FIREFIGHTING MEASURES

Suitable extinguishing media : Alcohol-resistant foam

Carbon dioxide (CO2)

Dry chemical

Unsuitable extinguishing

media

: High volume water jet

Specific hazards during

firefighting

: Do not allow run-off from fire fighting to enter drains or water

courses.

Hazardous combustion

products

: Carbon dioxide (CO2)

Carbon monoxide Smoke

Specific extinguishing

methods

:

Further information : Collect contaminated fire extinguishing water separately. This

must not be discharged into drains.

Fire residues and contaminated fire extinguishing water must

be disposed of in accordance with local regulations. For safety reasons in case of fire, cans should be stored

separately in closed containments.

Use a water spray to cool fully closed containers.

Special protective equipment

for firefighters

Wear self-contained breathing apparatus for firefighting if

necessary.



A07962 TM WILDWOOD FIG 12N6.6

Version 1.0 Revision Date 03/18/2016 Print Date 12/07/2016

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.

Ensure adequate ventilation.

Remove all sources of ignition.

Evacuate personnel to safe areas.

Beware of vapours accumulating to form explosive concentrations. Vapours can accumulate in low areas.

Environmental precautions

: Prevent product from entering drains.

Prevent further leakage or spillage if safe to do so.

If the product contaminates rivers and lakes or drains inform

respective authorities.

SECTION 7. HANDLING AND STORAGE

Advice on safe handling

Do not breathe vapours/dust.

Avoid exposure - obtain special instructions before use.

Avoid contact with skin and eyes. For personal protection see section 8.

Smoking, eating and drinking should be prohibited in the

application area.

Take precautionary measures against static discharges. Provide sufficient air exchange and/or exhaust in work rooms. Container may be opened only under exhaust ventilation

hood.

Open drum carefully as content may be under pressure. Dispose of rinse water in accordance with local and national

regulations.

Persons susceptible to skin sensitisation problems or asthma, allergies, chronic or recurrent respiratory disease should not be employed in any process in which this mixture is being

used.

Conditions for safe storage

: BEWARE: Aerosol is pressurized. Keep away from direct sun exposure and temperatures over 50 °C. Do not open by force

or throw into fire even after use. Do not spray on flames or

red-hot objects. No smoking.

Keep container tightly closed in a dry and well-ventilated

place.

Containers which are opened must be carefully resealed and

kept upright to prevent leakage. Observe label precautions.

Electrical installations / working materials must comply with

the technological safety standards.

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters



A07962 TM WILDWOOD FIG 12N6.6

Version 1.0 Revision Date 03/18/2016 Print Date 12/07/2016

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
acetone	67-64-1	TWA	500 ppm	ACGIH
		STEL	750 ppm	ACGIH
		TWA	250 ppm 590 mg/m3	NIOSH REL
		TWA	1,000 ppm 2,400 mg/m3	OSHA Z-1
		TWA	750 ppm 1,800 mg/m3	OSHA P0
		STEL	1,000 ppm 2,400 mg/m3	OSHA P0
propane	74-98-6	TWA	1,000 ppm	ACGIH
		TWA	1,000 ppm 1,800 mg/m3	NIOSH REL
		TWA	1,000 ppm 1,800 mg/m3	OSHA Z-1
		TWA	1,000 ppm 1,800 mg/m3	OSHA P0

Biological occupational exposure limits

Component	CAS-No.	Control	Biological	Sampling	Permissible	Basis
		parameters	specimen	time	concentration	
2-PROPANONE	67-64-1	Acetone	Urine	End of shift (As soon as possible after	50 mg/l	ACGIH BEI
				exposure ceases)		

Personal protective equipment

Respiratory protection : In the case of vapour formation use a respirator with an

approved filter.

In the case of dust or aerosol formation use respirator with an

approved filter.

Hand protection

Remarks : The suitability for a specific workplace should be discussed

with the producers of the protective gloves.

Eye protection : Eye wash bottle with pure water

Tightly fitting safety goggles

Wear face-shield and protective suit for abnormal processing

problems.

Skin and body protection : Impervious clothing

Choose body protection according to the amount and

concentration of the dangerous substance at the work place.

Hygiene measures : When using do not eat or drink.

When using do not smoke.

Wash hands before breaks and at the end of workday.



A07962 TM WILDWOOD FIG 12N6.6

Version 1.0 Revision Date 03/18/2016 Print Date 12/07/2016

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : Aerosol containing a liquefied gas

Colour : colourless

Odour : mild

Odour Threshold : No data available
pH : No data available
Melting point/freezing point : No data available
Boiling point : No data available
Vapour pressure : 5,515.8 hPa
Density : No data available

Solubility(ies)

Water solubility : partly soluble

Partition coefficient: n-

octanol/water

: No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity : No decomposition if stored and applied as directed.

Chemical stability : No decomposition if stored and applied as directed.

Possibility of hazardous

reactions

: No decomposition if stored and applied as directed.

Vapours may form explosive mixture with air.

Conditions to avoid : Heat, flames and sparks.

SECTION 11. TOXICOLOGICAL INFORMATION

Acute toxicity

Product:

Acute oral toxicity : Acute toxicity estimate : > 5,000 mg/kg

Method: Calculation method

Components:

acetone:

Acute oral toxicity : LD50 Rat: 5,800 mg/kg

Acute inhalation toxicity : LC50 Rat: 132 mg/l



A07962 TM WILDWOOD FIG 12N6.6

Version 1.0 Revision Date 03/18/2016 Print Date 12/07/2016

Exposure time: 3 h

LC50 Rat: 50.1 mg/l

Acute dermal toxicity : LD50 Guinea pig: > 7,426 mg/kg

LD50 Rabbit: > 7,426 mg/kg

propane:

Acute inhalation toxicity : LC50 Mouse: 1,237 mg/l

Exposure time: 2 h

LC50 Rat: 658 mg/l Exposure time: 4 h

LC50 Rat: 1,355 mg/l

Skin corrosion/irritation

Product:

Remarks: May cause skin irritation and/or dermatitis.

Serious eye damage/eye irritation

Product:

Remarks: Contact with eyes may cause irritation.

Respiratory or skin sensitisation

Product:

Remarks: Causes sensitisation.

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

acetone:

propane:

Oils, sweet orange (terpenes and terpenoids):

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity



A07962 TM WILDWOOD FIG 12N6.6

Version 1.0 Revision Date 03/18/2016 Print Date 12/07/2016

No data available

Further information

Product:

Remarks: Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting., Concentrations substantially above the TLV value may cause narcotic effects., Solvents may degrease the skin.

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

No data available

Persistence and degradability

No data available

Bioaccumulative potential

Product:

Partition coefficient: n-

octanol/water

: Remarks: No data available

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation 40 CFR Protection of Environment; Part 82 Protection of

Stratospheric Ozone - CAA Section 602 Class I

Substances

Remarks This product neither contains, nor was manufactured

with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A

+ B).

Additional ecological

information

: An environmental hazard cannot be excluded in the

event of unprofessional handling or disposal., Harmful to

aquatic life with long lasting effects.

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues : The product should not be allowed to enter drains, water

courses or the soil.

Do not contaminate ponds, waterways or ditches with

chemical or used container.

Send to a licensed waste management company.



A07962 TM WILDWOOD FIG 12N6.6

Version 1.0 Revision Date 03/18/2016 Print Date 12/07/2016

Contaminated packaging : Empty remaining contents.

Dispose of as unused product. Do not re-use empty containers.

Do not burn, or use a cutting torch on, the empty drum.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA): ORM-D, CONSUMER COMMODITY

Transportation Regulation: IMDG (Vessel):

UN1950, AEROSOLS, FLAMMABLE, 2.1, - Limited quantity

Transportation Regulation: IATA (Cargo Air):

UN1950, AEROSOLS, FLAMMABLE, 2.1, - Limited quantity

Transportation Regulation: IATA (Passenger Air):

UN1950, AEROSOLS, FLAMMABLE, 2.1, - Limited quantity

Transportation Regulation: TDG (Canada):

UN1950, AEROSOLS, FLAMMABLE, 2.1, - Limited quantity

SECTION 15. REGULATORY INFORMATION

EPCRA - Emergency Planning and Community Right-to-Know Act

CERCLA Reportable Quantity

Components	CAS-No.	Component RQ	Calculated product RQ
		(lbs)	(lbs)
acetone	67-64-1	5000	*

^{*:} Calculated RQ exceeds reasonably attainable upper limit.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Fire Hazard

Sudden Release of Pressure Hazard

Acute Health Hazard

SARA 302 : No chemicals in this material are subject to the reporting

requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with

known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop 65 This product does not contain any chemicals known to State of



A07962 TM WILDWOOD FIG 12N6.6

Version 1.0 Revision Date 03/18/2016 Print Date 12/07/2016

California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

TSCA On TSCA Inventory

DSL This product contains the following components that are not on the

Canadian DSL nor NDSL.

AICS
Not in compliance with the inventory
NZIoC
Not in compliance with the inventory
PICCS
Not in compliance with the inventory
IECSC
Not in compliance with the inventory


Inventory Acronym and Validity Area Legend:

AICS (Australia), DSL (Canada), IECSC (China), REACH (European Union), ENCS (Japan), ISHL (Japan), KECI (Korea), NZIoC (New Zealand), PICCS (Philippines), TCSI (Taiwan), TSCA (USA)

SECTION 16. OTHER INFORMATION

Further information

NFPA:



Special hazard.

HMIS III:

HEALTH	3
FLAMMABILITY	4
PHYSICAL HAZARD	2

0 = not significant, 1 = Slight,

2 = Moderate, 3 = High

4 = Extreme, * = Chronic

OSHA GHS Label Information:

Hazard pictograms







Signal w ord : Danger:

Hazard statements : Extremely flammable aerosol. Contains gas under pressure; may explode if heated.

May cause an allergic skin reaction. Causes serious eye irritation. May cause

drow siness or dizziness.

Precautionary statements :

Prevention: Keep aw ay from heat/sparks/open flames/hot surfaces. No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Avoid breathing dust/fume/gas/mist/ vapours/spray. Wash skin thoroughly after handling. Use only outdoors or in a well-ventilated area. Contaminated work clothing should not be allowed out of the workplace. Wear eye protection/face protection. Wear protective gloves.

Response: IF ON SKIN: Wash with plenty of soap and water. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation or rash occurs: Get medical advice/attention. If eye



A07962 TM WILDWOOD FIG 12N6.6

Version 1.0 Revision Date 03/18/2016 Print Date 12/07/2016

irritation persists: Get medical advice/ attention. Wash contaminated clothing before reuse

Storage: Store in a w ell-ventilated place. Keep container tightly closed. Store locked up. Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F. **Disposal:** Dispose of contents/container in accordance with local regulation.

Version:	1.0
Revision Date:	03/18/2016
Print Date:	12/07/2016

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®,Zep Professional®, Enforcer®, National Chemical™, Selig™, Misty®, Next Dimension™, Petro®, i-Chem®, TimeMist®, TimeWick™, MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National™, FC Forward Chemicals®,Rexodan®, Mykal™, and a number of private labeled brands.