

## **ZEP HRDW & LAM FLR CLNR Z**

Version 3.1 Revision Date 12/06/2016 Print Date 08/02/2018

#### **SECTION 1. PRODUCT AND COMPANY IDENTIFICATION**

Material name : ZEP HRDW & LAM FLR CLNR Z

Material number : ZUHLF128

Manufacturer or supplier's details

Company : Zep Inc.

Address : 1310 Seaboard Industrial Blvd., NW

Atlanta, GA 30318

Telephone : 404-352-1680

## **Emergency telephone numbers**

For SDS Information : Compliance Services 1-877-428-9937

For a Medical Emergency : 877-541-2016 Toll Free - All Calls Recorded

For a Transportation : CHEMTREC: 800-424-9300 - All Calls Recorded.

Emergency In the District of Columbia 202-483-7616

## Recommended use of the chemical and restrictions on use

Recommended use : Floor Care

Note: This product is labeled as a consumer product in accordance with the United States Consumer Product Safety Commission regulations. The warnings presented below in this Safety Data Sheet (SDS) comply with the 2012 OSHA Hazard Communication Standard (GHS - Globally Harmonized System of Classification and Labeling). The requirements for the labeling and warnings of consumer products may differ from those required for GHS based hazard communication.

## **SECTION 2. HAZARDS IDENTIFICATION**

## **Emergency Overview**

Appearance	liquid
Colour	colourless
Odour	pleasant

### **GHS Classification**

Not a hazardous substance or mixture.

#### **GHS** label elements

Not a hazardous substance or mixture.

#### **SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Substance / Mixture : Mixture

#### **Hazardous components**

Chemical name	CAS-No.	Concentration [%]
2-(2-butoxyethoxy)ethanol	112-34-5	>= 1 - < 5



## ZEP HRDW & LAM FLR CLNR Z

Version 3.1 Revision Date 12/06/2016 Print Date 08/02/2018

The exact percentages of disclosed substances are withheld as trade secrets.

### **SECTION 4. FIRST AID MEASURES**

General advice : Do not leave the victim unattended.

Show this safety data sheet to the doctor in attendance.

Move out of dangerous area. Do not leave the victim unattended.

If inhaled : If unconscious place in recovery position and seek medical

advice.

If symptoms persist, call a physician.

In case of skin contact If on clothes, remove clothes.

If skin irritation persists, call a physician.

Wash off immediately with plenty of water for at least 15

minutes.

In case of eye contact : Remove contact lenses.

Protect unharmed eye.

If eye irritation persists, consult a specialist. If in eyes, rinse with water for 15 minutes.

If swallowed Keep respiratory tract clear.

Never give anything by mouth to an unconscious person.

If symptoms persist, call a physician.

DO NOT induce vomiting unless directed to do so by a

physician or poison control center.

Most important symptoms

and effects, both acute and

delayed

: Effects may be delayed, symptoms may include minor eye or

skin irritation.

Overexposure may cause mild eye or skin irritation.

: Treat symptomatically. Symptoms may be delayed. Notes to physician

#### **SECTION 5. FIREFIGHTING MEASURES**

Suitable extinguishing media : Water spray jet

Alcohol-resistant foam Carbon dioxide (CO2)

Dry chemical

Unsuitable extinguishing

media

: High volume water jet

Specific hazards during

firefighting

: Do not allow run-off from fire fighting to enter drains or water

courses.

Hazardous combustion

products

: Carbon dioxide (CO2)

Carbon monoxide

Smoke

Specific extinguishing

methods

: Use extinguishing measures that are appropriate to local

circumstances and the surrounding environment.



## **ZEP HRDW & LAM FLR CLNR Z**

Version 3.1 Revision Date 12/06/2016 Print Date 08/02/2018

Further information : Standard procedure for chemical fires.

Use extinguishing measures that are appropriate to local

circumstances and the surrounding environment.

Special protective equipment

for firefighters

Wear self-contained breathing apparatus for firefighting if

necessary.

#### **SECTION 6. ACCIDENTAL RELEASE MEASURES**

Personal precautions, protective equipment and emergency procedures : Ensure adequate ventilation.

Use personal protective equipment. Evacuate personnel to safe areas.

Environmental precautions : If the product contaminates rivers and lakes or drains inform

respective authorities.

Prevent further leakage or spillage if safe to do so.

Prevent product from entering drains.

Methods and materials for containment and cleaning up

Wipe up with absorbent material (e.g. cloth, fleece). Keep in suitable, closed containers for disposal.

### **SECTION 7. HANDLING AND STORAGE**

Advice on safe handling : For personal protection see section 8.

Smoking, eating and drinking should be prohibited in the

application area.

Conditions for safe storage : Electrical installations / working materials must comply with

the technological safety standards.

Keep in a dry, cool and well-ventilated place.

Electrical installations / working materials must comply with

the technological safety standards.

Materials to avoid : No materials to be especially mentioned.

#### **SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**

#### Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
2-(2-butoxyethoxy)ethanol	112-34-5	TWA (Inhalable fraction and vapor)	10 ppm	ACGIH

**Engineering measures** : effective ventilation in all processing areas

### Personal protective equipment



## **ZEP HRDW & LAM FLR CLNR Z**

Version 3.1 Revision Date 12/06/2016 Print Date 08/02/2018

Respiratory protection : In case of insufficient ventilation, wear suitable respiratory

equipment.

Hand protection

Remarks : The suitability for a specific workplace should be discussed

with the producers of the protective gloves.

Eye protection : Safety glasses

Eye wash bottle with pure water

Skin and body protection : Impervious clothing

Hygiene measures : General industrial hygiene practice.

#### **SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**

Appearance : liquid

Colour : colourless
Odour : pleasant

Odour Threshold : No data available

pH : 8.5 - 9.0

Melting point/freezing point : No data available

Boiling point : 100 °C

Flash point

does not flash

Evaporation rate : 1

Upper explosion limit : Not applicable
Lower explosion limit : Not applicable
Vapour pressure : not determined
Density : 0.99 g/cm3

Solubility(ies)

Water solubility : soluble

Partition coefficient: n-

octanol/water

: No data available

Auto-ignition temperature : not determined

Thermal decomposition : No data available

Viscosity

Viscosity, kinematic : No data available



## **ZEP HRDW & LAM FLR CLNR Z**

Version 3.1 Revision Date 12/06/2016 Print Date 08/02/2018

### **SECTION 10. STABILITY AND REACTIVITY**

Reactivity : Stable

Chemical stability : Stable under normal conditions.

Possibility of hazardous

reactions

: Stable under recommended storage conditions.

No hazards to be specially mentioned.

Conditions to avoid : No data available

Incompatible materials : None.

Hazardous decomposition

products

: Carbon oxides

#### **SECTION 11. TOXICOLOGICAL INFORMATION**

#### **Potential Health Effects**

Aggravated Medical

Condition

: None known.

Symptoms of Overexposure

: Effects may be delayed, symptoms may include minor eye or

skin irritation.

Carcinogenicity:

IARC No component of this product present at levels greater than or

equal to 0.1% is identified as probable, possible or confirmed

human carcinogen by IARC.

OSHA No component of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by OSHA.

NTP No component of this product present at levels greater than or

equal to 0.1% is identified as a known or anticipated carcinogen

by NTP.

## **Acute toxicity**

No data available

Skin corrosion/irritation

No data available

Serious eye damage/eye irritation

No data available

Respiratory or skin sensitisation

No data available

Germ cell mutagenicity

No data available

Carcinogenicity



# **ZEP HRDW & LAM FLR CLNR Z**

Version 3.1 Revision Date 12/06/2016 Print Date 08/02/2018

No data available

### Reproductive toxicity

No data available

## 2-(2-butoxyethoxy)ethanol:

STOT - single exposure

No data available

### STOT - repeated exposure

No data available

### **Aspiration toxicity**

No data available

#### **Further information**

## **Product:**

Remarks: No data available

#### **SECTION 12. ECOLOGICAL INFORMATION**

## **Ecotoxicity**

No data available

## Persistence and degradability

No data available

## Bioaccumulative potential

Product:

Partition coefficient: n-

: Remarks: No data available

octanol/water **Components:** 

2-(2-butoxyethoxy)ethanol:

Partition coefficient: n- : Pow: 1

octanol/water

Mobility in soil

No data available

### Other adverse effects

No data available

**Product:** 

Regulation 40 CFR Protection of Environment; Part 82 Protection of

Stratospheric Ozone - CAA Section 602 Class I

Substances

Remarks This product neither contains, nor was manufactured

with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A



## **ZEP HRDW & LAM FLR CLNR Z**

Version 3.1 Revision Date 12/06/2016 Print Date 08/02/2018

+ B).

Additional ecological

information

: No data available

#### **SECTION 13. DISPOSAL CONSIDERATIONS**

### **Disposal methods**

Waste from residues : Dispose of in accordance with local regulations.

Do not contaminate ponds, waterways or ditches with

chemical or used container.

The product should not be allowed to enter drains, water

courses or the soil.

Contaminated packaging : Empty remaining contents.

Do not re-use empty containers. Dispose of as unused product.

#### **SECTION 14. TRANSPORT INFORMATION**

Transportation Regulation: 49 CFR (USA):

NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IMDG (Vessel):

NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Cargo Air):

NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Passenger Air):

NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: TDG (Canada):

NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

### **SECTION 15. REGULATORY INFORMATION**



## ZEP HRDW & LAM FLR CLNR Z

Version 3.1 Revision Date 12/06/2016 Print Date 08/02/2018

**TSCA list** : No substances are subject to a Significant New Use Rule.

No substances are subject to TSCA 12(b) export notification

requirements.

**EPCRA - Emergency Planning and Community Right-to-Know Act** 

**CERCLA Reportable Quantity** 

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : No SARA Hazards

SARA 302 : No chemicals in this material are subject to the reporting

requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with

known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop 65 This product does not contain any chemicals known to State of

California to cause cancer, birth defects, or any other

reproductive harm.

The components of this product are reported in the following inventories:

TSCA On TSCA Inventory

**DSL** This product contains one or more components that are listed on the

Canadian NDSL. All other components are on the Canadian DSL.

For information on the country notification status for other regions please contact the manufacturer's regulatory group.

**Inventory Acronym and Validity Area Legend:** 

TSCA (USA), DSL (Canada), NDSL (Canada)

#### **SECTION 16. OTHER INFORMATION**




## **ZEP HRDW & LAM FLR CLNR Z**

Version 3.1 Revision Date 12/06/2016 Print Date 08/02/2018

#### **Further information**

### NFPA:



Special hazard.

#### HMIS III:

HEALTH	0
FLAMMABILITY	0
PHYSICAL HAZARD	0

- 0 = not significant, 1 = Slight,
- 2 = Moderate, 3 = High
- 4 = Extreme, \* = Chronic

#### **OSHA - GHS Label Information:**

Not a hazardous substance or mixture.

Version:	3.1
Revision Date:	12/06/2016
Print Date:	08/02/2018

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®,Zep Professional®, Enforcer®, National Chemical™, Selig™, Misty®, Next Dimension™, Petro®, i-Chem®, TimeMist®, TimeWick™, MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National™, FC Forward Chemicals®,Rexodan®, Mykal™, and a number of private labeled brands.