

POWERING YOUR *life.*

Model 100326-1


UPC 850878006266

Warranty 2 Years

25 TON

 TOWABLE Up to 45 mph

Operation



Horizontal



Vertical

Features

Log Catchers & Strippers - Strips, catches and holds logs

Auto-return control valve

DOT approved wheels

Towable - fits most ATV/UTV towing applications

Specifications

START TYPE	Recoil
ENGINE SIZE	224cc
RAM FORCE	25 ton
CYCLE TIME	11 seconds
HYDRAULIC TANK CAPACITY	4 gal.
MAX LOG LENGTH	24 in.
MAX LOG WEIGHT	100 lb.
COUPLER BALL SIZE	2 in.
TIRE SIZE	16 in.
CYLINDER SIZE	3.9 in. x 22.6 in.
CYLINDER ROD SIZE	1.6 in.
GEAR PUMP	2 stage
MAX PRESSURE	3900 psi
MAX FLOW CAPACITY	11 gpm
CONTROL VALVE	Detent (auto return)
GASOLINE CAPACITY (gal)	0.8
OIL TYPE	10w-30
OIL CAPACITY (fl. oz/mL)	16.9/500
LOW OIL SHUT-OFF	Yes
EMISSIONS	EPA/CARB



Champion's towable 25-ton log splitter with its 224cc engine easily powers through the toughest logs. The fast 11-second cycle time and auto-return valve reduce your work time, while the handy log catchers and easy adjustment from horizontal to vertical save your back.

Inside the box

LOG SPLITTER
LOG CATCHERS

OPERATOR'S MANUAL
OIL FUNNEL

What You Need

GASOLINE
ENGINE OIL
HYDRAULIC OIL

PLIERS
WRENCH/SOCKET SET

*Specifications, descriptions and illustrations are subject to change without notice.

PACKAGED (gross)
Weight: 500.5 lb.
Size: 71.3 x 28.3 x 19.1 in.

PRODUCT (net)
Weight: 434.3 lb.
Size: 89.5 x 51.3 x 39.3 in.

CHAMPION POWER EQUIPMENT, INC.
12039 Smith Ave., Santa Fe Springs, CA 90670, USA
www.championpowerequipment.com – Made In China