



## 021-4055

### Premier Sliding Beam Anchor

**FEATURES :**

- 180°/360° swiveling connection point
- Lightweight aluminum construction
- Easy trailing for hands-free work
- One-handed trigger with dual sided adjustment
- Reinforced jaws for sturdy, smooth sliding action
- Fits beams 4" to 13" with flanges up to 1-1/4"
- For overhead and foot level tie-off
- Protective label cover
- Overall length 19-1/2"
- Minimum breaking strength : 5,000 lbs.

**FALL ARREST POINT(S) :**

- 1 D-ring

**ITEM WEIGHT :**

- 4.0 lbs. (1.8 kg)



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (141 kg)
OSHA	up to 420 lbs. (191 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.18-2017 (Type A)
OSHA	1926.502, 1910.140

SIZE(S)	
N/A	

COMPONENT	MATERIAL SPECIFICATION
Support Bar	Aluminum
Clamps	Aluminum
D-ring	Stainless Steel/Plated steel
Jaws	Plated steel
Label Cover	Polyester