SAFETY DATA SHEET

1. Identification

Product identifier **2 in 1 Rug Spotter RTU**

Other means of identification

Product code F374012

Recommended use All-Purpose Spotter

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Manufacturer

Company name	Franklin Cleaning Technology	
Address	One Fuller Way Great Bend, KS 67530 United States	
Telephone	Customer Service	(800) 810-4829
E-mail	Not available.	
Emergency phone number	CHEMTREC	(800) 424-9300
	Emergency	(620) 792-1711
	24 hour Emergency	(800) 424-9300

2. Hazard(s) identification

Physical hazards	Not classified.	
Health hazards	Acute toxicity, inhalation	Category 4
Environmental hazards	Not classified.	
OSHA defined hazards	Not classified.	

Label elements



Signal word Warning

Hazard statement Harmful if inhaled.

Precautionary statement

Prevention Avoid breathing vapors. Use only outdoors or in a well-ventilated area.

Response If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor if you feel unwell.

Storage Store away from incompatible materials.

Disposal Dispose of waste and residues in accordance with local authority requirements.

Hazard(s) not otherwise classified (HNOC) None known.

Supplemental information None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
BUTOXYETHANOL		111-76-2	3 - < 5
Other components below reportable levels			90 - 100

*Designates that a specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation Remove victim to fresh air and keep at rest in a position comfortable for breathing. Oxygen or artificial respiration if needed. Call a POISON CENTER or doctor/physician if you feel unwell.

Skin contact Wash off with soap and water. Get medical attention if irritation develops and persists.

Eye contact Rinse with water. Get medical attention if irritation develops and persists.

Ingestion Rinse mouth. Get medical attention if symptoms occur.

Most important symptoms/effects, acute and delayed Direct contact with eyes may cause temporary irritation.

Indication of immediate medical attention and special treatment needed Provide general supportive measures and treat symptomatically. Keep victim warm. Keep victim under observation. Symptoms may be delayed.

General information Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

Specific hazards arising from the chemical During fire, gases hazardous to health may be formed.

Special protective equipment and precautions for firefighters Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

Fire-fighting equipment/instructions Move containers from fire area if you can do so without risk.

Specific methods Use standard firefighting procedures and consider the hazards of other involved materials.

General fire hazards No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Wear appropriate protective equipment and clothing during clean-up. Avoid inhalation of vapors and spray mists. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.

Methods and materials for containment and cleaning up Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Cover with plastic sheet to prevent spreading. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.

Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.

Environmental precautions Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling Do not get in eyes, on skin, or on clothing. Avoid inhalation of vapors and spray mists. Avoid prolonged exposure. Use only outdoors or in a well-ventilated area. Wear appropriate personal protective equipment. Observe good industrial hygiene practices.

Conditions for safe storage, including any incompatibilities Store in original tightly closed container. Store in a well-ventilated place. Keep out of the reach of children. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
BUTOXYETHANOL (CAS 111-76-2)	PEL	240 mg/m3
		50 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
BUTOXYETHANOL (CAS 111-76-2)	TWA	20 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
BUTOXYETHANOL (CAS 111-76-2)	TWA	24 mg/m3
		5 ppm

Biological limit values

ACGIH Biological Exposure Indices

Components	Value	Determinant	Specimen	Sampling Time
BUTOXYETHANOL (CAS 111-76-2)	200 mg/g	Butoxyacetic acid (BAA), with hydrolysis	Creatinine in urine	*

* - For sampling details, please see the source document.

Exposure guidelines

US - California OELs: Skin designation

BUTOXYETHANOL (CAS 111-76-2) Can be absorbed through the skin.

US - Minnesota Haz Subs: Skin designation applies

BUTOXYETHANOL (CAS 111-76-2) Skin designation applies.

US - Tennesse OELs: Skin designation

BUTOXYETHANOL (CAS 111-76-2) Can be absorbed through the skin.

US NIOSH Pocket Guide to Chemical Hazards: Skin designation

BUTOXYETHANOL (CAS 111-76-2) Can be absorbed through the skin.

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

BUTOXYETHANOL (CAS 111-76-2) Can be absorbed through the skin.

Appropriate engineering controls Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

Eye/face protection Chemical respirator with organic vapor cartridge and full facepiece.

Skin protection

Hand protection Wear appropriate chemical resistant gloves.

Other Wear appropriate chemical resistant clothing.

Respiratory protection Chemical respirator with organic vapor cartridge and full facepiece.

Thermal hazards Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance Clear.

Physical state Liquid.

Form Liquid.

Color Colorless

Odor Matches to Standard

Odor threshold Not available.

pH 9

Melting point/freezing point Not available.

Initial boiling point and boiling range 212 °F (100 °C)

Flash point > 201.2 °F (> 94.0 °C)

Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	0.00001 hPa estimated
Vapor density	Not available.
Relative density	Not available.
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Density	8.35 lbs/gal
Percent volatile	99.1 % estimated
Specific gravity	1
VOC (Weight %)	3 % estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Ingestion	Expected to be a low ingestion hazard.
Inhalation	Harmful if inhaled.
Skin contact	2-Butoxy ethanol may be absorbed through the skin in toxic amounts if contact is repeated and prolonged. These effects have not been observed in humans.
Eye contact	Direct contact with eyes may cause temporary irritation.
Symptoms related to the physical, chemical and toxicological characteristics	Direct contact with eyes may cause temporary irritation.

Information on toxicological effects

Acute toxicity Harmful if inhaled.

Product	Species	Test Results
2 in 1 Rug Spotter RTU (CAS Mixture)		
Acute		
Dermal		
LD50	Rabbit	13333.333 mg/kg estimated

Product	Species	Test Results
Inhalation		
LC50	Mouse	23333.334 ppm, 7 Hours estimated
	Rat	15000 ppm, 4 Hours estimated
Oral		
LD50	Mouse	40 g/kg estimated
	Rat	17790.6133 mg/kg estimated

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation Prolonged skin contact may cause temporary irritation.

Serious eye damage/eye irritation Direct contact with eyes may cause temporary irritation.

Respiratory or skin sensitization

Respiratory sensitization Not available.

Skin sensitization This product is not expected to cause skin sensitization.

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.

IARC Monographs. Overall Evaluation of Carcinogenicity

BUTOXYETHANOL (CAS 111-76-2) 3 Not classifiable as to carcinogenicity to humans.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Reproductive toxicity This product is not expected to cause reproductive or developmental effects.

Specific target organ toxicity - single exposure Not classified.

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard Not available.

Chronic effects Prolonged inhalation may be harmful. May be harmful if absorbed through skin.

2-Butoxy ethanol may be absorbed through the skin in toxic amounts if contact is repeated and prolonged. These effects have not been observed in humans.

12. Ecological information

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Product		Species	Test Results
2 in 1 Rug Spotter RTU (CAS Mixture)			
Aquatic			
Fish	LC50	Fish	5265.7129 mg/l, 96 hours estimated

* Estimates for product may be based on additional component data not shown.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential No data available.

Partition coefficient n-octanol / water (log Kow)

BUTOXYETHANOL 0.83

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Dispose of contents/container in accordance with local/regional/national/international regulations.

Local disposal regulations Dispose in accordance with all applicable regulations.

Hazardous waste code	The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	This substance/mixture is not intended to be transported in bulk.

15. Regulatory information

US federal regulations

All components are listed or exempted from listing on the U.S. EPA TSCA Inventory List. This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

BUTOXYETHANOL (CAS 111-76-2) Listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories

Immediate Hazard - Yes
Delayed Hazard - No
Fire Hazard - No
Pressure Hazard - No
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes

SARA 313 (TRI reporting)

Chemical name	CAS number	% by wt.
BUTOXYETHANOL	111-76-2	3 - < 5

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations

US. Massachusetts RTK - Substance List

BUTOXYETHANOL (CAS 111-76-2)

US. New Jersey Worker and Community Right-to-Know Act

BUTOXYETHANOL (CAS 111-76-2)

US. Pennsylvania Worker and Community Right-to-Know Law

BUTOXYETHANOL (CAS 111-76-2)

US. Rhode Island RTK

BUTOXYETHANOL (CAS 111-76-2)

US. California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

16. Other information, including date of preparation or last revision

Issue date	07-03-2014
Revision date	05-13-2015
Version #	02
Disclaimer	The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.
Revision Information	Physical & Chemical Properties: Multiple Properties Toxicological Information: Toxicological Data Transport Information: Agency Name, Packaging Type, and Transport Mode Selection HazReg Data: North America GHS: Classification