

# Product data sheet

## Characteristics

# LAL364001021

Circuit breaker, LA, LH, Q4, unit mount, 400A, 3 pole, 22 kA, 600 VAC, 10 kA, 250 VDC, shunt trip



### Main

Product or component type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

### Complementary

Line Rated Current	400 A
Number of Poles	3P
Mounting Mode	Unit mount
Magnetic Hold Current	2000 A
Magnetic Tripping Current	4000 A
Electrical connection	Lugs load Lugs line
Terminal identifier	AL400LA
Tightening torque	115.06 Lbf.in (13 N.m) 0.07...0.47 in <sup>2</sup> (42...304 mm <sup>2</sup> ) (AWG 1...600 kcmil) 115.06 lbf.in (13 N.m) 0.07...0.20 in <sup>2</sup> (42...127 mm <sup>2</sup> ) (AWG 1...250 kcmil)
Height	11 in (279.40 mm)
Width	6 in (152.40 mm)
Depth	5.84 in (148.34 mm)

### Environment

Certifications	IEC CSA UL Listed
----------------	-------------------------

### Ordering and shipping details

Category	00935 - LAL/LHL BRKR, SW, MAG-GARD
Discount Schedule	DE2
GTIN	00785901339496
Nbr. of units in pkg.	1
Package weight(Lbs)	16.77 lb(US) (7.61 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	8.90 in (22.606 cm)
Package 1 width	11.50 in (29.210 cm)
Package 1 Length	17.40 in (44.196 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------