

Safety Data Sheet acc. to OSHA HCS (HazCom 2012)

Printing date 02/03/2021

Reviewed on 02/03/2021

1 Identification

- **Product identifier**
- **Trade name: Silicone Oil**
- **Catalogue number:** 194295
- **CAS Number:**
63148-62-9
- **Application of the substance / the mixture:** Laboratory chemicals
- **Manufacturer/Supplier:**
Tintometer Inc.
6456 Parkland Drive
Sarasota, FL 34243
USA
phone: (941) 756-6410
fax: (941) 727-9654
www.lovibond.us
Made in Germany
- **Emergency telephone number:** + 1 866 928 0789 (English, French, Spanish)

2 Hazard(s) identification

- **Classification of the substance or mixture**
The substance is not classified, according to the Globally Harmonized System (GHS).
- **Label elements**
- **GHS label elements** none
- **Hazard pictograms** none
- **Signal word** none
- **Hazard statements** none
- **Other hazards** No further relevant information available.

3 Composition/information on ingredients

- **Chemical characterization: Substances**
- **CAS No. Description**
63148-62-9 Siloxane, dimethyl
- **EC number:** 613-156-5

4 First-aid measures

- **Description of first aid measures**
- **General information:** Immediately remove any clothing soiled by the product.
- **After inhalation:**
Supply fresh air.
Seek medical treatment in case of complaints.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:**
Rinse opened eye for several minutes (at least 15 min) under running water. If symptoms persist, consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **Most important symptoms and effects, both acute and delayed**
Temporary clouding of vision.
after swallowing of large amounts:
gastric or intestinal disorders
diarrhoea

Safety Data Sheet

acc. to OSHA HCS (HazCom 2012)

Printing date 02/03/2021

Reviewed on 02/03/2021

Trade name: **Silicone Oil**

(Contd. of page 1)

· **Indication of any immediate medical attention and special treatment needed:** No further relevant information available.

* 5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **Special hazards arising from the substance or mixture**
Can burn in fire.
Formation of toxic gases is possible during heating or in case of fire.
In case of fire, the following can be released:
formaldehyde
Carbon monoxide (CO) and carbon dioxide (CO₂)
- **Advice for firefighters**
- **Protective equipment:**
Wear self-contained respiratory protective device.
Wear fully protective suit.
- **Additional information**
Collect contaminated fire fighting water separately. It must not enter the sewage system.
Dispose of fire debris and contaminated fire fighting water in accordance with official regulations.
Ambient fire may liberate hazardous vapours.

* 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**
- **Advice for non-emergency personnel:**
Do not breathe vapors/spray.
Particular danger of slipping due to leaked / spilled product.
- **Advice for emergency responders:** Protective equipment: see section 8
- **Environmental precautions:** Do not allow product to reach sewage system or any water course.
- **Methods and material for containment and cleaning up:**
Ensure adequate ventilation.
Absorb with liquid-binding material (sand, diatomite, universal binders).
Dispose contaminated material as waste according to item 13.
- **Reference to other sections**
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

* 7 Handling and storage

- **Precautions for safe handling**
- **Advice on safe handling:** No special precautions are necessary if used correctly.
- **Hygiene measures:**
Take off immediately all contaminated clothing.
Wash hands before breaks and at the end of work.
Do not eat, drink or smoke when using this product.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** Store in a cool location.
- **Information about storage in one common storage facility:** Store away from oxidizing agents.
- **Further information about storage conditions:**
Protect from heat and direct sunlight.
Protect from exposure to the light.
Protect from humidity and water.
- **Recommended storage temperature:** 20°C +/- 5°C (approx. 68°F)
- **Specific end use(s)** No further relevant information available.

— US —
(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS (HazCom 2012)

Printing date 02/03/2021

Reviewed on 02/03/2021

Trade name: **Silicone Oil**

(Contd. of page 2)

* 8 Exposure controls/personal protection

- **Control parameters**
- **Components with limit values that require monitoring at the workplace:** Not required.
- **Additional information:** The lists that were valid during the creation were used as basis.
- **Engineering measures:**
Technical measures and appropriate working operations should be given priority over the use of personal protective equipment. See item 7.
- **Personal protective equipment:**
Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled.
- **Breathing equipment:**
Under normal use conditions according to the instruction manual no personal protective equipment is needed. If exposure limits are exceeded or health impacts are experienced use respiratory protective device against the effects of fume/dust/aerosol.
- **Recommended filter device for short term use:** Filter AX
- **Protection of hands:**
Preventive skin protection by use of skin-protecting agents is recommended. After use of gloves apply skin-cleaning agents and skin cosmetics.
- **Material of gloves**
Nitrile rubber, NBR
Recommended thickness of the material: ≥ 0.11 mm
- **Penetration time of glove material**
Value for the permeation: Level ≤ 1 (10 min)
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Safety glasses
- **Body protection:** Protective work clothing
- **Limitation and supervision of exposure into the environment:**
Do not allow product to reach sewage system or any water course.

* 9 Physical and chemical properties

· Information on basic physical and chemical properties

· Appearance:

Form / Physical state:	Oily
Color:	Colorless

· Odor:	Odorless
· Odor threshold:	Not applicable.

· pH-value:	Not applicable.
--------------------	-----------------

· Melting point/freezing point:	Not applicable.
· Initial boiling point and boiling range:	$>35^{\circ}\text{C}$ ($>95^{\circ}\text{F}$) (CAS: 63148-62-9 Siloxane, dimethyl)

· Flash point:	$>120^{\circ}\text{C}$ ($>248^{\circ}\text{F}$) (c.c., CAS: 63148-62-9 Siloxane, dimethyl)
-----------------------	--

· Flammability (solid, gas):	The substance is capable of catching fire or being set on fire.
-------------------------------------	---

· Decomposition temperature:	$>150^{\circ}\text{C}$ ($>302^{\circ}\text{F}$)
-------------------------------------	---

· Auto-ignition temperature:	Product is not self-igniting.
-------------------------------------	-------------------------------

· Danger of explosion:	Product does not present an explosion hazard.
-------------------------------	---

· Flammability or explosive limits:	
Lower:	Not applicable.
Upper:	Not applicable.

· Oxidizing properties:	none
--------------------------------	------

· Vapor Pressure:	Not determined.
· Density at 20°C (68°F):	0.97 g/cm ³ (8.09 lbs/gal)
· Relative density:	Not determined.
· Vapor density:	Not determined.
· Evaporation rate:	Not determined.

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS (HazCom 2012)

Printing date 02/03/2021

Reviewed on 02/03/2021

Trade name: **Silicone Oil**

(Contd. of page 3)

· Solubility(ies) Water:	Not miscible or difficult to mix.
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity: Kinematic at 25°C (77°F):	350 mm ² /s
· Other information	No further relevant information available.

*10 Stability and reactivity

- **Reactivity** see section "Possibility of hazardous reactions"
- **Chemical stability** Stable at ambient temperature (room temperature).
- **Possibility of hazardous reactions** Reacts with oxidizing agents.
- **Conditions to avoid** Strong heating (decomposition)
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:**
formaldehyde
In case of fire: see section 5.

*11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:** Based on available data, the classification criteria are not met.

· **LD/LC50 values that are relevant for classification:**

CAS: 63148-62-9 Siloxane, dimethyl

Oral	LD50	15400 mg/kg (rat)
Dermal	LD50.	>2000 mg/kg (rat)

- **Primary irritant effect:**
- **on the skin:** Based on available data, the classification criteria are not met.
- **on the eye:** Based on available data, the classification criteria are not met.
- **Sensitization:** Based on available data, the classification criteria are not met.

· **Information on components:**

CAS: 63148-62-9 Siloxane, dimethyl

Sensitization	OECD 406	(guinea pig: negative)
---------------	----------	------------------------

· **Carcinogenic categories**

· **IARC (International Agency for Research on Cancer)**

Substance is not listed.

· **NTP (National Toxicology Program)**

Substance is not listed.

· **OSHA-Ca (Occupational Safety & Health Administration)**

Substance is not listed.

- **Other information:** see section 8 / 15

· **Synergistic Products:** None

· **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction):**

- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT (specific target organ toxicity) -single exposure** Based on available data, the classification criteria are not met.
- **STOT (specific target organ toxicity) -repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA HCS (HazCom 2012)

Printing date 02/03/2021

Reviewed on 02/03/2021

Trade name: **Silicone Oil**

(Contd. of page 4)

- **Additional toxicological information:**

When used and handled according to specifications, the product does not have any harmful effects according to our experience and the information provided to us.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Other adverse effects** Avoid transfer into the environment.

*13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
Must not be disposed of together with household garbage. Do not allow product to reach sewage system. Disposal must be made according to official regulations.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleansing agent:** Water, if necessary with cleansing agents.

14 Transport information

<ul style="list-style-type: none"> · UN-Number · DOT, IMDG, IATA 	none
<ul style="list-style-type: none"> · UN proper shipping name · DOT, IMDG, IATA 	none
<ul style="list-style-type: none"> · Transport hazard class(es) · DOT, IMDG, IATA · Class 	none
<ul style="list-style-type: none"> · Packing group · DOT, IMDG, IATA 	none
<ul style="list-style-type: none"> · Environmental hazards: 	Not applicable.
<ul style="list-style-type: none"> · Special precautions for user 	Not applicable.
<ul style="list-style-type: none"> · Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code 	Not applicable.
<ul style="list-style-type: none"> · Transport/Additional information: 	Not dangerous according to the above specifications.

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**

- **Section 355 (Extremely hazardous substances):**

Substance is not listed.

- **Section 313 (Specific toxic chemical listings):**

Substance is not listed.

- **TSCA (Toxic Substances Control Act):**

ACTIVE

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS (HazCom 2012)

Printing date 02/03/2021

Reviewed on 02/03/2021

Trade name: **Silicone Oil**

(Contd. of page 5)

· Hazardous Air Pollutants
Substance is not listed.
· Proposition 65
· Chemicals known to cause cancer:
Substance is not listed.
· Chemicals known to cause reproductive toxicity for females:
Substance is not listed.
· Chemicals known to cause reproductive toxicity for males:
Substance is not listed.
· Chemicals known to cause developmental toxicity:
Substance is not listed.
· New Jersey Right-to-Know List:
Substance is not listed.
· New Jersey Special Hazardous Substance List:
Substance is not listed.
· Pennsylvania Right-to-Know List:
Substance is not listed.
· Pennsylvania Special Hazardous Substance List:
Substance is not listed.
· EPA (Environmental Protection Agency)
Substance is not listed.
· NIOSH-Ca (National Institute for Occupational Safety and Health)
Substance is not listed.
· Information about limitation of use: Not required.
· Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

*16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Date of preparation / last revision 02/03/2021 / -

· Abbreviations and acronyms:

OECD: Organisation for Economic Co-operation and Development
 STOT: specific target organ toxicity
 SE: single exposure
 RE: repeated exposure
 EC50: half maximal effective concentration
 IC50: half maximal inhibitory concentration
 NOEL or NOEC: No Observed Effect Level or Concentration
 ACGIH[®] - American Conference of Governmental Industrial Hygienists
 •A1 - Confirmed human carcinogen
 •A2 - Suspected human carcinogen
 •A3 - Confirmed animal carcinogen with unknown relevance to humans
 •A4 - Not classifiable as a human carcinogen
 •A5 - Not suspected as a human carcinogen
 IARC - International Agency for Research on Cancer
 •Group 1 - Carcinogenic to humans
 •Group 2A - Probably carcinogenic to humans
 •Group 2B - Possibly carcinogenic to humans
 •Group 3 - Not classifiable as to carcinogenicity to humans
 •Group 4 - Probably not carcinogenic to humans
 NTP - National Toxicology Program, U.S. Department of Health and Human Services
 •Group K - Known to be Human Carcinogens
 •Group R - Reasonably Anticipated to be Human Carcinogens
 IMDG: International Maritime Code for Dangerous Goods
 DOT: US Department of Transportation
 IATA: International Air Transport Association
 EINECS: European Inventory of Existing Commercial Chemical Substances
 CAS: Chemical Abstracts Service (division of the American Chemical Society)
 LC50: Lethal concentration, 50 percent
 LD50: Lethal dose, 50 percent
 NIOSH: National Institute for Occupational Safety
 OSHA: Occupational Safety & Health
 TLV: Threshold Limit Value

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS (HazCom 2012)

Printing date 02/03/2021

Reviewed on 02/03/2021

Trade name: Silicone Oil

PEL: Permissible Exposure Limit
REL: Recommended Exposure Limit

(Contd. of page 6)

· Sources

Data arise from safety data sheets, reference works and literature.
ECHA: European CHemicals Agency <http://echa.europa.eu>

· * Data compared to the previous version altered.

— US —