

HSM[®] Classic

225.2 L6 shredder

Professional data security; ideal central device for large offices



EPL Listed*

- Auto start via electronic eye
- New auto stop with LED is triggered automatically when bin is full or door is open
- Powerful, specially adjusted motor for longer periods of use - with thermal protection for high performance
- Tried and tested closed tooth wheel drive prevents penetration of dirt and slows wear, increasing the service life
- Enclosed housing protects against the spread of paper dust and provides for quiet operation
- Casters for increased mobility and shared use
- Anti-Jam technology designed to easily and quickly reverse in the event machine is overloaded
- External auto-oiler included
- Uses a 58 gallon capacity shred bag; Part #HSM2117



HSM part#	HSM14584
Cutting type	Cross cut
Cutting size	1/32" x 3/16"
Security level DIN 32757-1	6
Security level DIN 66399	P-7 F-3
Cutting capacity per run in sheets	10 - 12 [^]
Cutting Speed	27 ft / min
Throat opening	12"
Motor at maximum number of sheets	1440W
Motor power (horsepower)	1.93
Voltage	115 V / 60Hz
Dimensions (H x W x D)	35 1/5" x 19 7/10" x 18 1/2"
Weight	106 lbs
Shred-bin volume	31.7 gal
Cutting capabilities	

All technical specifications are approximate values. Technical and design modifications reserved.

*Meets DOD and NSA/CSS 02-01 mandatory security requirements

[^]Sheet capacity will vary depending on paper size, weight, quality and proper power supply

HSM of America, LLC
 419 Boot Road
 Downingtown, PA 19335
 www.hsmofamerica.com
 Customer Service: 800.613.2110

Great Products, Great People.

HSM[®]