

Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	40 A
Number of Poles	3P
Pole contact composition	3 NO
Range of Product	DPA

Complementary

Maximum Horse Power Rating	3 Hp 115 V AC, 1 phase 7.5 Hp 230 V AC, 1 phase 10 Hp 230 V AC, 3 phase 20 Hp 460 V AC, 3 phase 25 hp 575 V AC, 3 phase
Locked rotor rated current	240 A 277 V AC 200 A 460 V AC 160 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	3 phase
Electrical Connection	Quick connect terminals Box lugs
Height	2.31 In (58.67 mm) 2.31 in (58.70 mm)
Width	2.37 In (60.20 mm) 2.4 in (60.2 mm)
Depth	2.90 In (73.66 mm) 3.0 in (76 mm)
Net Weight	0.99 Lb(US) (0.45 kg) 0.99 lb(US) (0.45 kg)

Environment

Product Certifications	UL Recognized[RETURN]CSA
------------------------	--------------------------

Ordering and shipping details

Category	US1CP1B21344
Discount Schedule	CP1B
GTIN	785901073444
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.500 in (6.350 cm)
Package 1 Width	3.0000000000 in (7.620 cm)
Package 1 Length	4.0000000000 in (10.160 cm)
Package 1 Weight	16.736 oz (474.457 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	6.900 in (17.526 cm)
Package 2 Width	5.600 in (14.224 cm)
Package 2 Length	8.500 in (21.590 cm)
Package 2 Weight	8.501 lb(US) (3.856 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------