



Main

Range of product	EZ meter-pak
Product or component type	Meter center main unit
Main type	Main Lugs
Included Items	Box

Complementary

Main rated current	1200 A
Bus rated current	1200 A
Material	Aluminium/copper busbar
Enclosure material	Steel
[Ue] rated operational voltage	120/240 V AC
Device mounting	Surface
Number of Phases	1 phase in 1 phase out
Service feed location	UG
Electrical connection	Lugs 1 AWG 6...300 kcmil aluminium/copper) ground Studs 3line Studs 3neutral
Wiring configuration	3-wire
Height	44.71 in (1135.63 mm)
Width	33.16 in (842.26 mm)
Depth	11.12 in (282.45 mm)

Environment

Product certifications	UL Listed
Enclosure Rating	NEMA 3R

Ordering and shipping details

Category	00020-EZ METER-PAK
Discount Schedule	DE4
GTIN	00785901262411
Package weight(Lbs)	88.00 lb(US) (39.916 kg)
Returnability	Yes
Country of origin	MX

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------