



## Main

Range of product	125 A Frame EDB-EGB-EJB
Product or component type	Miniature circuit-breaker
Device short name	EGB
Module type	E-Frame
Trip unit rating	1800 A

## Complementary

Line Rated Current	40 A
Maximum operating voltage	480Y/277 V AC
AWG gauge	AWG 12...AWG 2/0 aluminium AWG 14...AWG 2/0 copper
Breaking capacity	35 KA 277 V AC 65 KA 240 V AC 35 KA 480Y/277 V AC 65 KA 120 V AC 65 kA 120/240 V AC
Circuit breaker application	HACR rated HID rated
Electrical connection	Lugs aluminium
Holding current	630 A
Local signalling	Trip indicator
Mounting mode	Bolt-on
Number of poles	3
Number of spaces	4
Number of spaces required	4
Product destination	NF panelboard
Protection type	Short-circuit Overload
Device composition	Shunt trip
Trip unit technology	Thermal-magnetic
Breaking capacity code	G
Tightening torque	34.52 Lbf.in (3.9 N.m) 0.00...0.01 in <sup>2</sup> (2.5...6 mm <sup>2</sup> ) (AWG 14...AWG 10) 49.56 lbf.in (5.6 N.m) 0.02...0.11 in <sup>2</sup> (10...70 mm <sup>2</sup> ) (AWG 8...AWG 2/0)
Height	5.66 in (143.76 mm)
Width	3.92 in (99.57 mm)
Depth	4.05 in (102.87 mm)
Net Weight	4 lb(US) (1.81 kg)

## Environment

Product certifications	CULus
Ambient air temperature for operation	104 °F (40 °C)

## Ordering and shipping details

Category	00936 - EGB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901285182
Nbr. of units in pkg.	1
Package weight(Lbs)	4.12 lb(US) (1.87 kg)
Returnability	No
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------