

# Product data sheet

## Characteristics

# 8903S QO1V03

Contactor, Type S, multipole lighting,  
electrically held, 100A, 2 pole, 220/240 VAC  
50/60 Hz coil, open style



### Main

Product	Electrically Held Lighting Contactor
Type	S

### Complementary

Control Circuit Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Current Rating	100 A
Number of Poles	2P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical connection	Lugs
Height	7.24 in (184 mm)
Depth	6.50 in (165 mm)
Width	5.43 in (138 mm)

### Environment

Enclosure Type	Not rated (open device) surface none
Product certifications	UL Listed CSA

### Ordering and shipping details

Category	21325 - 8903 S (NOT S°C) ELECT.
Discount Schedule	CP1
GTIN	00785901024057
Nbr. of units in pkg.	1
Package weight(Lbs)	11.78 lb(US) (5.34 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	7.30 in (18.542 cm)
Package 1 width	8.80 in (22.352 cm)
Package 1 Length	14.30 in (36.322 cm)

## Offer Sustainability

EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------