



Main

| | |
|---------------------------------------|-----------------------------------|
| Range compatibility | Harmony XVM Optimum |
| Accessory / separate part category | Lighting accessory |
| Accessory / separate part type | Incandescent bulb |
| Accessory / separate part designation | Incandescent bulb |
| Accessory / separate part destination | Beacon and indicator bank |
| Bulb base | BA 15d |
| Signalling type | Steady |
| [Us] rated supply voltage | 120 V AC/DC |
| Luminance | 60.39 fc (650 cd/m ²) |
| Sale per indivisible quantity | 10 |

Complementary

| | |
|--------------------------------|------------------------|
| Maximum power dissipation in W | 5 W |
| Net Weight | 0.02 lb(US) (0.007 kg) |

Ordering and shipping details

| | |
|-----------------------|-------------------------|
| Category | 22611 - XVB-STACKLIGHTS |
| Discount Schedule | XV |
| GTIN | 00785901682806 |
| Nbr. of units in pkg. | 10 |
| Package weight(Lbs) | 0.02 lb(US) (0.01 kg) |
| Returnability | Yes |
| Country of origin | ID |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 1.97 in (5 cm) |
| Package 1 width | 1.38 in (3.51 cm) |
| Package 1 Length | 3.46 in (8.8 cm) |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 3.07 oz (87 g) |
| Package 2 Height | 1.38 in (3.5 cm) |
| Package 2 width | 1.97 in (5 cm) |
| Package 2 Length | 3.46 in (8.8 cm) |
| Unit Type of Package 3 | S01 |
| Number of Units in Package 3 | 140 |
| Package 3 Weight | 3.30 lb(US) (1.499 kg) |
| Package 3 Height | 5.91 in (15 cm) |
| Package 3 width | 5.91 in (15 cm) |
| Package 3 Length | 15.75 in (40 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|