

VLSA11DS

Disconnect switch, TeSys VLS, auxiliary contact block, 1 normally closed and 1 normally open, door



Main

Range	TeSys
Device short name	VLSA
Product or component type	Auxiliary contact block
Performance level	High performance
Contacts type and composition	1 NC + 1 NO
Contact operation	Simultaneous 1 NC Simultaneous 1 NO
Range compatibility	TeSys VARIO LS VLSA TeSys VARIO LS VLS3P TeSys VARIO LS VLS1P
Network type	DC AC
Network frequency	50/60 Hz

Complementary

Mounting location	Right Left
Main device mounting support	Door
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	10 A 131 °F (55 °C)
[Ithe] conventional enclosed thermal current	10 A
[Ie] rated operational current	6 A AC-15)24 V AC 6 A AC-15)48 V AC 6 A AC-15)127 V AC 3 A AC-15)240 V AC 3 A DC-13)24 V DC 1.5 A DC-13)48 V DC 0.55 A DC-13)127 V DC 0.27 A DC-13)240 V DC
Minimum output current	10 mA
Minimum output voltage	5 V
Connections - terminals	Control circuit screw clamp terminals 0.00 in ² (2.5 mm ²) flexible - without cable end
Tightening torque	Control circuit 7.08...8.85 lbf.in (0.8...1 N.m) screw clamp terminals
Height	2.86 in (72.6 mm)
Width	0.33 in (8.5 mm)
Depth	1.82 in (46.2 mm)
Net Weight	0.07 lb(US) (0.03 kg)
Color	Grey

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	UL 508 CSA C22.2 No 14 IEC 60947-3 IEC 60947-5
Product certifications	CULus GL
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 2...100 Hz Fc 0.7 g) IEC 60068-2-6 Shocks 11 ms Ea 15 gn) IEC 60068-2-27
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Fire resistance	1562 °F (850 °C) IEC 60695-2-11

Ordering and shipping details

Category	21734 - TESYS VLS DISCONNECT SWITCHES
Discount Schedule	CP1
GTIN	00785901568360
Nbr. of units in pkg.	1
Package weight(Lbs)	0.1 lb(US) (0.05 kg)
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.29 dm
Package 1 width	0.66 dm
Package 1 Length	0.88 dm

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration