

# Product data sheet

## Characteristics

# 8501CDO22V64

Power Relay, Type C, 10A resistive at 110 VDC, DPDT, 2 normally open and 2 normally closed contact, 220 VDC coil



### Main

Product range	Power Relay 8501C
Product type	Power relay
Short name	Type C
[In] rated line current	20 A
Device application	Suited for controlling small single phase motors and other light loads
Switch function	DPDT
Contact composition	2 NO/2 NC
[Uc] control circuit voltage	220 V DC
Maximum switching voltage	325 V DC

### Complementary

Class number	8501
Phase	1 phase
Terminal connects	Screw clamp terminal
Wire range	AWG 10 copper
Terminal tightening torque	11...15 lbf.in (1.24...1.69 N.m)
Coil burden	2 W
Mounting	Panel mounting

### Environment

Ambient temperature range - operational	-22...140 °F (-30...60 °C)
Product certifications	UL listed file E78351 CCN NLDX CSA CE
Height	3.12 in (79.25 mm)
Width	2.5 in (63.50 mm)
Depth	2.53 in (64.26 mm)

### Ordering and shipping details

Category	21131 - 8501 C
Discount Schedule	CP2
Nbr. of units in pkg.	1
Package weight(Lbs)	0.49 lb(US) (0.22 kg)
Returnability	No
Country of origin	CN

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------