



### Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1FH
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F265 LC1F330
Control circuit type	AC at 40...400 Hz
[Uc] control circuit voltage	220...230 V AC 40...400 Hz
Average resistance	70.6 Ohm inrush 68 °F (20 °C) 1578 Ohm holding 68 °F (20 °C)
Operating time	100...170 ms opening 40...65 ms closing
Mechanical durability	10 Mcycles
Maximum operating rate	2400 cyc/h 131 °F (55 °C)

### Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out 0.35...0.55 U <sub>c</sub> 40...400 Hz 131 °F (55 °C) Operational 0.85...1.1 U <sub>c</sub> 40...400 Hz 131 °F (55 °C)
Inrush power in VA	650 VA 40...400 Hz 0.9 68 °F (20 °C)
Hold-in power consumption in VA	10 VA 40...400 Hz 0.3 68 °F (20 °C)
Heat dissipation	8 W 40...400 Hz

### Environment

Ambient air temperature for operation	23...131 °F (-5...55 °C)
Net Weight	1.65 lb(US) (0.75 kg)

### Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901553359
Nbr. of units in pkg.	1
Package weight(Lbs)	1.87 lb(US) (0.85 kg)
Returnability	Yes
Country of origin	CZ

### Packing Units

Package 1 Height	0.950 dm
Package 1 width	1.000 dm
Package 1 Length	1.900 dm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------